

Corning® Fetal Bovine Serum

CORNING

Why Choose Corning Fetal Bovine Serum?

Corning offers a wide variety of fetal bovine serum (FBS) options to satisfy most common applications and is a perfect complement to Corning classical cell culture media. Our direct relationship with abattoirs helps support a consistent supply, reducing the risk of supply shortages. Corning FBS is fully traceable to the abattoir and meets the industry's toughest quality standards.

Origin

Our Premium FBS, with an endotoxin specification of less than 5 EU/mL, and hemoglobin specification of less than 25 mg/dL, is only collected from government inspected abattoirs in the United States, Australia and New Zealand. All FBS is derived from healthy bovine cows and heifers that have passed ante- and post-mortem inspection and were found free of contagious diseases.

Our Regular FBS, with an endotoxin specification of less than 20 EU/mL, and hemoglobin specification of less than 30 mg/dL, is derived from government registered abattoirs in South America and recognized by the World Organization for Animal Health (OIE) as having negligible risk of Bovine Spongiform Encephalopathy (BSE) and being free from foot and mouth disease (FMD).

True Pooled Sterile Filtered

All Corning FBS is triple 0.1 micron sterile filtered. In addition to USP <71> and EP 2.6.1 sterility testing, all lots must test negative for mycoplasma.

Serum is true pooled after filtration to ensure consistency from bottle to bottle within a lot. True pooling greatly reduces the variability within a lot.

Certificate of Analysis and Biochemical Profile

Corning sera products are evaluated for quality, performance and analytical testing, including sterility, mycoplasma, total protein, endotoxin and hemoglobin levels in compliance with current versions of the USP and/or EP, where applicable. Premium FBS also undergoes virus testing. A biochemical profile is also provided with each lot. All of this information can be found on our comprehensive Certificate of Analysis at www.corning.com/resources.

Custom Testing, Volume, Vessels, or Pack Sizes

In addition to our comprehensive standard suite of testing and characterization, Corning offers customized testing, volume, vessels, or pack sizes upon request. If the test you require is not present on the Certificate of Analysis, simply inquire with your Corning sales representative to see if a custom testing solution is available.



Other Certifications

Corning's FBS supply chain is certified for traceability by the International Serum Industry Association (ISIA).

Corning holds Certificates of Suitability (CEP) from the European Directorate for the Quality of Medicines (EDQM) for US origin, New Zealand origin, and Australian origin FBS.

Ordering Information

Products may not be available in all markets.

Corning® Fetal Bovine Serum

Cat. No.	Description	Storage	Size	Qty/Pk
35-010-CV	Fetal Bovine Serum, regular, USDA Safety Tested	-40°C to -10°C	500 mL	1
35-011-CV	Fetal Bovine Serum, regular, USDA Safety Tested (heat inactivated)	-40°C to -10°C	500 mL	1
35-079-CV	Fetal Bovine Serum, regular, South American Origin	-40°C to -10°C	500 mL	1
35-089-CV	Fetal Bovine Serum, regular, South American Origin (heat inactivated)	-40°C to -10°C	500 mL	1
35-015-CV	Fetal Bovine Serum, premium, US Origin	-40°C to -10°C	500 mL	1
35-016-CV	Fetal Bovine Serum, premium, US Origin (heat inactivated)	-40°C to -10°C	500 mL	1
35-070-CV	Fetal Bovine Serum, premium, US Origin (gamma irradiated)	-40°C to -10°C	500 mL	1
35-017-CV*	Fetal Bovine Serum, premium, US Origin (heat inactivated and gamma irradiated)	-40°C to -10°C	500 mL	1
35-071-CV	Fetal Bovine Serum, premium, US Origin (dialyzed)	-40°C to -10°C	500 mL	1
35-072-CV	Fetal Bovine Serum, premium, US Origin (charcoal stripped)	-40°C to -10°C	500 mL	1
35-073-CV	Fetal Bovine Serum, premium, US Origin (ultra low IgG)	-40°C to -10°C	500 mL	1
35-075-CV	Fetal Bovine Serum, premium, US Origin (tetracycline negative)	-40°C to -10°C	500 mL	1
35-076-CV	Fetal Bovine Serum, premium, Australian Origin	-40°C to -10°C	500 mL	1
35-086-CV	Fetal Bovine Serum, premium, Australian Origin (heat inactivated)	-40°C to -10°C	500 mL	1
35-096-CV	Fetal Bovine Serum, premium, Australian Origin (gamma irradiated)	-40°C to -10°C	500 mL	1
35-106-CV*	Fetal Bovine Serum, premium, Australian Origin (heat inactivated and gamma irradiated)	-40°C to -10°C	500 mL	1
35-078-CV	Fetal Bovine Serum, premium, New Zealand Origin	-40°C to -10°C	500 mL	1
35-088-CV	Fetal Bovine Serum, premium, New Zealand Origin (heat inactivated)	-40°C to -10°C	500 mL	1
35-098-CV	Fetal Bovine Serum, premium, New Zealand Origin (gamma irradiated)	-40°C to -10°C	500 mL	1
35-108-CV*	Fetal Bovine Serum, premium, New Zealand Origin (heat inactivated and gamma irradiated)	-40°C to -10°C	500 mL	1

*Made to order. Please contact your local Corning Account Manager for more details.

Small sizes available for purchase. Please inquire about availability.

Cat. No.	Description	Storage	Size	Qty/Pk
35-010-CF	Fetal Bovine Serum, regular, USDA Safety Tested	-40°C to -10°C	50 mL	1
35-011-CF	Fetal Bovine Serum, regular, USDA Safety Tested (heat inactivated)	-40°C to -10°C	50 mL	1
35-079-CF	Fetal Bovine Serum, regular, South American Origin	-40°C to -10°C	50 mL	1
35-089-CF	Fetal Bovine Serum, regular, South American Origin (heat inactivated)	-40°C to -10°C	50 mL	1
35-015-CF	Fetal Bovine Serum, premium, US Origin	-40°C to -10°C	50 mL	1
35-016-CF	Fetal Bovine Serum, premium, US Origin (heat inactivated)	-40°C to -10°C	50 mL	1
35-072-CF	Fetal Bovine Serum, premium, US Origin (charcoal stripped)	-40°C to -10°C	50 mL	1
35-076-CF	Fetal Bovine Serum, premium, Australian Origin	-40°C to -10°C	50 mL	1
35-086-CF	Fetal Bovine Serum, premium, Australian Origin (heat inactivated)	-40°C to -10°C	50 mL	1
35-078-CF	Fetal Bovine Serum, premium, New Zealand Origin	-40°C to -10°C	50 mL	1
35-088-CF	Fetal Bovine Serum, premium, New Zealand Origin (heat inactivated)	-40°C to -10°C	50 mL	1

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.



Corning Incorporated
Life Sciences
www.corning.com/lifesciences

NORTH AMERICA
t 800.492.1110
t 978.442.2200

ASIA/PACIFIC
Australia/New Zealand
t 61 427286832
Chinese Mainland
t 86 21 3338 4338

India
t 91 124 4604000
Japan
t 81 3-3586 1996
Korea
t 82 2-796-9500
Singapore
t 65 6572-9740
Taiwan
t 886 2-2716-0338

EUROPE
CSEurope@corning.com

France
t 0800 916 882

Germany
t 0800 101 1153

The Netherlands
t 020 655 79 28

United Kingdom
t 0800 376 8660

All Other European Countries
t +31 (0) 206 59 60 51

LATIN AMERICA
grupoLA@corning.com

Brazil
t 55 (11) 3089-7400

Mexico
t (52-81) 8158-8400