

Corning® PET Media Bottles with Leak-proof Screw Cap Validated Against IATA Standards

CORNING

For leak-proof storage of media, sera, and other aqueous solutions

Corning's polyethylene terephthalate (PET) disposable bottles are designed for safe, secure storage of tissue culture media, sera, buffers, and other aqueous solutions. The PET resin makes the bottle lightweight, break resistant, and as transparent as glass.


The screw cap is designed to ensure leak-proof performance and is validated against IATA standards for primary packaging used in air transportation.

Features

- ▶ Available in four sizes: 125 mL, 250 mL, 500 mL, and 1000 mL
- ▶ Packaged in convenient, shrink-wrapped trays within an outer bag to ensure cleanliness
- ▶ Break-resistant bottles are an ergonomic and easy to handle alternative to glass
- ▶ Bottles have Sterility Assurance Level (SAL) of 10^{-6}
- ▶ Molded graduations for accurate measurements
- ▶ Bottle materials meet USP Class VI requirements and are noncytotoxic, nonhemolytic, and nonpyrogenic
- ▶ Innovative HDPE screw cap is validated against IATA standards to ensure leak-proof air transport conditions



Physical Properties of Corning® PET Bottles



Molded graduations for accurate measurements

	Chemical Resistance		Sterilization	Thermal Durability
	Recommended	Not Recommended		
Polyethylene Terephthalate (PET) Bottles	Weak acids	Strong acids, ketones, aliphatic, aromatic, and chlorinated hydrocarbons	Do not autoclave	50°C

Ordering Information

Corning PET Media Bottles with Leak-proof Screw Cap Validated Against IATA Standards

Cat. No.	Capacity (mL)	Screw Cap Color	Neck I.D. (mm)	Screw Cap (mm)	Qty/Tray	Qty/Cs
432331	125	Natural	31.7	34.7	24	48
432332	250	Natural	31.7	34.7	24	48
432333	500	Natural	31.7	34.7	12	24
432334	1000	Natural	31.7	34.7	12	24

Bottles are packaged in convenient, shrink-wrapped trays within an outer bag to ensure cleanliness.

For more specific information on claims, visit the Certificates page at www.corning.com/lifesciences.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110. Outside the United States, call +1.978.442.2200 or contact your local Corning sales office.

CORNING

Corning Incorporated
Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

ASIA/PACIFIC
Australia/New Zealand
t 61 427286832

Chinese Mainland
t 86 21 3338 4338
f 86 21 3338 4300

India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291

Korea
t 82 2-796-9500
f 82 2-796-9300

Singapore
t 65 6572-9740
f 65 6735-2913

Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE
CSEurope@corning.com

France
t 0800 916 882
f 0800 918 636

Germany
t 0800 101 1153
f 0800 101 2427

The Netherlands
t 020 655 79 28
f 020 659 76 73

United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries
t +31 (0) 206 59 60 51
f +31 (0) 206 59 76 73

LATIN AMERICA
grupoLA@corning.com

Brazil
t 55 (11) 3089-7400

Mexico
t (52-81) 8158-8400