

# Corning® Cell Strainers

Simplify Single Cell Sample Prep

CORNING

## Corning Cell Strainers Fit All Major Brands of 50 mL Conical Tubes

Corning Cell Strainers are ready-to-use devices for rapidly isolating primary cells and making uniform single-cell suspensions. You can use these versatile devices to prepare:

- ▶ Samples for flow cytometry
- ▶ Single cell suspensions of blood cells
- ▶ Specimens for primary cell cultures and immunogens
- ▶ Primary cells from tissue

You can also use them to:

- ▶ Pre-filter solutions containing particulates >40 µm
- ▶ Clean cell suspensions prior to sub-culturing, counting, analysis or freezing

Features:

- ▶ Strong nylon mesh with 40, 70 or 100 µm pores for optimal performance in a variety of applications
- ▶ Noncytotoxic
- ▶ Sterilized by gamma irradiation
- ▶ Individually packed in easy to open bags
- ▶ Color-coded polypropylene frames
- ▶ Grip area for handling with forceps


New!





## Corning® Cell Strainers Ordering Information

Cat. No.	Pore Size	Color	Qty/Pk	Qty/Cs
431750	40 µm	Blue	1	50
431751	70 µm	White	1	50
431752	100 µm	Yellow	1	50



[www.corning.com/lifesciences/solutions](http://www.corning.com/lifesciences/solutions)

At Corning, cells are in our culture. In our continuous efforts to improve efficiencies and develop new tools and technologies for life science researchers, we have scientists working in Corning R&D labs across the globe, doing what you do every day. From seeding starter cultures to expanding cells for assays, our technical experts understand your challenges and your increased need for more reliable cells and cellular material.

It is this expertise, plus a 160-year history of Corning innovation and manufacturing excellence, that puts us in a unique position to offer a beginning-to-end portfolio of high-quality, reliable cell culture consumables.

For additional product or technical information, please visit [www.corning.com/lifesciences](http://www.corning.com/lifesciences) or call 800.492.1110. Customers outside the United States, please call +1.978.442.2200 or contact your local Corning sales office.

### Corning Incorporated Life Sciences

836 North St.  
Building 300, Suite 3401  
Tewksbury, MA 01876  
t 800.492.1110  
t 978.442.2200  
f 978.442.2476

[www.corning.com/lifesciences](http://www.corning.com/lifesciences)

### Worldwide Support Offices

#### ASIA/PACIFIC

**Australia/New Zealand**  
t 0402-794-347

**China**  
t 86 21 2215 2888  
f 86 21 6215 2988

**India**  
t 91 124 4604000  
f 91 124 4604099

**Japan**  
t 81 3-3586 1996  
f 81 3-3586 1291

**Korea**  
t 82 2-796-9500  
f 82 2-796-9300

**Singapore**  
t 65 6733-6511  
f 65 6861-2913

**Taiwan**  
t 886 2-2716-0338  
f 886 2-2516-7500

### EUROPE

**France**  
t 0800 916 882  
f 0800 918 636

**Germany**  
t 0800 101 1153  
f 0800 101 2427

**The Netherlands**  
t 31 20 655 79 28  
f 31 20 659 76 73

**United Kingdom**  
t 0800 376 8660  
f 0800 279 1117

### All Other European Countries

t 31 (0) 20 659 60 51  
f 31 (0) 20 659 76 73

### LATIN AMERICA

**Brasil**  
t (55-11) 3089-7419  
f (55-11) 3167-0700

**Mexico**  
t (52-81) 8158-8400  
f (52-81) 8313-8589

**CORNING** | **FALCON**® **AXYGEN**® **GOSELIN**® **PYREX**®

**Warranty/Disclaimer:** Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

For a listing of trademarks, visit us at [www.corning.com/lifesciences/trademarks](http://www.corning.com/lifesciences/trademarks). All other trademarks are the property of their respective owners.