

Made in the USA

A collection of six graduated cylinders of various sizes and orientations, each containing a colored liquid (red, blue, green, or orange). The cylinders are labeled with volume measurements such as "2ml in 1/100", "5ml in 1/10", and "2ml in 1/100".

Corning serological pipets are proudly manufactured in the United States to strict quality standards. Domestic manufacturing reduces transport emissions and promotes supply assurance.



The serological pipets now feature a human DNA-free claim. Pipets will be tested by DNA detection assay per ISO 18385 and found to be free of detectable human DNA. The limit of detection is 10^{-11} g of human genomic DNA.



Extractables analysis is conducted in accordance with USP <665>. Data is available upon customer request.



The serological pipets are sterilized and dosimetrically released per the requirements of ANSI/AAMI/ISO 11137. The Sterility Assurance Level has been increased from a SAL of 10^{-3} to 10^{-6} .

Ordering Information



Individually Wrapped, Clear Plastic Wrap


Cat. No.	Capacity (mL)	Graduations (mL)	Negative Grads. (mL)	Color-coded Stripe	Qty/Pk	Qty/Cs
4011	1	1/100	0.2	Yellow	50	1,000
4012	1	1/100	0.2	Yellow	50	200
4021	2	1/100	0.2	Green	50	1,000
4051	5	1/10	2.5	Blue	50	200
4101	10	1/10	3.0	Orange	50	200
4492*	10	1/10	3.0	Orange	50	200
4251	25	2/10	10.0	Red	50	200
4501	50	1/2	10.0	Purple	25	100
4484	100	1	n/a	Aqua	10	100

*Cat. No. 4492 features a wide tip for handling viscous fluids.



Individually Wrapped, Paper/Plastic Wrap

4485	1	1/100	0.2	Yellow	50	1,000
4486	2	1/100	0.2	Green	50	1,000
4487	5	1/10	2.5	Blue	50	200
4488	10	1/10	3.0	Orange	50	200
4489	25	2/10	10.0	Red	25	200
4490	50	1/2	10.0	Purple	25	100
4491	100	1	N/A	Aqua	10	100



Bulk Packed in Bags

4010	1	1/100	0.2	Yellow	50	1,000
4020	2	1/100	0.2	Green	50	1,000
4050	5	1/10	2.5	Blue	50	500
4100	10	1/10	3.0	Orange	50	500
4250	25	2/10	10.0	Red	25	200
4500	50	1/2	10.0	Purple	25	100

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.

CORNING

For additional product or technical information, visit www.corning.com/lifesciences or call 800.492.1110. Outside the United States, call +1.978.442.2200.