

Corning® Australian Origin Fetal Bovine Serum

CORNING

Corning's Australian Origin Fetal Bovine Serum (FBS) is a high-quality option for a variety of cell culture applications. Specifically designed to support the most demanding scientific research, our FBS sourced from government inspected abattoirs in Australia, ensures stringent specifications, traceability, and compliance with industry standards. Corning's strong relationship with abattoirs ensures a steady and consistent supply of Australian Origin FBS. This direct sourcing minimizes supply chain disruptions, providing researchers with a dependable product.

Strict Quality Standards

Our Premium FBS, with an endotoxin specification of less than 5 EU/mL, and hemoglobin specification of less than 25 mg/dL. This ensures performance consistency in sensitive applications.

Filtration

All Corning FBS is triple 0.1 micron sterile filtered. In addition to USP <71> and EP 2.6.1 sterility testing, all lots must test negative for mycoplasma.

Comprehensive Testing

Corning sera products are evaluated for quality, performance and analytical testing, including sterility, mycoplasma, virus testing, total protein, endotoxin and hemoglobin levels in compliance with current versions of the USP and/or EP, where applicable. All of this information can be found on our comprehensive Certificate of Analysis at www.corning.com/resources.

Certifications

Corning's FBS supply chain is certified for traceability by the International Serum Industry Association (ISIA).

Corning holds Certificates of Suitability (CEP) from the European Directorate for the Quality of Medicines (EDQM) for Australian origin FBS.

Ordering Information

Corning Australian Origin Fetal Bovine Serum

Cat. No.	Description	Storage	Size	Qty/Pk
35-076-CV	Fetal Bovine Serum, premium, Australia Origin	-40°C to -10°C	500 mL	1
35-086-CV	Fetal Bovine Serum, premium, Australia Origin (heat inactivated)	-40°C to -10°C	500 mL	1
35-096-CV	Fetal Bovine Serum, premium, Australia Origin (gamma irradiated)	-40°C to -10°C	500 mL	1
35-106-CV*	Fetal Bovine Serum, premium, Australia Origin (heat inactivated and gamma irradiated)	-40°C to -10°C	500 mL	1

*Made to order. Please contact your local Account Representative for more details.



How to Purchase: For specific availability in your region and purchasing options, terms and conditions of sale, customer/product support, and certificates, visit www.corning.com/how-to-buy.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.

CORNING

Corning Incorporated
Life Sciences

www.corning.com/lifesciences

NORTH AMERICA

t 800.492.1110

t 978.442.2200

ASIA/PACIFIC

Australia/New Zealand

t 61 427286832

Chinese Mainland

t 86 21 3338 4338

India

t 91 124 4604000

Japan

t 81 3-3586 1996

Korea

t 82 2-796-9500

Singapore

t 65 6572-9740

Taiwan

t 886 2-2716-0338

EUROPE

CSEurope@corning.com

France

t 0800 916 882

Germany

t 0800 101 1153

The Netherlands

t 020 655 79 28

United Kingdom

t 0800 376 8660

All Other European Countries

t +31 (0) 206 59 60 51

LATIN AMERICA

grupolA@corning.com

Brazil

t 55 (11) 3089-7400

Mexico

t (52-81) 8158-8400

The information contained within is accurate as of the date of publication and subject to change without notice.

For a listing of trademarks, visit www.corning.com/trademarks. All other trademarks are the property of their respective owners.

© 2025 Corning Incorporated. All rights reserved. 8/25 CLS-CG-153