



CORNING

Jumper in a box (JIAB)

2019 Part Number Configurators

Jumper in a box (JIAB)

Part Number Configurators

SC and LC Simplex



1 Select connector code.

Single-Mode
 0202 = LC UPC
 2222 = LC APC
 2244 = LC APC/SC APC
 4444 = SC APC
 5858 = SC UPC

2 Defines cable type and fiber type.

SR2 = Simplex R 1.6 mm cable diameter, single-mode (OS2)

3 Select quantity. Quantity per box is determined by length.

B70 = 1-5 m or 1-16 ft
 B50 = 6-10 m or 17-35 ft
 B40 = 11-15 m or 36-52 ft
 B30 = 16-20 m or 53-66 ft

4 Select jumper length*.


01 - 20 meters
 01 - 65 feet

**Maximum length is 30 m or 65 ft.*

5 Select unit of measure.

F = Feet
 M = Meters

SC Duplex



1 Select connector code.

Multimode Duplex
 5757 = SC PC
 Single-Mode Duplex
 7272 = SC UPC

2 Select cable type and fiber type.

ZR4 = 2.0 mm Zipcord R MM OM4
 ZR3 = 2.0 mm Zipcord R MM OM3
 ZR2 = 2.0 mm Zipcord R SM OS2
 ZR1 = 2.0 mm Zipcord R MM OM1

3 Select quantity. Quantity per box is determined by length.

B60 = 1-2 m or 1-7 ft
 B50 = 3-4 m or 8-13 ft
 B40 = 5-6 m or 14-20 ft
 B35 = 7-8 m or 21-26 ft
 B30 = 9-10 m or 27-33 ft

4 Select jumper length*.

01 - 10 meters
 01 - 33 feet

**Maximum length is 10 m or 33 ft.*

5 Select unit of measure.

F = Feet
 M = Meters



CORNING

LET'S CONNECT!



Corning Optical
Communications
corning.com/ISP

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019 Corning Optical Communications. All rights reserved. CRR-1187-AEN / July 2019