



CORNING

Optical Splice Enclosure

A transition splice solution made for high density.

Indoor Transition Splice Architecture

When transitioning fiber and cable from outdoors to indoors, operators require a rugged enclosure that is optimized for quick re-entry and network expansion. There are three vital components that make up a transition splice solution: an enclosure, cable entry kits, and splice trays. Corning's optical splice enclosure (OSE) portfolio not only offers these three vital components, but also offers varying densities, scalability, and excellent fiber management.

Where does an OSE fit within an optical communications network?

- Building entrance terminal
- Splice vault
- Equipment room

Optical Splice Enclosure High Density



Flexible cable entry

- Top or bottom cable entry available
- Horizontal pass-through ports located near top and bottom of enclosure
- Cable entry plates allow standard cable entry and mid-span cable access

High-density splice trays

- Enclosure holds up to 30 trays
- Individual splice trays can hold up to 144 fibers
- Up to 3,240 single-fiber splice capacity per enclosure
- Up to 4,320 ribbon splice capacity per enclosure

Cable management

- Routing guides are located at the top of the enclosure to organize the cable
- Routing guides are also located on the side of each splice tray

Ease of installation

- A workshelf is available that can be placed within the bottom left- and right-side walls for improved splice tray access
- The workshelf is ideal when an enclosure is mounted within a rack

Additional Features and Benefits

- Wall mountable or 23-in rack mountable
- Enclosure dimensions (H x W x D): 114.0 x 55.9 x 33.0 cm
- Enclosure material: .090-in 5052-H32 aluminum sheet
- Locking feature available to place on door for increased protection

CORNING

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/ trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019 Corning Optical Communications. All rights reserved. CRR-624-AEN / July 2019