

FREEDM® Loose Tube, Indoor/Outdoor, Gel-Free, Interlocking Armored Cables, Riser

CORNING

Features and Benefits

Gel-free waterblocking technology

Craft-friendly cable preparation

Loose tube design

Mechanical ruggedness and environmental durability

Color-coded tubes and fibers

Quick and easy identification

All-dielectric cable construction

Requires no grounding or bonding

Flexible interlocking armor

Up to seven times the crush protection compared to non-armored cables

Common installations

Outdoor aerial and duct; indoor vertical riser and general purpose horizontal according to NEC Article 770

Corning FREEDM® loose tube gel-free interlocking armored cables are flame-retardant, indoor/outdoor, riser-rated cables for interbuilding and intrabuilding backbones in aerial, duct and riser applications. Encased in a spirally wrapped, aluminum interlocking armor for ruggedness and superior crush resistance, these cables are ideal for industrial and heavy traffic areas and installations requiring extra protection for optical cables and for high-fiber-count trunking applications in areas with limited conduit or vault space. The riser rating precludes the need for a transition splice when entering the building.

These cables are available in fiber counts up to 72 fibers and are protected against water penetration by innovative waterblocking materials. These materials swell to absorb water without the use of messy gels to provide more efficient and craft-friendly cable preparation, making cable access easier and simplifying the use of buffer tube fan-out kits. The buffer tubes and fibers in each tube are color coded for quick, easy identification. The SZ-stranded, loose tube design isolates fibers from installation, environmental rigors and allows for easy mid-span access. Available in 50 μm , 62.5 μm , single-mode and hybrid versions, the cable design is NEC listed.

The armored design allows for easy one-step installation which reduces overall installation costs. The UV-resistant, flame-retardant jacket is rugged and easy to strip.


Standards

Listings


National Electrical Code®
(NEC®) OFCR, CSA FT-4

Design and Test Criteria

ANSI/ICEA S-104-696; CSA
FT-4



FREEDM Loose Tube Interlocking Armored Cables,
36 Fibers | Photo PIM0808




FREEDM Loose Tube Interlocking Armored Cables,
36 Fibers | Photo PIM1708


CORNING

FREEDM® Loose Tube, Indoor/Outdoor, Gel-Free, Interlocking Armored Cables, Riser

CORNING



FREEDM Loose Tube Interlocking Armored Cables, 288 Fibers | Photo PIM0817



FREEDM Loose Tube Interlocking Armored Cables, 288 Fibers | Photo PIM1717

Specifications

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

* Note: Corning recommends storing indoor/outdoor cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Mechanical Characteristics Cable

Max. Tensile Strength, Short-Term	2700 N (600 lbf)
Max. Tensile Strength, Long-Term	810 N (180 lbf)

Fiber Count	Buffer Tube Diameter	Min. Bend Radius Installation	Nominal Outer Diameter	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Min. Bend Radius Operation	Weight
12 - 72	2.5 mm (0.1 in)	299 mm (11.8 in)	20.7 mm (0.81 in)	2700 N (600 lbf)	810 N (180 lbf)	207 mm (8.15 in)	293 kg/km (196.8 lb/1000 ft)
96	2.5 mm (0.1 in)	309 mm (12.2 in)	20.6 mm (0.81 in)	2700 N (600 lbf)	810 N (180 lbf)	206 mm (8.11 in)	318 kg/km (213.6 lb/1000 ft)
144	2.5 mm (0.1 in)	383 mm (15.1 in)	24.9 mm (0.98 in)	2700 N (600 lbf)	810 N (180 lbf)	249 mm (9.8 in)	440 kg/km (295.6 lb/1000 ft)

CORNING

FREEDM® Loose Tube, Indoor/Outdoor, Gel-Free, Interlocking Armored Cables, Riser

CORNING

Fiber Count	Buffer Tube Diameter	Min. Bend Radius Installation	Nominal Outer Diameter	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Min. Bend Radius Operation	Weight
192 - 216	2.5 mm (0.1 in)	383 mm (15.1 in)	24.9 mm (0.98 in)	2700 N (600 lbf)	810 N (180 lbf)	255 mm (10 in)	413 kg/km (277.5 lb/1000 ft)
240 - 288	2.5 mm (0.1 in)	425 mm (16.7 in)	27.4 mm (1.08 in)	2700 N (600 lbf)	810 N (180 lbf)	283 mm (11.1 in)	493 kg/km (331.2 lb/1000 ft)

Chemical Characteristics

RoHS

Free of hazardous substances according to RoHS 2002/95/EG

Transmission Performance

Multimode					
Fiber Core Diameter (μm)	62.5	50	50	50	50
Fiber Category	OM1	OM2	OM3	OM4	OM4 Extended Distance
Fiber Code	K	T	T	T	T
Performance Option Code	30	31	80	90	91
Wavelengths (nm)	850/1300	850/1300	850/1300	850/1300	850/1300
Maximum Attenuation (dB/km)	3.4/1.0	3.0/1.0	3.0/1.0	3.0/1.0	3.0/1.0
Serial 1 Gigabit Ethernet (m)	300/550	750/500	1000/600	1100/600	1100/600
Serial 10 Gigabit Ethernet (m)	33/-	150/-	300/-	550/-	600/-
Min. Overfilled Launch (OFL) Bandwidth (MHz*km)	200/500	700/500	1500/500	3500/500	3500/500
Minimum Effective Modal Bandwidth (EMB) (MHz*km)	220/-	950/-	2000/-	4700/-	5350/-

* 50 μm multimode fiber (OM3/OM4) meets 0.75 ns optical skew when used in all Corning Plug & Play™/EDGE™ systems solutions.

* 50 μm multimode fiber (OM4) T90 10 Gigabit Ethernet distance assumes 1.0 dB maximum total connector/splice loss.

* 50 μm multimode fiber (OM4) T91 10 Gigabit Ethernet Distance assumes 0.7 dB maximum total connector/splice loss.

CORNING

FREEDM® Loose Tube, Indoor/Outdoor, Gel-Free, Interlocking Armored Cables, Riser

CORNING

Single-mode		
Typical Attenuation* (dB/km)	-	0.33/0.33/0.19
Fiber Name	Single-mode (OS2)	SMF-28® Ultra fiber
Fiber Category	G.652.D	G.657.A1
Fiber Code	E	Z
Performance Option Code	01	01
Wavelengths (nm)	1310/1383/1550	1310/1383/1550
Maximum Attenuation (dB/km)	0.4/0.4/0.3	0.4/0.4/0.3

* Improved attenuation and bandwidth options available.

* Bend-insensitive single-mode fibers available on request.

* 50 µm multimode fiber macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

* Contact a Corning Customer Care Representative for additional information.

Ordering Information | Note: Contact Customer Care at 1-800-743-2675 for other options.

				U	F	-	T	4	1			D	A	1
1	2	3	4	5	6	7	8	9	10					

1 Select fiber count.
Standard offerings:
012-288
Increments of 12

2 Select fiber code.
K = 62.5 µm multimode (OM1)
T = 50 µm multimode (OM2/OM3/OM4/OM4+)
E = Single-mode (OS2) SMF-28e+®
Z = Single-mode (OS2) SMF-28® Ultra fiber

3 Defines cable type.
U = Loose tube

4 Defines outer jacket.
F = Indoor/outdoor riser

5 Defines fiber placement.
T = 12 fibers/buffer tube (standard)

6 Defines length markings.
4 = Markings in ft (standard)

7 Defines tensile strength.
1 = See specifications

8 Select performance option code.
30 = 62.5 µm multimode (OM1)
31 = 50 µm multimode (OM2)
80 = 50 µm multimode (OM3)
90 = 50 µm multimode (OM4)
91 = 50 µm multimode (OM4+)
01 = Single-mode (OS2) (Max. attenuation 0.4/0.4/0.3 dB/km)

9 Defines cable type.
D = Gel-free cable

10 Defines special manufacturing code.
A1 = Interlocking armor with riser-rated outer jacket

Note: This cable is available in 12 different jacket colors: blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. Black is the standard jacket color using the part number configurator above. Contact Customer Care at 1-800-743-2675 to order other color options.

CORNING

FREEDM® Loose Tube, Indoor/Outdoor, Gel-Free, Interlocking Armored Cables, Riser

CORNING

Notes



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.

All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.

CORNING