

Reel In A Box, MIC® Tight-Buffered Cable, Riser

CORNING

Features and Benefits

"Countdown" print indicates available cable remaining on the reel providing easier inventory management

Stackable boxes make storage more manageable

Smaller reel offerings mean smaller cable lengths than would normally be available

Cable cutting at Corning lowers operating expenses for our distributors and end users

Reel in a Box is Corning's innovative packaging solution for small reels of fiber optic cable in all inside plant applications, such as collocation data centers and wireless projects. This packaging solution provides features that enable our customers greater efficiencies than before.

Corning MIC® riser cables are designed for use in riser and general purpose environments for intrabuilding back-bone and horizontal installations. These multifiber cables use 900 µm buffered fibers to enable easy, consistent stripping and facilitate termination. The fibers are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.


Standards

Listings

National Electrical Code® (NEC®) OFNR, FT-4

Design and Test Criteria


UL-1666 and CSA FT-4 (for riser and general building applications); ICEA S-83-596



CORNING

Reel In A Box, MIC[®] Tight-Buffered Cable, Riser

CORNING



Specifications

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

* Note: Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Mechanical Characteristics Cable

Max. Tensile Strength, Short-Term	660 N (150 lbf)
Max. Tensile Strength, Long-Term	200 N (45 lbf)

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Weight
2	4.3 mm (0.17 in)	64.5 mm (2.5 in)	43 mm (1.7 in)	14.7 kg/km (9.88 lb/1000 ft)
4	4.6 mm (.18 in)	69 mm (2.7 in)	46 mm (1.8 in)	17.6 kg/km (11.82 lb/1000 ft)

CORNING

Reel In A Box, MIC[®] Tight-Buffered Cable, Riser

CORNING

Transmission Performance

Multimode					
Fiber Core Diameter (μm)	62.5	50	50	50	50
Fiber Category	OM1	OM2	OM3	OM4	OM4 Extended Distance
Fiber Code	K	T	T	T	T
Performance Option Code	30	31	80	90	91
Wavelengths (nm)	850/1300	850/1300	850/1300	850/1300	850/1300
Maximum Attenuation (dB/km)	3.4/1.0	2.8/1.0	2.8/1.0	2.8/1.0	2.8/1.0
Serial 1 Gigabit Ethernet (m)	300/550	750/600	1000/600	1000/600	1100/600
Serial 10 Gigabit Ethernet (m)	33/-	150/-	300/-	550/-	600/-
Min. Overfilled Launch (OFL) Bandwidth (MHz*km)	200/500	700/500	1500/500	3500/500	3500/500
Minimum Effective Modal Bandwidth (EMB) (MHz*km)	220/-	950/-	2000/-	4700/-	5350/-

Notes: 1) 50 μm multimode fiber macrobend loss ≤0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel.

Single-mode		
Fiber Name	SMF-28e [®] fiber	SMF-28 [®] Ultra fiber
Fiber Category	G.652.D	G.652.D/G.657.A1
Fiber Code	E	Z
Performance Option Code	31	31
Wavelengths (nm)	1310/1383/1550	1310/1383/1550
Maximum Attenuation (dB/km)	0.65/0.65/0.50	0.65/0.65/0.50

CORNING

Reel In A Box, MIC® Tight-Buffered Cable, Riser

CORNING

Ordering Information | *Note: Contact Customer Care at 1-800-743-2675 for other options.*

<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	8	1	-	3	1	1	<input type="text"/>	<input type="text"/>	-	<input type="text"/>	<input type="text"/>
1	2	3	4	5	6	7	8	9	10					

1 Select fiber count.
Standard offerings:
002 004

2 Select fiber code.
K = 62.5 µm multimode (OM1)
T = 50 µm multimode
(OM2/OM3/OM4/OM4+)
E = Single-mode (OS2)
SMF-28e® fiber
Z = Single-mode (OS2)
SMF-28® Ultra fiber

3 Defines cable type.
8 = Standard for MIC® cable

4 Defines outer jacket.
1 = Standard for riser

5 Defines fiber placement.
3 = Standard

6 Defines length markings.
1 = Markings in ft
(fiber count ≤ 10)

7 Defines tensile strength.
1 = See specifications

8 Select performance option code.
30 = 62.5 µm multimode (OM1)
31 = 50 µm multimode (OM2)
80 = 50 µm multimode (OM3)
90 = 50 µm multimode (OM4)
91 = 50 µm multimode (OM4+)
31 = Single-mode (OS2)
(Max. attenuation .65 / .65 / 0.5 dB/km)

9 Defines cable type.
- = Standard for MIC cable

10 Select reel length.
B1 = 500 ft (150 m)
B2 = 1000 ft (300 m)
B3 = 1500 ft (450 m)
B4 = 2000 ft (600 m)
B5 = 3000 ft (900 m)

Reel in a Box Shipping Dimensions (HxWxD)
39.37 x 39.37 x 38.73 cm – 15.5 x 15.5 x 15.25 in

Note: This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.

CORNING