

Classic Closet Connector Housings (CLSSC)

CORNING

Features and Benefits

Interconnect and cross-connect capability

Ideal for field connectorization

Ideal for loose tube, tight-buffered and ribbon

Variety of options

Field-installed lock kit

Security

Quality tested

Meets ANSI/TIA/EIA-568A and 606

Mounting provisions for buffer tube fan-out kits

Ideal for field connectorization

Housings have sliding tray (01U and 02U) or open top at front (03U and 04U)

Ease of access

Corning classic closet connector housings (CLSSC) provide interconnect or cross-connect capabilities between outside plant, riser or distribution cables and opto-electronics. The housings accept CCH connector panels. The units are designed for rack mounting in 19-in (48 cm) racks or optional 23-in (58 cm) equipment racks (1.75-in EIA hole spacing).

The CLSSC-01U and -02U can be mounted in 23-in racks by flipping the provided 19-in housing brackets, while 23-in extension brackets are available for the CLSSC-03U and -04U. They are available in rack space options of 1U (two panels), 2U (four panels), 3U (six panels) and 4U (12 panels). The 1U and 2U options feature a slide-out tray, while 3U and 4U options are designed with an open top at the front of the housing for ease of access and jumper routing.

Classic closet connector housings are compatible with CCH connector panels for multimode and single-mode applications in 6-, 8-, 12-, 16- and 24-fiber configurations. Documentation labels are provided, and components can be added as needed to construct a fiber distribution frame for any application. The units include multiple locations for jumper egress and come with the universal cable clamp for cable strain-relief. The 03U and 04U versions include a removable tinted-polycarbonate front door, and optional top and side covers are also available. All housings have field-installable lock kits available.




CLSSC-01U Classic Closet Connector Housing
| Photo LAN1859



CLSSC-04U Classic Closet Connector Housing
| Photo LAN1860

Classic Closet Connector Housings (CLSSC)



Ordering Information

Part Number	Description	Dimensions	Shipping
CLSSC-01U	Classic Closet Connector Housing; accepts up to two CCH panels; comes with blank panels and hardware to strain relieve one cable with the universal cable clamp (UCC) or up to five 0.4 in or smaller	4.4 cm x 43 cm x 30.5 cm (1.75 in x 17 in x 12 in)	4 lb (8.7 kg)
CLSSC-02U	Classic Closet Connector Housing; accepts up to four CCH panels; comes with blank panels and hardware to strain relieve one cable with the universal cable clamp (UCC) or up to five 0.4 in or smaller	8.9 cm x 43 cm x 30.5 cm (3.5 in x 17 in x 12 in)	4.3 lb (9.5 kg)
CLSSC-03U	Classic Closet Connector Housing (CLSSC), 3U, holds six CCH connector panels	13.3 cm x 43 cm x 30.5 cm (5.2 in x 16.9 in x 12 in)	4.6 lb (10.2 kg)
CLSSC-04U	Classic Closet Connector Housing; accepts up to 12 CCH panels; comes with blank panels and hardware to strain relieve one cable with the universal cable clamp (UCC) or up to five 0.4 in or smaller	17.8 cm x 43 cm x 30.5 cm (7 in x 17 in x 12 in)	4.9 lb (10.8 kg)

Classic Closet Connector Housings (CLSSC)

CORNING





Accessories

Part Number	Product Description	Units per Delivery	
CLSSC1-LABEL10	Replacement Label Kit for the CLSSC-01U/-02U/-03U; contains 10 1U high labels	1/1	
CLSSC4-LABEL10	Replacement Label Kit for the CCH, 4-rack-space housing; contains 10 labels	1/1	
CPP-UCC-KIT	Universal Cable Clamp Kit for CLSSC-01U and CLSSC-02U	1/1	
CLSSC4-UCC-KIT	Universal Cable Clamp Kit (UCCK) for CLSSC-03U and CLSSC-04U	1/1	
CJP-01U-P	Pretium® Jumper Management Panel 1U; provides jumper management in a 1.75-in rack space	1/1	
CJP-02U-P	Pretium® Jumper Management Panel 2U; provides jumper management in a 3.5-in rack space	1/1	
HDWR-LOCK-KIT	Lock Kit for front door of housing; contains one lock with two keys	1/1	
FDC-CABLE-GRND	Armored Cable Grounding Kit; contains armored grounding clip and ground strap	1/1	
CLSSC4-TOP-CVR	Patch Field Cover, covers top opening in CLSSC-03U/CLSSC-04U housings	1/1	
CLSSC4-SIDEPNL	Side Panels CLSSC-04U; kit includes two panels	1/1	
CDF-03U-23-BKT	Mounting Brackets for CCH-03U and CLSSC-03U, 23-in	1/1	
CDF-04U-23-BKT	Mounting Brackets for CCH-04U and CLSSC-04U, 23-in	1/1	

Classic Closet Connector Housings (CLSSC)

CORNING

Accessories

Part Number	Product Description	Units per Delivery	
CDF-01U-24-BKT	Mounting Brackets for CCH-01U and CLSSC-01U, 24-in	1/1	
CDF-02U-24-BKT	Mounting Brackets for CCH-02U and CLSSC-02U, 24-in	1/1	
CDF-03U-24-BKT	Mounting Brackets for CCH-03U and CLSSC-03U, 24-in	1/1	
CDF-04U-24-BKT	Mounting Brackets for CCH-04U and CLSSC-04U, 24-in	1/1	
CLSSC1-RECESS-KIT	CLSSC Flush-Mount Brackets, CLSSC-01U; 5 pairs	1/1	
CLSSC2-RECESS-KIT	CLSSC Flush-Mount Brackets, CLSSC-02U; 1 pair	1/1	
CPP-03U-RECESS-KIT	Flush-Mount Brackets, CLSSC-03U; 1 pair	1/1	
CPP-04U-RECESS-KIT	Flush Mounting Brackets CLSSC-04U, 1 pair	1/1	
CJH-02U	Rear-Mounted Closet Splice Housing designed to utilize the open space behind the 2U jumper management panel (CJP-02U), holds (4) 0.2-in splice trays	1/1	
CJH-02U-F	Rear-Mounted Closet Splice Housing designed to utilize the open space behind the 2U jumper management panel (CJP-02U), holds (3) 0.4-in splice trays	1/1	

* Note: Connector panels and modules must be ordered separately.

Classic Closet Connector Housings (CLSSC)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING



**Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm**

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018 Corning Optical Communications. All rights reserved.

The Corning logo consists of the word "CORNING" in a large, bold, sans-serif font.