

# Fiber Zone Box (FZB-04P)

CORNING

## Features and Benefits

**Mounts vertically or horizontally**  
Easy viewing of adapter plane

**Removable cover and air holes**  
Aids in cooling

**Accommodates up to four CCH-style panels or Plug & Play™ Systems modules**  
96-fiber density

**Strain-relief for Plug & Play™ Systems plugs provided**  
Integrated solution for Plug & Play™ Systems

**Simple, intuitive design**  
Quick installation

Corning fiber zone box (FZB-04P) is a smaller alternative to the flagship FZB-04U. Ideal for installations up to 96 fibers, the FZB-04P manages four CCH panels or Plug & Play™ systems modules. The FZB-04P can be mounted vertically or horizontally. When mounted vertically, the adapter plane of the panels or modules faces up toward the installer. This creative design element significantly increases the installer's and end user's ease-of-use for initial installation as well as moves, adds and changes. Strain-relief is an important aspect of all housings, particularly when placed in a sub-floor environment. The FZB-04P comes equipped with integrated strain-relief for Corning Plug & Play systems trunk plugs as well as the universal cable clamp (UCC) for standard installations. From installation to daily maintenance, the FZB015004P is a convenient, easy-to-use product designed with the installer in mind.



**Fiber Zone Box (FZB-04P)**  
| Photo LAN1408



**Fiber Zone Box (shown with 24-fiber LC duplex adapter CCH panels)** | Photo LAN1465


# Fiber Zone Box (FZB-04P)

CORNING

## Ordering Information

Part Number	Description	Dimensions (HxWxD)	Shipping Weight
FZB-04P	Fiber Zone Box designed to accommodate 4 CCH-style panels or Plug & Play™ Systems modules	10.1 cm x 45.7 cm x 32 cm (4 in x 18 in x 12.6 in)	15 lb (6.8 kg)

## Accessories

Part Number	Product Description	Units per Delivery	
UCC-001	Universal Cable Clamp, strain-relief kit, includes one cable clamp	1/1	

\* Connector panels and modules must be ordered separately. Refer to LAN-133-EN and LAN-664-EN for additional ordering information.

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). Corning Optical Communications is ISO 9001 certified. © 2014 Corning Optical Communications. All rights reserved.

CORNING