

Closet Connector Housing Panels (CCH-CP)

CORNING

Features and Benefits

Universal design approach

One-size-fits-all LANScape® Solutions housings


Broadest range of fiber count and adapter types

Solutions for all needs

Colored icon labeling

Easy connector identification

Corning closet connector housing panels (CCH-CP) are offered in a variety of fiber counts for use with LANScape® solutions hardware products for a “one-size-fits-all” approach. Used with factory-installed or field-installable connectors, these panels provide inter-connect or cross-connect capability in a housing at main cross-connections, intermediate cross-connections, telecommunication rooms or work areas. Available with a variety of industry-standard adapter types, the CCH-CP provides an efficient way to securely mate two connectors and offers multimode and single-mode applications in 6-, 8-, 12-, 16- and 24-fiber count options, plus 36-, 72-, 96- and 144-fiber count options with MTP® connector adapters.



LC Duplex Panel (24-fiber) and MTP Connector Panel (72-fiber) | Photo LAN4525



ST Compatible Panel (12-fiber) and SC Duplex Connector Panel (12-fiber) | Photo LAN4526

Closet Connector Housing Panels (CCH-CP)

CORNING

Ordering Information

CCH-CP	<div><div></div><div></div></div>	-	<div><div></div><div></div></div>
	1		2

1 Select fiber count.


- 06 = 6 fibers
- 08 = 8 fibers
- 12 = 12 fibers
- 16 = 16 fibers
- 24 = 24 fibers
- 36 = 36 fibers
- 72 = 72 fibers
- 96 = 96 fibers
- E4 = 144 fibers

See Note 1.

2 Select adapter code (see Adapter/Connector Code Options table).

Note: Fiber count for desired adapter is available in table on following page.

Part Number Example

Part Number	Product Description	Units per Delivery	
CCH-CP12-A9	Closet Connector Housing (CCH) Panel, LC adapters, Duplex, UPC, 12 F, Single-mode (OS2)	1/1	

CORNING

Closet Connector Housing Panels (CCH-CP)

CORNING

Adapter Code	Fiber Type	Alignment	Housing	Fiber/ Adapter	Available Fiber/Panel Counts									
					6	8	12	16	24	36	72	96	144	
LC Duplex														
A8	62.5 µm multimode (OM1)	Ceramic	Composite	2	X	X	X	X	X					
D3	50 µm multimode (OM2)	Ceramic	Composite	2	X	X	X	X	X					
E4	50 µm multimode (OM3/4)	Ceramic	Composite	2	X	X	X	X	X					
A9	Single-mode, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
B3	Single-mode, APC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
LC Duplex Shuttered														
AB	62.5 µm multimode (OM1)	Ceramic	Composite	2	X	X	X	X	X					
AC	50 µm multimode (OM2)	Ceramic	Composite	2	X	X	X	X	X					
AD	50 µm multimode (OM3/4)	Ceramic	Composite	2	X	X	X	X	X					
AE	Single-mode, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X		X			
AF	Single-mode, APC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
Non-keyed LC Duplex														
BE	Single-mode, red, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BF	Single-mode, black, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BG	Single-mode, yellow, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BH	Single-mode, green, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BJ	Single-mode, violet, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BK	Single-mode, orange, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BL	Single-mode, rose, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
BM	Single-mode, slate, UPC (OS2)	Ceramic	Composite	2	X	X	X	X	X					
SC Duplex														
91	62.5 µm multimode (OM1)	Metal	Composite	2	X	X	X							
G7	50 µm multimode (OM2)	Ceramic	Composite	2	X	X	X							
E7	50 µm multimode (OM3/4)	Ceramic	Composite	2	X	X	X							
59	Single-mode, UPC (OS2)	Ceramic	Composite	2	X	X	X							
D9	Single-mode, APC (OS2)	Ceramic	Composite	2	X	X	X							
SC														
56	62.5 µm multimode (OM1)	Metal	Composite	1	X	X	X							
G6	50 µm multimode (OM2)	Ceramic	Composite	1	X	X	X							
E6	50 µm multimode (OM3/4)	Ceramic	Composite	1	X	X	X							
3C	Single-mode, UPC (OS2)	Ceramic	Composite	1	X	X	X							
6C	Single-mode, APC (OS2)	Ceramic	Composite	1	X	X	X							
ST® Compatible Connector														
15T	62.5 µm multimode (OM1)	Ceramic	Metal	1	X	X	X							
G5	50 µm multimode (OM2)	Ceramic	Metal	1	X	X	X							
H3	50 µm multimode (OM3/4)	Ceramic	Metal	1	X	X	X							
19T	Single-mode, UPC (OS2)	Ceramic	Metal	1	X	X	X							
FC														
11	Single-mode, UPC (OS2)	Metal	Metal	1	X	X	X							
21	Single-mode, APC (OS2)	Metal	Metal	1	X	X	X							
MTP® Connector														
69	62.5 µm multimode (OM1)	N/A	Composite	12							X	X	X	X
G3	50 µm multimode (OM2)	N/A	Composite	12							X	X	X	X
E3	50 µm multimode (OM3/4)	N/A	Composite	12							X	X	X	X
90	Single-mode (OS2)	N/A	Composite	12							X	X	X	X
Fiber Type		Housing Color, Simplex and Duplex					Housing Color, MTP							
62.5 µm multimode (OM1)		Beige					Black							
50 µm multimode (OM2)		Black					Black							
50 µm multimode (OM3/4)		Aqua					Aqua							
Single-mode, UPC (OS2)		Blue					Black							
Single-mode, APC (OS2)		Green					Black							

Closet Connector Housing Panels (CCH-CP)

The Corning logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

Notes



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.

The Corning logo consists of the word "CORNING" in a large, bold, uppercase, sans-serif font.