

OptiSheath® MultiPort Splitter Terminals



Features and Benefits

OptiTap® Single-fiber Connector ports for customer drop terminations

Lower installation costs and faster customer connections

OptiTip® Multifiber Connector ports integrate with FlexNAP™ System

Lower initial deployment cost, greater design flexibility

Available with preterminated or non-connectorized stubs

Add terminals as needed to defer costs

Available with 1x4 or 1x8 splitter

Reduces distribution cable fiber count

Available with expansion port

Easily enables future growth

Factory-installed and -tested connectors

Reliability and quality assurance

The OptiSheath® MultiPort Splitter Terminal is designed for use in outside plant fiber access networks. This innovative terminal provides fast, easy subscriber connections and splitter functionality in one low-profile housing. By enabling incremental subscriber connections, costs are deferred to better match revenue streams. Splitter functionality reduces the distribution cable fiber count requirement, lowering initial cost. The terminal's reliability and flexibility make it the ideal choice for network access point terminals in all-fiber access networks and fiber-to-the-x (FTTx) deployments.

The OptiSheath MultiPort Splitter Terminal is available in these configurations: 4-port (1x4 splitter) with expansion port, 4-port (1x4 splitter) and 8-port (1x8 splitter).

Terminals stubbed with the OptiTip® Multifiber Connector work with the FlexNAP™ Terminal Distribution System, improving design flexibility. Terminals with non-connectorized stubs may be consolidated and spliced at a splice enclosure. The ability to route several stubs to one location increases workforce efficiency and reduces the overall installation time required to connect customers in FTTx networks.

Standards

Design and Test Criteria	Telcordia GR-771-CORE, Issue 1
Common Installations	Splitters meet applicable sections of GR-1209-CORE and GR-1221-CORE
Approvals and Listings	RDUP (RUS) Listed



OptiSheath MultiPort Splitter Terminals, 1x4 and 1x4 with Expansion Port | Photo TRCLS211A




OptiSheath® MultiPort Splitter Terminals

CORNING



Universal Mounting Bracket, MOB-KT-UNIV-BKT
| Photo TRCLS002



OptiSheath MultiPort Splitter Terminals with the
FlexNAP System | Drawing ZA-3672

Specifications

Mechanical Characteristics

	Dimensions (L x W x H)	Weight
OptiSheath MultiPort Splitter Terminal	381 mm x 101 mm x 147 mm (15.0 in x 4.0 in x 5.8 in)	1.1 kg (2.4 lb)

Shipping Package

	Packaging Dimensions (L x H x W)	Weight	Packaging Method
Terminal Stub Length (cables ≤ 350 ft)	152 mm x 762 mm x 762 mm (6 in x 30 in x 30 in)	-	Box
Terminal Stub Length (cables > 350 ft)	846 mm x 178 mm x 846 mm (33 in x 7 in x 33 in)	-	Reel

Optical Characteristics

	Fiber Type	Insertion Loss, Maximum	Insertion Loss, Typical	Reflectance, Maximum
OptiTap® Single-Fiber Connector	Single-mode (OS2)	0.50 dB	0.15 dB	-65 dB
OptiTip® Multifiber Connector	Single-mode (OS2)	0.50 dB	0.35 dB	≤ -65 dB

CORNING

OptiSheath® MultiPort Splitter Terminals

CORNING

Ordering Information

M		S	-			4	4						W	-	
	1				2			3		4		5			6

1 Select stub end.

- O = No connector
- T = OptiTap® Single-fiber Connectors
- T = OptiTip® Multifiber Connector (with expansion port only)

2 Select splitter type.

- F8 = 1x8, no expansion port
- H4 = 1x4, no expansion port
- H5 = 1x4, with expansion port

3 Select cable type.

- FD = SST flat dielectric drop cable
- TD = SST flat toneable drop cable

4 Select cable length.

Examples:

- 025 = 25 ft
- 050 = 50 ft
- 075 = 75 ft
- 100 = 100 ft
- 500 = 500 ft
- 050 = 500 ft
- A00 = 1000 ft

See Note 1.

5 Select unit of measure.

- F = Feet
- M = Meters

6 Select packaging.

- P = Individual packaging

See Notes 2 and 3.

Table A: Alpha Codes for lengths ≥ 1000 ft

A00	=	1000
B00	=	1100
C00	=	1200
D00	=	1300
E00	=	1400
F00	=	1500
G00	=	1600
H00	=	1700
J00	=	1800
K00	=	1900
L00	=	2000

1) Minimum cable length is 10 ft or 3 m. Additional lengths may be ordered in increments of 10 and 25 ft or 5 m. For lengths ≥ 1000 ft (see Table A). Maximum length is 3400 ft or 1035 m.

2) Leave blank for bulk packaging; minimum order quantities will apply.

3) Shipping reel provided on lengths greater than 350 ft or 106 m.

4) Please contact Customer Care at 1-800-743-2675 for extended length offerings.

CORNING

OptiSheath® MultiPort Splitter Terminals

CORNING

Hardware Accessories

Part Number	Product Description	Units per Delivery	
MOB-KT-UNIV-BKT	Universal Mounting Bracket Pack for 4- and 12-port housing	10/1	

Cleaning Accessories

Part Number	Product Description	Units per Delivery	
CLEANER-PORT-OTAP	Single-fiber Port Cleaner for OptiTap® connector end faces	1/1	

Related Products

FlexNAP™ System Brochure	EVO-601-EN
FlexNAP™ Outside Plant System	CRR-114-AEN
FlexNAP™ System Design Guide	EVO-659-EN
OptiTap® Single-Fiber Connector	EVO-592-EN

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2015 Corning Optical Communications. All rights reserved.

CORNING