

# ROC™ Drop Toneable Cables with FastAccess™ Technology

CORNING

## Features and Benefits

### FastAccess technology

Saves time and reduces complexity

### No special tools

Ease of use

### Backward compatible

Enables fast connectorization and splicing

### Innovative cable design

Retains industry standard hardware compatibility such as wedge clamps

### Compact, robust design

Improves ease of handling and installation; reduces transportation and storage costs

### Toneable


Underground detection

ROC™ Drop Toneable Cables with FastAccess™ Technology provides a more efficient, craft-friendly cable preparation unparalleled by traditional flat drop cables. The innovative FastAccess Technology design simplifies removal of the cable jacket resulting in up to 55 percent faster fiber access time than traditional drop cables. This technology improves ease of use because no special tools are needed. The cable design is backward compatible for easy connectorization or splicing. Optimized for both field-and-factory termination processes, the compact design allows for easier handling in the field, reduces slack storage requirements and improves transportation and storage costs. The toneable version allows for easy detection of buried cables with a toning conductor. ROC Drop Toneable with FastAccess Technology are also available in preconnectorized assemblies.

## Standards

Design and Test Criteria

Meets Telcordia GR-20 requirements



ROC Drop Toneable Cable, 1-Fiber

CORNING

# ROC™ Drop Toneable Cables with FastAccess™ Technology

CORNING

## Specifications

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-30 °C to 70 °C (-22 °F to 158 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

\* Note: Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Mechanical Characteristics Cable	
Max. Tensile Strength, Long-Term	400 N (90 lbf)
Max. Tensile Strength, Short-Term	1350 N (300 lbf)

Fiber Count	Nominal Outer Diameter	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Min. Bend Radius Installation	Weight
1	6.6 mm x 3.0 mm (0.26 in x 0.12 in)	1350 N (300 lbf)	400 N (90 lbf)	63 mm (2.46 in)	17.9 kg/km (12 lb/1000 ft)

Chemical Characteristics	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

## Transmission Performance

Single-mode		
Typical Attenuation* (dB/km)	-	0.350.350.35
Fiber Name	Single-mode (OS2)	ClearCurve® LBL
Fiber Category	G.652.D	G.652.D
Fiber Code	E	J
Performance Option Code	01	01
Wavelengths (nm)	1310/1383/1550	1310/1383/1550
Maximum Attenuation (dB/km)	0.4/0.4/0.3	0.4/0.4/0.3

\* \*\*Typical attenuation values match the attenuation values listed in the optical fiber specifications. See [www.corning.com/opticalfiber](http://www.corning.com/opticalfiber) for Corning optical fiber specifications. Better attenuation performance options are available for some fiber and cable types. Contact Customer Care for additional fiber options.

CORNING

# ROC™ Drop Toneable Cables with FastAccess™ Technology

CORNING

## Notes



**Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA**

**800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)**

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks).

All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2017 Corning Optical Communications. All rights reserved.

CORNING