

Fiber Transition Housing FTH-602 Series



Features and Benefits

Multiple fiber termination options Supports up to six SC APC simplex adapters and fusion splices	
Slack storage Provides up to three meters of slack storage (dependent upon type of cable installed)	
Compact housing Small mounting footprint	
Weather-resistant housing design Fiber and connections protected for long life	
Supports 1 - 6 SC APC adapters Accommodates up to 6 drop connections	


Standards

Approval and Listings	UL-Listed to United States and Canadian safety standards
Design and Test Criteria	Tested to Telcordia standards
RoHS Compliant	

The Corning Fiber Transition Housing (FTH) provides an optical demarcation and interconnection point for fiber-to-the-premises (FTTP) applications. Mounted on the inside or outside of the structure, the FTH provides physical protection for the transition between provider and customer and facilitates system testing.

This compact housing provides termination, interconnection and slack fiber storage for up to six fibers. The integrated plastic backplate incorporates slack routing, splice holders, and grounding, while supporting up to six SC APC simplex adapters and fusion splices. Fiber entering and exiting the housing may be secured using the integrated strain relief lances. Slack fiber is held neatly and securely by the slack storage spool and routing guides.

The housing is molded from an engineering-grade thermoplastic selected to withstand harsh outdoor environments. The housing may be installed on a wall or secured to a vertical conduit. Unauthorized access is deterred by the security screw latch. For added security, a wire lock may be installed on the integrated locking hasp.



Fiber Transition Housing

FTH-602 Series



Specifications

Dimensions		
	Dimensions (HxWxD)	Weight
FTH-602 Series	21.6 cm x 19.8 cm x 6.4 cm (8.5 in x 7.8 in x 2.5 in)	3.4 kg (.75 lb)

Shipping Information			
	Minimum Order Quantity	Shipping Dimensions (HxWxD)	Shipping Weight
FTH-602 Series	10	41.9 cm x 38.1 cm x 27.3 cm (16.5 in x 15 in x 10.7 in)	5.0 kg (11 lb)

Ordering Information

FTH - 602 - 0

1

2

3

4

5

6

- 1

Select base configuration
2 = Standard base
- 3

Select ground configuration
0 = No ground post
1 = With ground post
- 5

Select security screw
0 = Standard 3/8-in hex screw
1 = Captive KS screw
- 2

Select adapter quantity and type
A = 1 SC APC simplex adapter
B = 2 SC APC simplex adapters
C = 6 SC APC simplex adapters
U = No adapter
- 4

Select fiber management configuration
0 = Backplate ONLY*
1 = Backplate with SC Bracket
- 6

Select cover**
0 = Cover, blank

*Fiber management guides and splice holder integrated into backplate
** Custom options available – Call Customer Care





Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.