

# ADSS Aramid Single Jacket Cable up to 100m span LT 2.3

CORNING

Corning single jacket ADSS cables for short span application are all-dielectric, self-supporting (ADSS) cables designed for easy and economical one-step installation in campus backbones with self-supporting installations where metallic messengers cannot be used. The loose tube design provides stable performance over a wide temperature range and is compatible with any telecommunications-grade optical fiber. The economical single-jacket design can span distances up to 100m in NESC light/medium conditions and 50m in NESC heavy conditions (see sag and tension chart for details). This cable incorporates innovative waterblocking materials, eliminating the need for traditional flooding compound and providing efficient and craft-friendly cable preparation. While the concentric, self-supporting cable design allows easy, one-step installation using standard hardware and installation methods, the SZ-stranded, loose tube design isolates optical fibres from installation and environmental rigors and facilitates mid-span access. These ADSS optical cables are available with HDPE jacket for installation in telecom applications.

## Features and Benefits

All dielectric self-supporting aerial cable

Non-metallic strength members over the cable core


Dry cable core by swellable elements

Single-layer stranded construction up to 144 fibers

Single-mode fibers fully compliant to standard ITU G.652 D (reduced OH- peak) showing low attenuation throughout the 1285 nm to 1625 nm wavelength range

Telcordia standard for fiber and loose tube coloring

Cable design according to CORNING standard



ADSS Aramid Single Jacket Cable up to 100m span LT 2.3

# ADSS Aramid Single Jacket Cable up to 100m span LT 2.3

CORNING

## Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Specifications

### General Specifications

Environment	Outdoor
Product Type	Self-Supporting, ADSS
Cable Type	Loose Tube

### Temperature Range

Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)

### Design Characteristics Cable

Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes
12 - 72	12	6	1 - 6
96	12	8	8
144	12	12	12

### Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
12 - 72	10.5 mm	158 mm	210 mm	2000 N/10 cm	4600 N	2770 N	84 kg/km

# ADSS Aramid Single Jacket Cable up to 100m span LT 2.3

CORNING

## Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
96	11.8 mm	177 mm	236 mm	2000 N/10 cm	5200 N	3120 N	107 kg/km
144	14.9 mm	227 mm	302 mm	2000 N/10 cm	5880 N	3600 N	165 kg/km



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil  
+55 21 3416 5150 • FAX: +55 21 2441 2037 • [www.corning.com/opcomm/csa](http://www.corning.com/opcomm/csa)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.