

# MiniXtend® Cable, LT, A-DQ(ZN)2Y

CORNING

Corning MiniXtend products are fiber optic stranded loose tube or central tube fully dielectric outdoor cable typically used in Long-Haul, Metro- or Access Networks when limited space is available.

With the dual layer tube design and low friction PE sheath MiniXtend cables are optimized for blowing and best used in mini or micro ducts.

The buffer tubes and fiber in each tube are color-coded for quick and easy identification. MiniXtend are available with Corning Single Mode Fiber SMF 28e+® & SMF 28e® ULTRA (ITU-G 652D) or bend improved ClearCurve® fibers (ITU-G 657).

## Features and Benefits

### Reduced outer cable diameter

High fiber density in microduct systems

### Compact and light

CapEx-optimized installations and upgrades

### Optimized cable stiffness

Long installation lengths

### Fully dielectric

No grounding required

### Color-coded tubes and fibers

Easy identification of tubes and

### SMF-28e+® according to ITU-T G.652.D

Transmission security, low attenuation and polarization mode dispersion



MiniXtend® Cable, LT, A-DQ(ZN)2Y

# MiniXtend® Cable, LT, A-DQ(ZN)2Y

CORNING

## Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Specifications

### General Specifications

Environment	Outdoor
Product Type	Dielectric
Cable Type	Stranded Loose Tube

### Temperature Range

Temperature Range, Storage	-30 °C - 70 °C (-22 °F - 158 °F)
Temperature Range, Installation	-5 °C - 40 °C (23 °F - 104 °F)
Temperature Range, Operation	-30 °C - 70 °C (-22 °F - 158 °F)

### Design Characteristics Cable

Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Buffer Tube Diameter
12 -	12	6	1 - 6	1.4 mm
96	12	8	8	1.4 mm
144	12	12	12	1.4 mm

### Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Cable Weight
12	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km

# MiniXtend® Cable, LT, A-DQ(ZN)2Y



## Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Cable Weight
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
24	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
36	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
48	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
60	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
72 -	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
96	6.3 mm	126 mm	94.5 mm	1000 N/10 cm	1000 N	35 kg/km
144	8 mm	160 mm	120 mm	1000 N/10 cm	1000 N	55 kg/km



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil  
 +55 21 3416 5150 • FAX: +55 21 2441 2037 • [www.corning.com/opcomm/csa](http://www.corning.com/opcomm/csa)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.