

ALTOS® Figure-8 Loose Tube, Gel-Free Cable

CORNING

Corning ALTOS® figure-8 gel-free cables are self-supporting aerial cables designed for easy and economical one-step installation. The loose tube design provides stable performance over a wide temperature range and is compatible with any telecommunications-grade optical fiber. The gel-free design is fully waterblocked using craft-friendly water-swellaable materials, making cable access simple and requiring no clean up. While the flexible, craft-friendly buffer tubes are easy to route in closures, the SZ-stranded, loose tube design isolates optical fibers from installation and environmental rigors and facilitates mid-span access. The figure-8 cable design allows easy, one-step installation, using standard hardware and installation methods. These cables have a medium density polyethylene jacket that is rugged, durable and easy to strip.

Features and Benefits

Gel-free waterblocking technology


Craft-friendly cable preparation

Polyethylene jacket

Rugged, durable and easy to strip (while providing superior protection against UV radiation, fungus, abrasion and other environmental factors)

Figure-8 cable design

Easy, one-step installation



ALTOS® Figure-8 Loose Tube, Gel-Free Cable

ALTOS® Figure-8 Loose Tube, Gel-Free Cable

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Environment	Outdoor
Product Type	Self-Supporting, Figure-8
Cable Type	Loose Tube

Temperature Range

Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Installation	-30 °C - 70 °C (-22 °F - 158 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)
Notes	Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Design Characteristics Cable

Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Buffer Tube Diameter
12 - 72	12	6	1 - 6	2.5 mm
96	12	8	8	2.5 mm
144	12	12	12	2.5 mm
192 - 216	12	18	16 - 18	2.5 mm
288	12	24	24	2.5 mm

ALTOS® Figure-8 Loose Tube, Gel-Free Cable

CORNING

Mechanical Characteristics Cable				
Fiber Count	Nominal Outer Diameter	Min. Bend Diameter Installation	Min. Bend Diameter Operation	Cable Weight
12	10.5 mm	316 mm	210 mm	297 kg/km
12	14.3 mm	430 mm	286 mm	396 kg/km
12	10.5 mm	316 mm	210 mm	297 kg/km
12	14.3 mm	430 mm	286 mm	396 kg/km
12	10.5 mm	316 mm	210 mm	297 kg/km
12	14.3 mm	430 mm	286 mm	396 kg/km
24	10.5 mm	316 mm	210 mm	297 kg/km
24	14.3 mm	430 mm	286 mm	396 kg/km
24	10.5 mm	316 mm	210 mm	297 kg/km
24	14.3 mm	430 mm	286 mm	396 kg/km
24	10.5 mm	316 mm	210 mm	297 kg/km
24	14.3 mm	430 mm	286 mm	396 kg/km
36	10.5 mm	316 mm	210 mm	297 kg/km
36	14.3 mm	430 mm	286 mm	396 kg/km
36	10.5 mm	316 mm	210 mm	297 kg/km
36	14.3 mm	430 mm	286 mm	396 kg/km
36	10.5 mm	316 mm	210 mm	297 kg/km
36	14.3 mm	430 mm	286 mm	396 kg/km
48	10.5 mm	316 mm	210 mm	297 kg/km
48	14.3 mm	430 mm	286 mm	396 kg/km
48	10.5 mm	316 mm	210 mm	297 kg/km
48	14.3 mm	430 mm	286 mm	396 kg/km
48	10.5 mm	316 mm	210 mm	297 kg/km
48	14.3 mm	430 mm	286 mm	396 kg/km
60	10.5 mm	316 mm	210 mm	297 kg/km
60	14.3 mm	430 mm	286 mm	396 kg/km
60	10.5 mm	316 mm	210 mm	297 kg/km
60	14.3 mm	430 mm	286 mm	396 kg/km

ALTOS® Figure-8 Loose Tube, Gel-Free Cable

CORNING

Mechanical Characteristics Cable				
Fiber Count	Nominal Outer Diameter	Min. Bend Diameter Installation	Min. Bend Diameter Operation	Cable Weight
60	10.5 mm	316 mm	210 mm	297 kg/km
60	14.3 mm	430 mm	286 mm	396 kg/km
72	10.5 mm	316 mm	210 mm	297 kg/km
72	14.3 mm	430 mm	286 mm	396 kg/km
72	10.5 mm	316 mm	210 mm	297 kg/km
72	14.3 mm	430 mm	286 mm	396 kg/km
72	10.5 mm	316 mm	210 mm	297 kg/km
72	14.3 mm	430 mm	286 mm	396 kg/km
96	12.2 mm	366 mm	244 mm	321 kg/km
96	16 mm	480 mm	320 mm	432 kg/km
96	12.2 mm	366 mm	244 mm	321 kg/km
96	16 mm	480 mm	320 mm	432 kg/km
96	12.2 mm	366 mm	244 mm	321 kg/km
96	16 mm	480 mm	320 mm	432 kg/km
144	15.8 mm	474 mm	316 mm	386 kg/km
144	19.7 mm	592 mm	394 mm	527 kg/km
144	15.8 mm	474 mm	316 mm	386 kg/km
144	19.7 mm	592 mm	394 mm	527 kg/km
144	15.8 mm	474 mm	316 mm	386 kg/km
144	19.7 mm	592 mm	394 mm	527 kg/km
192	16 mm	480 mm	320 mm	371 kg/km
192	19.9 mm	598 mm	398 mm	513 kg/km
192	16 mm	480 mm	320 mm	371 kg/km
192	19.9 mm	598 mm	398 mm	513 kg/km
192	16 mm	480 mm	320 mm	371 kg/km
192	19.9 mm	598 mm	398 mm	513 kg/km
216	16 mm	480 mm	320 mm	371 kg/km
216	19.9 mm	598 mm	398 mm	513 kg/km

ALTOS® Figure-8 Loose Tube, Gel-Free Cable

CORNING

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Diameter Installation	Min. Bend Diameter Operation	Cable Weight
216	16 mm	480 mm	320 mm	371 kg/km
216	19.9 mm	598 mm	398 mm	513 kg/km
216	16 mm	480 mm	320 mm	371 kg/km
216	19.9 mm	598 mm	398 mm	513 kg/km
288	18.2 mm	546 mm	364 mm	420 kg/km



1 Select fiber count.

Standard offerings:

012 048 096 216
024 060 144 288
036 072 192

**288-fibers only available in non-armored*

2 Select fiber code.

K = 62.5 µm multimode (OM1)
T = 50 µm multimode (OM2/OM3/OM4)
E = Single-mode (G.652.D)
L = Single-mode (G.652.D) SMF-28e+® LL
Z = Single-mode (G.652.D/ G.657.A1) SMF-28® Ultra
P = Single-mode (G.652) SMF-28® ULL
F = Single-mode (G.655) LEAF®

3 Defines cable type.

U = ALTOS® Loose Tube Cable with 2.5 mm buffer tubes

4 Select outer jacket.

A = Non-armored, Figure-8
B = Armored, Figure-8

5 Select fiber placement.

T = 12 fibers/buffer tube (standard)
6 = 6 fibers/buffer tube
See Note 1.

6 Select length markings.

3 = Markings in meters
4 = Markings in feet (standard)

7 Defines tensile strength.

1 = See specifications

8 Select performance option code.

30 = 62.5 µm multimode (OM1)
31 = 50 µm multimode (OM2)
80 = 50 µm multimode (OM3)
90 = 50 µm multimode (OM4)
01 = Single-mode (OS2) (Max. attenuation 0.4/0.4/0.3 dB/km)
00 = Single-mode (OS2) (Max. attenuation 0.35/0.35/0.25 dB/km)
22 = Single-mode (OS2) (Max. attenuation 0.34/0.34/0.22 dB/km)
19 = Single-mode (Ultra Low-Loss) (Max. attenuation 0.33/-/0.19 dB/km)
01 = Single-mode NZDSF* (Max. attenuation -/-/0.25 dB/km)

**Non-Zero Dispersion-Shifted Single-mode Fiber*

9 Defines cable type.

D = Gel-Free Cable

10 Defines special requirements.

20 = No special requirements

ALTOS® Figure-8 Loose Tube, Gel-Free Cable

The Corning logo consists of a solid blue square. Inside the square, the word "CORNING" is written in a white, serif, all-caps font, centered horizontally and vertically.

Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.