

CCH Module

CORNING

CCH cassettes enable fast field termination and easy modular management of connectorization within the housing.

A CCH termination and slack storage cassette option with no splice tray, suitable for use with field-installable connectors, is also available.

Each cassette is shipped with one rail for use with CCH-01U/2U/3U housings and two rails used with CCH-04U and the WCH-02P/4P/6P housings. Grommets and cable ties for strain relief, and protective braided tubing for incoming cable are also included. Splicing cassettes ship with 12 single fibre heat-shrink splice protectors.

Features and Benefits

Manage cable slack for a CCH panel in a modular footprint

Fast, easy and reliable initial routing, and quick, simple reaccess for moves, adds and changes (MACs)



CCH Module



Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	Meets ANSI/TIA/EIA-568A and 606

Specifications

General Specifications	
Application	Data Centre , Enterprise Networks
Mounting Type	Rack 19" , Rack 23" , Wall-mount
Product type	Rack-Mountable Hardware
Technology	Fusion Splice

Temperature Range	
Temperature range, operation	-40 °C - 70 °C

CCH Module



Design		
Part Number	Housing type	Panel or module type
CCH-CF	Rack-Mountable Hardware	CCH
CCH-CS-PST	Rack-Mountable Hardware	CCH



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2024 Corning Optical Communications. All rights reserved.