

# CCH Cassette

CORNING

CCH cassettes enable fast field termination and easy modular management of connectorization within the housing.

A CCH termination and slack storage cassette option with no splice tray, suitable for use with field-installable connectors, is also available.

Each cassette is shipped with one rail for use with CCH-01U/2U/3U housings and two rails used with CCH-04U and the WCH-02P/4P/6P housings. Grommets and cable ties for strain relief, and protective braided tubing for incoming cable are also included. Splicing cassettes ship with 12 single fiber heat-shrink splice protectors.

## Features and Benefits

### Manage cable slack for a CCH panel in a modular footprint

Fast, easy and reliable initial routing, and quick, simple reaccess for moves, adds and changes (MACs)



# CCH Cassette



Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	Meets ANSI/TIA/EIA-568A and 606

## Specifications

General Specifications	
Application	Data Center , Enterprise Networks
Mounting Type	Rack 19-in , Rack 23-in , Wall-Mountable
Product Type	Rack-Mountable Hardware
Technology	Fusion Splice

Temperature Range	
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)

# CCH Cassette



Design		
Part Number	Housing Type	Panel or Module Type
CCH-CF	Rack-Mountable Hardware	CCH
CCH-CS-PST	Rack-Mountable Hardware	CCH



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.