

# CCH Pigtailed Splice Cassette

CORNING

Closet Connector Housing (CCH) pigtailed splice cassettes enable faster field splicing and easy modular management of connectorization within the housing. They are preloaded and prerouted for quick fusion splicing of either individual or ribbon fiber pigtails, using the same space-saving platform as the standard CCH splice cassette.

The prerouted pigtailed cassettes reduce field labor by streamlining features and components to allow for efficiencies in the field. They are prepped with a 2 m pigtail assembly with all pre-existing CCH panel connector options. The pigtailed cassettes have colored 250  $\mu\text{m}$  for ease of splicing. They also enable strain relief to be pre-applied to the assemblies from the manufacturing facility. With the pigtailed cassette, individual splice tray or separate splice housings are eliminated, allowing splicing to be done away from the rack housing in more convenient workspaces. The modular design makes it easy to access the fiber in an individual cassette without disturbing the other fibers in the housing. Each cassette is shipped with the pigtailed CCH adapter panel of the customer's choice, one rail for use with CCH-01U/2U/3U housings, and two rails used with CCH-04U housings. Grommets and cable ties for additional strain relief and protective braided tubing for incoming cable are also included. Splicing cassettes ship with the appropriate quantity and type of heat-shrink splice protectors.

## Features and Benefits

### Manage cable slack for a CCH panel in a modular footprint

Fast, easy and reliable initial routing, and quick, simple reaccess for moves, adds and changes (MACs)

### Includes everything needed to convert a CCH housing for modular routing and/or splicing

Easy ordering and field installation

### Modular splice capability

Manage all splices inside the housing

### Colored 250 $\mu\text{m}$ at splice point

Easy to identify and prep colored 250  $\mu\text{m}$  for fast and easy splicing

### Pre-prepped splice cassette

Saves time in the field with a ready to splice product

### Broad operating temperature range (-40°C to +65°C)

Utility and flexibility



# CCH Pigtailed Splice Cassette



## Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	Meets ANSI/TIA/EIA-568A and 606, Tested in accordance with Telecordia GR-3125, UL1863 - Communication Circuit Accessories

## Specifications

### General Specifications

Access Type	Front access
Application	Data Center , Enterprise Networks
Product Type	Rack-Mountable Hardware
Technology	Fusion Splice

### Temperature Range

Temperature Range, Operation	-40 °C - 65 °C (-40 °F - 149 °F)
------------------------------	----------------------------------

### Design Adapter

Part Number	Housing Color	Adapter Type
CCH-CS06-A9-P00RE		LC Duplex
CCH-CS12-A8-P00KE		LC Duplex
CCH-CS12-A9-P00RE		LC Duplex
CCH-CS12-A9-P00RJ		LC Duplex
CCH-CS12-AE-P00RE		LC Duplex
CCH-CS12-B3-P00RE		LC Duplex
CCH-CS12-E4-P00QE		LC Duplex
CCH-CS12-E4-P00TE		LC Duplex
CCH-CS24-A9-P00RE		LC Duplex
CCH-CS24-A9-P00RJ		LC Duplex

# CCH Pigtailed Splice Cassette



Design Adapter		
Part Number	Housing Color	Adapter Type
CCH-CS24-AD-P00QE		LC Duplex
CCH-CS24-AD-P00TE		LC Duplex
CCH-CS24-AE-P00RE		LC Duplex
CCH-CS24-B3-P00RE		LC Duplex
CCH-CS24-B3-P00RJ		LC Duplex
CCH-CS24-D3-P00BE		LC Duplex
CCH-CS24-E4-P00QE		LC Duplex
CCH-CS24-E4-P00TE		LC Duplex
CCH-CS06-D9-P00RE		SC
CCH-CS12-59-P00RE		SC
CCH-CS12-6C-P00RE		SC
CCH-CS12-91-P00KJ		SC
CCH-CS12-D9-P00RE		SC
CCH-CS12-E7-P00TE		SC
CCH-CS12-G7-P00BE		SC
CCH-CS06-H3-P00TE		ST® compatible
CCH-CS12-5T-P00KE		ST® compatible
CCH-CS12-G5-P00BE		ST® compatible
CCH-CS12-G6-P00BE		ST® compatible
CCH-CS12-H3-P00TE		ST® compatible
CCH-CS24-AV-P00QE	Violet	LC Duplex
CCH-CS12-6T-P00RE		ST® compatible

Dimension			
Part Number	Height	Width	Depth
CCH-CS06-A9-P00RE	5 cm		
CCH-CS12-3C-P00RE	5 cm		

# CCH Pigtailed Splice Cassette



Dimension			
Part Number	Height	Width	Depth
CCH-CS12-5T-P00KE	5 cm		
CCH-CS12-A8-P00KE	5 cm		
CCH-CS12-A9-P00RJ	5 cm		
CCH-CS24-A9-P00RJ	5 cm		
CCH-CS24-B3-P00RJ	5 cm		
CCH-CS12-AE-P00RE	35 mm (1.38 in)	162 mm (6.38 in)	200 mm (7.87 in)
CCH-CS24-E4-P00QE	35 mm (1.38 in)	162 mm (6.38 in)	200 mm (7.87 in)

## Shipping Information

Part Number	Height	Width	Depth
CCH-CS06-A9-P00RE			
CCH-CS06-D9-P00RE			
CCH-CS06-H3-P00TE			
CCH-CS12-3C-P00RE			
CCH-CS12-59-P00RE			
CCH-CS12-5T-P00KE			
CCH-CS12-6C-P00RE			
CCH-CS12-6T-P00RE			
CCH-CS12-91-P00KJ			
CCH-CS12-A8-P00KE			
CCH-CS12-A9-P00RE			
CCH-CS12-A9-P00RJ			
CCH-CS12-AE-P00RE			
CCH-CS12-B3-P00RE			
CCH-CS12-D9-P00RE			
CCH-CS12-E4-P00QE			
CCH-CS12-E4-P00TE			

# CCH Pigtailed Splice Cassette

CORNING

Part Number	Height	Width	Depth
CCH-CS12-E7-P00TE			
CCH-CS12-G5-P00BE			
CCH-CS12-G6-P00BE			
CCH-CS12-G7-P00BE			
CCH-CS12-H3-P00TE			
CCH-CS24-A9-P00RE			
CCH-CS24-A9-P00RJ			
CCH-CS24-AD-P00QE			
CCH-CS24-AD-P00TE			
CCH-CS24-AE-P00RE			
CCH-CS24-AV-P00QE			
CCH-CS24-B3-P00RE			
CCH-CS24-B3-P00RJ			
CCH-CS24-D3-P00BE			
CCH-CS24-E4-P00QE	50 mm (1.97 in)	203 mm (7.99 in)	368 mm (14.49 in)
CCH-CS24-E4-P00TE			

CCH-CS   -   - P00

**1** Select fiber count.

- 06 = 6 fibers
- 08 = 8 fibers
- 12 = 12 fibers
- 16 = 16 fibers
- 24 = 24 fibers

See Note 1.

**3** Select fiber type.

- K = 62.5 μm multimode (OM1)
- B = 50 μm multimode (OM2)
- T = 50 μm multimode (OM3)
- Q = 50 μm multimode (OM4)
- R = Single-mode (OS2)

**4** Select splicing type.

- E = Single-fiber splicing
- J = Ribbon splicing (only for fiber counts of 12 or 24)

**2** Select adapter code (see Adapter/Connector Code Options table).

See Note 2.

# CCH Pigtailed Splice Cassette

The CORNING logo is displayed in white, uppercase letters within a solid blue rectangular box.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.