

Gabinete de empalmes (CSH)

CORNING

El gabinete de empalme (CSH) de Corning proporciona almacenamiento y protección de empalmes de fibra en bandejas accesibles individualmente. Los gabinetes se utilizan en racks de equipos o gabinetes de equipos, de 48 cm (19 pulg.) o 58 cm (23 pulg.), y en el empalme de transición entre el cable clasificado para exteriores y el cable clasificado como riser / plenum en la entrada de un edificio. El empalme flexible se logra cuando el CSH se usa junto con un gabinete de montaje en rack. El CSH está disponible en modelos de 3 espacios de rack de altura y 5 espacios de rack. Un estante deslizante brinda acceso a las bandejas de empalme y las guías de enrutamiento. El gabinete tiene paneles de acceso extraíbles en la parte superior e inferior trasera para la entrada del pigtail vertical desde los gabinetes CLSSC-03U o CLSSC-04U y puertas delanteras y traseras con cerradura (con los kits de cerradura opcionales).

Características y beneficios

Abrazadera de cable universal

Alivio de tensión de cable

Diseño de lado abierto

Salida de fibra fácil

Montaje en proyección o empotrado

Varias opciones de instalación

Várias portas de entrada de cabo com ilhó

Opções de instalação e proteção



Gabinete de empalmes (CSH)

Gabinete de empalmes (CSH)

CORNING

Specifications

Especificaciones generales

Tipo de producto	Carcasas
------------------	----------

Design

Part Number	Tipo de carcasa	Opciones de bandejas de empalme
CSH-03U	Cajas de empalme de armario (CSH)	Hasta 12 categorías 2R, 2S o 2M
CSH-03U-F	Cajas de empalme de armario (CSH)	Hasta 7 categorías 4R, 4S o 4A
CSH-05U	Cajas de empalme de armario (CSH)	Hasta 22 categorías 2R, 2S o 2M
CSH-05U-F	Cajas de empalme de armario (CSH)	Hasta 14 categorías 2R, 4S o 4A

Design Adapter

Part Number	Color de la carcasa
CSH-03U	Negro
CSH-03U-F	Negro
CSH-05U	Negro
CSH-05U-F	Negro

Dimension

Part Number	Altura	Ancho	Profundidad
CSH-03U	133 mm	432 mm	305 mm
CSH-03U-F	133 mm	432 mm	305 mm
CSH-05U	222 mm	152,4 mm	305 mm
CSH-05U-F	222 mm	152,4 mm	305 mm

Ordering Information

Part Number	Contenido del embalaje	Unidades por entrega
CSH-03U	Closet Splice Housing 3U; Installation guide; 4 blank panels; Installation Kit; UCC Kit; #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Spiral Wrap, Tie Wraps	1/1
CSH-03U-F	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1
CSH-05U	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1
CSH-05U-F	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1

Gabinete de empalmes (CSH)

The Corning logo consists of the word "CORNING" in white, uppercase, sans-serif font, centered within a solid blue square.

Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

Una lista completa de las marcas registradas de Corning Comunicacoes Opticas se encuentra disponible en www.corning.com/opcomm/trademarks. Todas las otras marcas comerciales son propiedad de sus respectivos dueños. Corning Comunicacoes Opticas posee la certificación ISO 9001. © 2026 Corning Comunicacoes Opticas. Todos los derechos reservados.