

# Closet Splice Housing (CSH)

CORNING

Corning closet splice housing (CSH) provides storage and protection of fiber splices in individually accessible trays. The housings are used in equipment racks or equipment cabinets, 19 in (48 cm) or 23 in (58 cm), and in the transition splice between outdoor-rated and riser/plenum-rated cable at a building entrance. Pigtail splicing is accomplished when the CSH is used in conjunction with a rack-mount housing. The CSH is available in 3-rack-space tall and 5-rack-space models. A sliding shelf provides access to splice trays and routing guides. The housing has top and bottom rear removable access panels for vertical pigtail entry from the CLSSC-03U or CLSSC-04U housings and lockable front and rear doors (with the optional lock kits).

## Features and Benefits

### Universal cable clamp

Cable strain-relief

### Open-side design

Easy fiber egress

### Projection- or flush-mountable

Various installation options

### Multiple grommeted cable entry ports

Installation options and protection



Closet Splice Housing (CSH)

# Closet Splice Housing (CSH)



## Specifications

### General Specifications

Product Type	Housings
--------------	----------

### Design

Part Number	Housing Type	Splice Tray Options
CSH-03U	Closet Splice Housing (CSH)	Up to 12 category 2R, 2S or 2M
CSH-03U-F	Closet Splice Housing (CSH)	Up to 7 category 4R, 4S or 4A
CSH-05U	Closet Splice Housing (CSH)	Up to 22 category 2R, 2S or 2M
CSH-05U-F	Closet Splice Housing (CSH)	Up to 14 category 2R, 4S or 4A

### Design Adapter

Part Number	Housing Color
CSH-03U	Black
CSH-03U-F	Black
CSH-05U	Black
CSH-05U-F	Black

### Dimension

Part Number	Height	Width	Depth
CSH-03U	133 mm	432 mm	305 mm
CSH-03U-F	133 mm	432 mm	305 mm
CSH-05U	222 mm	152.4 mm	305 mm
CSH-05U-F	222 mm	152.4 mm	305 mm

# Closet Splice Housing (CSH)



## Ordering Information

Part Number	Package Contents	Units per Delivery
CSH-03U	Closet Splice Housing 3U; Installation guide; 4 blank panels; Installation Kit; UCC Kit; #12-24 and #10-32 mounting screws, Cage Nut Mounting Kit, Spiral Wrap, Tie Wraps	1/1
CSH-03U-F	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1
CSH-05U	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1
CSH-05U-F	Housing with 19-in mounting ears; splice tray stacker with 24-in hook-and-loop strap; flip card label; installation guide; label, unit ID; 12 tie wraps, 1/8 x 4, white; spiral wrap, 3 ft; set of 19-in flush-mount ears; set of 23-in mounting ears; 8 mounting screws, #10-32; 4 mounting screws, #12-24; 4 mounting screws, M6; 2 Universal Cable Clamp (UCC) Kits, with 5 cable inserts; bracket for mounting UCC clamp; 2 central member strain-relief clamp kits; 2 sandpapers, 80 grit, 1-in wide and 2 nylon wing nuts, #6-32	1/1

# Closet Splice Housing (CSH)

The CORNING logo is a dark blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil  
+55 21 3416 5150 • FAX: +55 21 2441 2037 • [www.corning.com/opcomm/csa](http://www.corning.com/opcomm/csa)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.