


EDGE™ Field-Term Cassette



EDGE™ Field-term Cassettes provide the interface between the trunk cable and the LC duplex jumpers that connect directly into the electronics. The LC duplex adapters feature hinged VFL-compatible shutters that move up and out of the way when the connector is inserted. The field-term cassette contains no pigtail, but allows for field termination of bulk cables directly into the rear side of the LC duplex adapters using UniCams or anaerobic connectors. This cassette may also be used with preterminated LC trunks.



EDGE™ Field-Term Cassette



Specifications

General Specifications	
Application	Data Center
Product Type	Cassettes
Splice option	Yes

Design				
Part Number	Housing Type	Fiber Count	Adapter Type Front	Adapter Color Front
EDGE-CS12-AD	EDGE™	12	Shuttered LC	Aqua
EDGE-CS12-AF	EDGE™	12	Shuttered LC	Green
EDGE-CS12-AE	EDGE™	12	Shuttered LC	Blue

Design				
Part Number	Polish	Number of Splice Trays	Panel or Module Type	Splice Tray Type
EDGE-CS12-AD		1	EDGE™	EDGE™ splice field-term cassette
EDGE-CS12-AF	APC	1	EDGE™	EDGE™ splice field-term cassette
EDGE-CS12-AE	UPC	1	EDGE™	EDGE™ splice field-term cassette

Design Adapter				
Part Number	Insert	Housing Material	Adapter Type	Housing Color
EDGE-CS12-AD	Ceramic	Composite	LC Duplex Shuttered	Aqua
EDGE-CS12-AE	Ceramic	Composite	LC Duplex Shuttered	Blue
EDGE-CS12-AF	Ceramic	Composite	LC Duplex Shuttered	Green

EDGE™ Field-Term Cassette



Dimension			
Part Number	Height	Depth	Width
EDGE-CS12-AD	12 mm	176 mm	90 mm
EDGE-CS12-AF	12 mm	176 mm	90 mm
EDGE-CS12-AE	25 mm	135 mm	247 mm

Ordering Information

Part Number	Units per Delivery
EDGE-CS12-AD	1/1
EDGE-CS12-AE	1/1
EDGE-CS12-AF	1/1

Shipping Information

Part Number	Height	Width	Depth
EDGE-CS12-AD	25 mm	247 mm	135 mm
EDGE-CS12-AE	25 mm	247 mm	135 mm
EDGE-CS12-AF	25 mm	247 mm	135 mm



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.