

EDGE™ Module

The logo consists of a solid blue square with the word "CORNING" written in white, uppercase, serif font centered within it.

EDGE™ low-loss modules provide an interface between the MTP® connector on an MTP trunk and the LC duplex jumpers that connect directly to the electronics. These modules feature VFL-compatible LC shuttered adapters and are manufactured with Corning® CleanAdvantage™ Technology, an innovative factory cleaning and sealing process that minimizes debris transfer and allows you to connect with confidence.

All EDGE modules meet RoHS standards and are ideal for data center, local area network (LAN), and storage area network (SAN) applications.

Specifications

General Specifications

Product Type	Panels and Modules
Application	Data Center LAN/SAN

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Housing Type	Modules
--------------	---------

Ordering Information

Part Number	Product Description	Units Per Delivery
ECM-RM12-04-89G	12F, Bend-improved Single-mode (OS2), LC Duplex, UPC	Piece
ECM-RM12-05-93Q	12F, 50 µm multimode (OM4)	Piece
ECM-RM12-05-93T	12F, 50 µm multimode (OM3)	Piece
ECM-RM12-18-89G	12F, Bend-improved (OS2), LC Duplex, APC, MTP® PC, Connector (pinned), single-mode	Piece
ECM-UM12-04-89G	12 F, LC Duplex to MTP® Connector, Bend-improved single-mode (OS2)	Piece
ECM-UM12-04-89G-Z	12 Fiber, OS2, LC Duplex to MTP (pinned), Universal Polarity, 4-pack	Piece
ECM-UM12-05-93Q	12 F, 50 µm (OM4), LC Duplex, PC, MTP® PC, Connector (pinned), multimode	Piece
ECM-UM12-05-93Q-VI	12 F, LC Duplex, PC to MTP® Connector, 50 µm multimode (OM4)	Piece
ECM-UM12-05-93Q-Z	12 Fiber, OM4, LC Duplex to MTP (pinned), Universal Polarity, 4-pack	Piece

EDGE™ Module



Part Number	Product Description	Units Per Delivery
ECM-UM12-05-93T	12 F, 50 µm (OM3), LC Duplex, PC, MTP® PC, Connector (pinned), multimode	Piece
ECM-UM12-18-89G	12F, Bend-improved Single-mode (OS2)	Piece



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.