

FREEDM® One Tight-Buffered Cable, Riser

CORNING

Corning FREEDM® One riser cables are flame-retardant, UV-resistant, indoor/outdoor cables designed for aerial and duct applications with no need for a transition splice when entering the building. The tight-buffered construction facilitates easier termination for low-fiber-count applications in the local area network (LAN) and eliminates the need for fan-out kits. The design features TIA-598 color-coded 900 µm buffered fibers for easy identification, consistent stripping and direct termination. The small diameter and bend radius of the cable allow for easy installation in space-constrained areas while the innovative waterblocking technology is ideal for outside plant (OSP) applications. The all-dielectric cable construction requires no grounding or bonding, and the UV-resistant, flame-retardant jacket is rugged, durable and easy to strip. Note: This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

Features and Benefits

Waterblocking technology

OSP (outdoor) applications

Small diameter and bend radius

Easy installation in space-constrained areas

Color-coded fibers


Quick and easy identification

All-dielectric construction

Requires no grounding or bonding

UV-resistant, flame-retardant jacket

Rugged, durable and easy to strip



FREEDM® One Tight-Buffered Cable, Riser

FREEDM® One Tight-Buffered Cable, Riser

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Environment	Indoor/Outdoor
Product Type	Dielectric
Cable Type	Tight-Buffered
Flame Rating	Riser (OFNR)

Temperature Range

Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Installation	-10 °C - 60 °C (14 °F - 140 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)

Design Characteristics Cable

Fiber Count
2 - 24

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
2	5.2 mm	78 mm	52 mm	675 N	200 N	20.8 kg/km
2	5.2 mm	78 mm	52 mm	675 N	200 N	21.25 kg/km

FREEDM® One Tight-Buffered Cable, Riser

CORNING

Mechanical Characteristics Cable						
Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
4	5.5 mm	82.5 mm	55 mm	675 N	200 N	24.42 kg/km
4	5.5 mm	82.5 mm	55 mm	675 N	200 N	24 kg/km
4	5.5 mm	82.5 mm	55 mm	675 N	200 N	24.42 kg/km
6	5.5 mm	82.5 mm	55 mm	675 N	200 N	26.45 kg/km
6	5.5 mm	82.5 mm	55 mm	675 N	200 N	26 kg/km
6	5.5 mm	82.5 mm	55 mm	675 N	200 N	26.45 kg/km
6	5.3 mm	82.5 mm	27 mm	675 N	200 N	26 kg/km
6	5.5 mm	82.5 mm	55 mm	675 N	200 N	26.45 kg/km
12	6.5 mm	97.5 mm	65 mm	675 N	200 N	35.9 kg/km
12	6.5 mm	97.5 mm	65 mm	675 N	200 N	36.55 kg/km
12	6.5 mm	97.5 mm	65 mm	675 N	200 N	35.9 kg/km
12	6.5 mm	97.5 mm	65 mm	675 N	200 N	36.55 kg/km
12	6.5 mm	97.5 mm	65 mm	675 N	200 N	35.9 kg/km
18	7.4 mm	111 mm	74 mm	1350 N	400 N	51.16 kg/km
18	7.4 mm	111 mm	74 mm	1350 N	400 N	50.5 kg/km
18	7.4 mm	111 mm	74 mm	1350 N	400 N	51.16 kg/km
18	7.4 mm	111 mm	74 mm	1350 N	400 N	50.5 kg/km
24	8 mm	120 mm	80 mm	1350 N	400 N	59.78 kg/km

FREEDM® One Tight-Buffered Cable, Riser

CORNING

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
24	8 mm	120 mm	80 mm	1350 N	400 N	59.1 kg/km
24	8 mm	120 mm	80 mm	1350 N	400 N	59.78 kg/km

8
F
-
3
1
1

-
2
9

1 Select fiber count.
Standard offerings:
006 012 018 024

2 Select fiber code.
K = 62.5 µm multimode (OM1)
T = 50 µm multimode (OM2/OM3/OM4/OM4+)
E = Single-mode (OS2) SMF-28e+®
Z = Single-mode (OS2) SMF-28® Ultra fiber

3 Defines cable type.
8 = FREEDM® One cable

4 Defines outer jacket.
F = Indoor/outdoor riser

5 Defines fiber placement.
3 = Standard for FREEDM One riser cable

6 Defines length markings.
1 = Markings in ft (standard) for single-layer design.

7 Defines tensile strength.
1 = See Specifications.

8 Select performance option code.
30 = 62.5 µm multimode (OM1)
31 = 50 µm multimode (OM2)
80 = 50 µm multimode (OM3)
90 = 50 µm multimode (OM4)
91 = 50 µm multimode (OM4+)
31 = Single-mode (OS2)
(Max. attenuation .65 / .65 / 0.5 dB/km)

9 Defines cable type.
- = FREEDM® One Cable

10 Defines special requirements.
29 = No special requirements



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.