

Everon® Copper Datacom V250 Shielded

CORNING

Our Cat.6 copper interconnect products work together to provide an easy-to-use solution for deploying high-speed connections throughout a building. The RJ45 jack is a key component in this system. These RJ45 jacks have been certified by an independent test laboratory to hardware certification. Each jack component is able to terminate to any certified Cat.6 TIA, ISO/IEC and EN standards for hardware performance, confirmed by independent laboratory certifications. The jack's unique three cable entry points help make installation simple. The traditional one-click design enables an easy, tool-less termination on Cat. 6 shielded twisted pair cables, meeting industry performance standards.



Everon® Copper Datacom V250 Shielded

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Category	6
----------	---

Environmental Conditions

Temperature Range, Operation	-10 °C - 60 °C
------------------------------	----------------

Design

Part Number	Insulation diameter max.	Jack Type	Color	Housing Material	Conductor
XF500006010	1.6 mm	RJ45 - 8/8	White	Metal	24 - 22 AWG
XF500006028	1.6 mm	RJ45 - 8/8	White	Metal	24 - 22 AWG

Mechanical Characteristics

Part Number	Contact surface
XF500006010	Gold, 1.27 µm
XF500006028	Gold, 1.27 µm



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2024 Corning Optical Communications. All rights reserved.