

EDGE8® MTP® Extender Trunk

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Os troncos extensores EDGE8 MTP fornecem distância adicional para o backbone da solução EDGE8. Com um conector MTP sem pinos em uma extremidade do cabo, um conector MTP com pinos na outra extremidade e uma polaridade TIA-568 Tipo A, esses troncos são projetados para fazer a interface com um módulo universal das soluções EDGE8 e um tronco EDGE8 MTP. Todos os troncos são fornecidos com cliques de alívio de tensão que permitem a instalação sem ferramentas nas caixas dos sistemas das soluções EDGE8. Os troncos extensores MTP são usados com mais frequência em uma Área de Distribuição de Zona (ZDA).

Características e benefícios

Snap-in strain-relief clips

Provide easier cable management

Small outer diameter

Improves cable tray fill ratio and allows for imported airflow

Low-loss connectivity

Enables system design flexibility

Bend-improved fibre

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables

Tecnologia CleanAdvantage™ da Corning® e tampa contra poeira otimizada

Elimina a necessidade de delimitação e limpeza antes da conexão de campo inicial

EDGE8® MTP® Extender Trunk

CORNING

Especificações

Normas

RoHS

Livre de substâncias perigosas de acordo com RoHS 2011/65/EU

Ordering Information

Part Number	Product Description	Units Per Delivery
GE5E608QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E608TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E616QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E616TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E624QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E624TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E632QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece

EDGE8® MTP® Extender Trunk

CORNING

Part Number	Product Description	Units Per Delivery
GE5E632TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E648QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E648TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E672QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E672TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E696QLZDCX030M	50 µm multimode (OM4), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE5E696TLZDCX030M	50 µm multimode (OM3), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E808GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 8F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E816GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 16F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece

EDGE8® MTP® Extender Trunk

CORNING

Part Number	Product Description	Units Per Delivery
GE7E824GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 24F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E832GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 32F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E848GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 48F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E872GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 72F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece
GE7E896GLZDCX030M	Bend-improved Single-mode (OS2), 8F MTP (pinned) Connector to 8F MTP (non-pinned) Connector, 96F, with 33/60 in legs, tool-less pulling grip one side, 100 ft	Piece



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

Uma lista completa das marcas registrada da Corning Comunicações Ópticas está disponível em www.corning.com/opcomm/trademarks. Todas as outras marcas são de propriedade de seus respectivos proprietários. Corning Comunicações Ópticas é certificada ISO 9001. ©2025 Corning Comunicações Ópticas. Todos os direitos reservados.