

FREEDM® LST™ Loose Tube, Gel-Free Cable, Plenum

CORNING

Corning FREEDM® loose tube gel-free plenum cables are flame-retardant, indoor/outdoor, plenum-rated cables suitable for installation in interbuilding and intrabuilding backbones in aerial, duct and riser or plenum applications. The loose tube design offers mechanical ruggedness and environmental durability while the all-dielectric cable construction requires no grounding or bonding. The water-swallowable yarn eliminates the need for gel-filling compound and allows more efficient and craft-friendly cable preparation. The 250 µm color-coded fibers allow quick and easy identification during installation.

The flexible, flame-retardant outer jacket is UV-resistant and enables direct exposure to sunlight. Interlocking armor is available for special applications requiring additional mechanical durability. The plenum rating of this cable eliminates the need to transition splice when entering the building and minimizes routing restrictions once inside the building. Meeting the requirements of the National Electrical Code® (NEC®) Article 770, the cables are also OFNP and FT-6 listed.

Features and Benefits

Gel-free waterblocking technology

Craft-friendly cable preparation

Loose tube design

Stable performance and compatibility with all common fiber types

Color-coded fibers


Quick and easy identification

All-dielectric construction

Requires no grounding or bonding

All-dielectric strength member

Mechanical durability



FREEDM® LST™ Loose Tube, Gel-Free Cable, Plenum

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Cable Type	Loose Tube
Flame Rating	Plenum (OFNP)

Temperature Range

Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)

Design Characteristics Cable

Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes
6	6	1	1
12	12	1	1

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
6 - 12	9 mm (0.35 in)	135 mm (5.31 in)	90 mm (3.54 in)	1350 N (303.49 lbf)	400 N (89.92 lbf)	6098 kg/km (4097.67 lb/1000 ft)
12	9 mm (0.35 in)	135 mm (5.31 in)	90 mm (3.54 in)	1350 N (303.49 lbf)	400 N (89.92 lbf)	52.5 kg/km (35.28 lb/1000 ft)

FREEDM® LST™ Loose Tube, Gel-Free Cable, Plenum

CORNING

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
12	9 mm (0.35 in)	135 mm (5.31 in)	90 mm (3.54 in)	1350 N (303.49 lbf)	400 N (89.92 lbf)	6098 kg/km (4097.67 lb/1000 ft)

Transmission Performance

Multimode

Fiber Category	OM1	OM2	OM3	OM4	OM4 Extended Distance
Fiber Code	K	T	T	T	T
Performance Option Code	30	31	80	90	91
Fiber Core Diameter	62.5 µm	50 µm	50 µm	50 µm	50 µm
Wavelengths	850 nm / 1300 nm	850 nm / 1300 nm	850 nm / 1300 nm	850 nm / 1300 nm	850 nm / 1300 nm
Maximum Attenuation	3.4 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km
Serial 1 Gigabit Ethernet	300 MHz*km / 550 MHz*km	750 MHz*km / 500 MHz*km	1000 MHz*km / 600 MHz*km	1100 MHz*km / 600 MHz*km	1100 MHz*km / 600 MHz*km
Serial 10 Gigabit Ethernet	33 MHz*km / -	150 MHz*km / -	300 MHz*km / -	550 MHz*km / -	600 MHz*km / -
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 500 MHz*km	700 MHz*km / 500 MHz*km	1500 MHz*km / 500 MHz*km	3500 MHz*km / 500 MHz*km	3500 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -	950 MHz*km / -	2000 MHz*km / -	4700 MHz*km / -	5350 MHz*km / -

FREEDM® LST™ Loose Tube, Gel-Free Cable, Plenum

CORNING

Transmission Performance

Single-mode

Fiber Name	Single-mode (OS2) - SMF-28® Ultra fiber
Performance Option Code	01
Fiber Category	G.652.D - G.652.D/G.657.A1
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Code	E - Z
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km

□ □ □ □ S P - T 4 1 □ □ D 2 0
1 2 3 4 5 6 7 8 9 10

1 Select fiber count.

Standard offerings:

002 008 018
004 012 024

2 Select fiber code.

K = 62.5 µm multimode (OM1)
T = 50 µm multimode
(OM2/OM3/OM4/OM4+)
E = Single-mode (OS2)
SMF-28e+®
Z = Single-mode (OS2)
SMF-28® Ultra fiber

3 Defines cable type.

S = LST cable

4 Defines outer jacket.

P = Indoor/outdoor plenum

5 Defines fiber placement.

T = 12 fibers/buffer tube
(standard)

6 Defines length markings.

4 = Markings in ft (standard)

7 Defines tensile strength.

1 = See specifications

8 Select performance option code.

30 = 62.5 µm multimode (OM1)
31 = 50 µm multimode (OM2)
80 = 50 µm multimode (OM3)
90 = 50 µm multimode (OM4)
91 = 50 µm multimode (OM4+)
01 = Single-mode (OS2)

(Maximum attenuation 0.4/0.4/0.3 dB/km)

9 Defines cable type.

D = Gel-free cable

10 Defines special requirements.

20 = No special requirements



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.