

Our Cat.5e copper interconnect products work together to provide an easy-to-use solution for deploying high-speed connections throughout a building. The RJ45 jack is a key component in this system. The jack's two cable entry points help make installation simple. The traditional one-click design enables an easy, tool-less termination on cables, meeting industry performance standards.

Features and Benefits

Tool-less jack

Easy and quick to install - reliable connection
The conductors are wired in a single operation

Two cable entry points

Less cable bending required - better compliance with minimum bend radius
Enables a wide range of cable routing options
Easy to use in tight spaces

Reusable

Jack can be reused even after wiring mistake

No untwisting of pairs before termination

Minimized stripping length - limited pair untwist - pairs kept together, no wire guide required

Clip-in mounting

Designed to fit many other accessories

Accepts solid and stranded conductors

Enables "jack-to-plug" cables to be manufactured using stranded conductors

Integral shutter

No additional shuttering required on faceplates

Everon® Copper Datacom E100 Flex



Specifications

Mechanical Specifications	
Solid Wire Diameter	5 mm to 65 mm

Ordering Information

Part Number	Product Description	Units Per Delivery
FQ100021333	OCK5EFV, E100F, RJ45 Vol, Cat5e, BP480, White	Piece
FQ100029310	OCK5EF8, E100FWH, RJ45 Vol, Cat5e, Bag/8, White	Piece



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.