

Everon® Copper Datacom V250 Shielded

CORNING

Our Cat.6 copper interconnect products work together to provide an easy-to-use solution for deploying high-speed connections throughout a building. The RJ45 jack is a key component in this system. These RJ45 jacks have been certified by an independent test laboratory to hardware certification. Each jack component is able to terminate to any certified Cat.6 TIA, ISO/IEC and EN standards for hardware performance, confirmed by independent laboratory certifications. The jack's unique three cable entry points help make installation simple. The traditional one-click design enables an easy, tool-less termination on Cat. 6 shielded twisted pair cables, meeting industry performance standards.



Everon® Copper Datacom V250 Shielded



Specifications

Mechanical Specifications	
Solid Wire Diameter	5 mm to 65 mm

Ordering Information

Part Number	Product Description	Units Per Delivery
XF500006010	VOLOCK6SH8, V250S, RJ45 Vol, Cat6, Bag/8, white	Piece
XF500006028	VOLOCK6SHV, V250S, RJ45 Vol, Cat6, BP480, white	Piece



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.