

MiniXtend® HD Cable

CORNING

Corning® MiniXtend® HD cables are high-density micro cables that are up to 60 percent smaller and up to 70 percent lighter than standard loose tube cables and up to 20 percent smaller than standard micro cables. MiniXtend HD cables have an SZ-stranded loose tube construction and provide high fiber counts in limited duct space in long-haul, metro and access networks.

With a dual-layer tube design and a low-friction PE sheath, MiniXtend HD cables are optimized for blowing into microducts.

Both the buffer tubes and the fibers contained within are color-coded for quick and easy identification.

MiniXtend HD cables feature Corning® SMF-28® Ultra 200 single-mode fiber (ITU-T G.652.D and ITU-T G.657.A1): the industry's first 200 micron fiber with a 9.2 micron Mode-Field Diameter (MFD).

Features and Benefits

Reduced outer cable diameter

High fiber density in microduct systems

Compact and light

CapEx-optimized installations and upgrades

Optimized cable stiffness

Long installation lengths

Fully dielectric


No grounding required

Color-coded tubes and fibers

Easy identification of tubes & fibers

SMF-28® Ultra 200 fiber

ITU-T G.652.D and G.657.A1-compliant 200 micron single-mode fiber with a 9.2 micron MFD, low loss and enhanced bend performance



MiniXtend® HD Cable

CORNING

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Specifications

General Specifications	
Environment	Outdoor
Product Type	Dielectric
Cable Type	Stranded Loose Tube

Temperature Range	
Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Installation	-15 °C - 60 °C (5 °F - 140 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)

Design Characteristics Cable				
Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Buffer Tube Diameter
144	24	6	6	1.7 mm (0.07 in)
192	24	8	8	1.7 mm (0.07 in)
216	24	9	9	1.7 mm (0.07 in)
288	24	12	12	1.7 mm (0.07 in)

Transmission Performance

Single-mode	
Fiber Category	G.652.D/G.657.A1
Fiber Name	SMF-28® Ultra 200 Optical Fiber

MiniXtend® HD Cable

CORNING

Single-mode	
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Code	Z
Maximum Attenuation	0.34 dB/km / 0.34 dB/km / 0.20 dB/km



1 Select fiber count.
144 192 216 288

2 Defines fiber type.
Z = Single-mode (OS2)
SMF-28® Ultra fiber

3 Defines cable type.
H = MiniXtend HD Cable
(in combination with 9: HA)

4 Defines outer jacket.
4 = Single-jacket (all-dielectric)

5 Defines fiber placement.
Y = 24 fibers/buffer tube

6 Select length markings.
3 = Markings in meters
4 = Markings in feet

7 Defines tensile strength.
1 = Standard

8 Defines performance option code.
40 = Single-mode (OS2)
Max. attenuation 0.34/0.34/0.20 dB/km

9 Defines cable type.
A = MiniXtend HD Cable

10 Defines special requirements.
20 = Standard construction



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.