

# LSZH Ribbon Gel-Filled Cable

CORNING

Corning LSZH ribbon cables are designed for indoor/outdoor application where limited-smoke and zero-halogen requirements exist. These cables are organized with 12-fiber ribbons inside a central tube that are surrounded by dielectric strength members and a specially formulated flame-retardant outer jacket. The 12-fiber ribbons have readily identifiable ribbon ID numbers and fiber colors that allow for easy access to individual fibers. The precise fiber and ribbon geometries result in excellent mass splicing yields. The cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables. Contact Customer Care at 1-800-743-2675 to order other color options.

## Features and Benefits

### Precise fiber and ribbon geometries

Excellent mass splicing yields

### Ribbon ID numbers and fiber colors


Easily identifiable

### Available with interlocking armor

Additional mechanical durability

### Common installations

Outdoor aerial and duct



# LSZH Ribbon Gel-Filled Cable



## Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Specifications

### General Specifications

Environment	Indoor/Outdoor
Product Type	Distribution
Cable Type	Ribbon
Flame Rating	LSZH (OFNR-LS)

### Temperature Range

Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Installation	-30 °C - 60 °C (-22 °F - 140 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)

### Design Characteristics Cable

Fiber Count	Buffer Tube Diameter	Ribbons per Tube	Fibers per Ribbon
12	81 mm (3.19 in)	1	12
24	81 mm (3.19 in)	2	12
36	81 mm (3.19 in)	3	12
48	81 mm (3.19 in)	4	12
72	81 mm (3.19 in)	6	12
96	81 mm (3.19 in)	8	12
144	11 mm (0.43 in)	12	12
192	11 mm (0.43 in)	16	12
216	11 mm (0.43 in)	18	12

# LSZH Ribbon Gel-Filled Cable



## Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
12 - 36	12 mm (0.47 in)	146 mm (5.75 in)	97 mm (3.82 in)	400 N (89.92 lbf)	400 N (89.92 lbf)	147.71 kg/km (99.26 lb/1000 ft)
48 - 72	13.4 mm (0.53 in)	186 mm (7.32 in)	124 mm (4.88 in)	400 N (89.92 lbf)	400 N (89.92 lbf)	174.19 kg/km (117.05 lb/1000 ft)
96	14 mm (0.55 in)	228 mm (8.98 in)	152 mm (5.98 in)	400 N (89.92 lbf)	400 N (89.92 lbf)	196 kg/km (131.71 lb/1000 ft)
144 - 216	17 mm (0.67 in)	228 mm (8.98 in)	152 mm (5.98 in)	400 N (89.92 lbf)	400 N (89.92 lbf)	295.3 kg/km (198.43 lb/1000 ft)

## Transmission Performance

### Multimode

Fiber Category	OM1	OM2	OM3	OM4	OM4 Extended Distance
Fiber Code	K	T	T	T	T
Performance Option Code	30	31	80	90	91
Fiber Core Diameter	62.5 $\mu$ m	50 $\mu$ m	50 $\mu$ m	50 $\mu$ m	50 $\mu$ m
Wavelengths	850 nm / 1300 nm	850 nm / 1300 nm	850 nm / 1300 nm	850 nm / 1300 nm	850 nm / 1300 nm
Maximum Attenuation	3.4 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km	3.0 dB/km / 1.0 dB/km
Serial 1 Gigabit Ethernet	300 m / 550 m	750 m / 600 m	1000 m / 600 m	1000 m / 600 m	1100 m / 600 m
Serial 10 Gigabit Ethernet	33 m / -	150 m / -	300 m / -	550 m / -	600 m / -

# LSZH Ribbon Gel-Filled Cable



Multimode					
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 500 MHz*km	700 MHz*km / 500 MHz*km	1500 MHz*km / - 500 MHz*km	3500 MHz*km / 500 MHz*km	
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -	950 MHz*km / -	950 MHz*km / -	4700 MHz*km / -	5350 MHz*km / -

## Transmission Performance

Single-mode	
Fiber Name	Single-mode (OS2)
Performance Option Code	01
Fiber Category	OS2
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Code	E
Maximum Attenuation	0.4 dB/km / 0.4 dB/km / 0.3 dB/km

# LSZH Ribbon Gel-Filled Cable

CORNING

□ □ □ □ C Z - 1 4 1 □ □ - 2 0  
 1 2 3 4 5 6 7 8 9 10

**1** Select fiber count.

Standard offerings:

012 036 072 144  
 024 048 096 216

**2** Select fiber code.

K = 62.5 μm multimode (OM1)  
 T = 50 μm multimode,  
 (OM2/OM3/OM4/OM4+)  
 E = Single-mode (OS2)  
 SMF-28e+®  
 Z = Single-mode (OS2)  
 SMF-28® Ultra fiber

**3** Defines cable type.

C = Ribbon Cable

**4** Defines outer jacket.

Z = LSZH

**5** Defines fiber placement.

1 = 12 fibers/buffer tube  
 (standard)

**6** Defines length markings.

4 = Markings in ft (standard)

**7** Defines tensile strength.

1 = See Specifications

**8** Select performance option code.

30 = 62.5 μm multimode (OM1)  
 31 = 50 μm multimode (OM2)  
 80 = 50 μm multimode (OM3)  
 90 = 50 μm multimode (OM4)  
 91 = 50 μm multimode (OM4+)  
 01 = Single-mode (OS2)  
 (Max. attenuation 0.4/0.4/0.3 dB/km)

**9** Defines cable type.

- = Gel-Filled Ribbon Cable

**10** Defines special manufacturing code.

20 = Standard



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.