

Eigenschaften und Vorteile

Enables direct connection to optical power meters for in-field testing

Environmentally sealed connector housing permits rapid connection to external flush-mounted bulkhead adapters on terminals or closures. Terminal or closure entry is not required for drop cable installation.

Temperature Range

Temperaturbereich, Lagerung	-40 °C - 70 °C
Temperaturbereich, Betrieb	-40 °C - 70 °C

Design

Part Number	Faseranzahl
434401E31AJ003M	1
435801E31AJ003M	1
435801G31AJ003M	1
436101E31AJ003M	1

Optical Characteristics

Faserkategorie	OS2
Fasertyp	Single-mode (OS2) / 250 µm
Fasercode	E
Wellenlänge	1310 nm / 1383 nm / 1550 nm
Maximale Dämpfung	0,4 dB/km / 0,4 dB/km / 0,4 dB/km



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Deutschland
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

Eine komplette Liste der Markenzeichen von Corning Optical Communications finden Sie unter www.corning.com/opcomm/emea/trademarks. Corning Optical Communications ist ISO 9001 und ISO 14001 zertifiziert. © 2026 Corning Optical Communications. Alle Rechte vorbehalten