

ROC™ Drop Dielectric Cable with FastAccess® Technology

CORNING

ROC™ Drop Dielectric Cables with FastAccess® Technology provides a more efficient, craft-friendly cable preparation unparalleled by traditional flat drop cables. The innovative FastAccess Technology design simplifies removal of the cable jacket resulting in up to 55 percent faster fiber access time. This technology improves ease of use because no special tools are needed. The cable design is backwards compatible for easy connectorization or splicing.

Optimized for both field and factory termination processes, the compact design allows for easier handling in the field, reduces slack storage requirements and improves transportation and storage costs. The dielectric version eliminates any bonding and grounding requirements. ROC Drop Dielectric Cables with FastAccess Technology are also available in preconnectorized assemblies.

Features and Benefits

FastAccess technology

Saves time and reduces complexity

No special tools

Ease of use

Backwards compatible

Enables fast connectorization and splicing

Innovative cable design


Retains industry standard hardware compatibility such as wedge clamps

Dielectric

Eliminates bonding and grounding requirements

Compact, robust design

Meets industry standards and eliminates installation complexity



ROC™ Drop Dielectric Cable with FastAccess® Technology

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Environment	Outdoor
Product Type	Self-Supporting
Cable Type	Single Tube
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	A-V (2ZN) 2Y

Temperature Range

Temperature Range, Storage	-40 °C - 70 °C
Temperature Range, Installation	-5 °C - 50 °C
Temperature Range, Operation	-40 °C - 70 °C

Design Characteristics Cable

Fiber Count	Fibers per Tube
1	1

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Cable Weight
1	5.4 mmx 3 mm	60 mm	1500 N/10 cm	1350 N	400 N	15.2 kg/km

ROC™ Drop Dielectric Cable with FastAccess® Technology

CORNING

Transmission Performance

Single-mode	
Fiber Name	ClearCurve® LBL - ClearCurve® ZBL
Performance Option Code	22
Fiber Category	OS2
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Code	J - U
Maximum Attenuation	0.36 dB/km / 0.36 dB/km / 0.22 dB/km



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.