

Not all preterminated cable manufacturers are the same

## 14 questions you should ask your manufacturer about preterminated trunk cables

- 1. Do the preterminated trunks have a minimum bend radius of five times the cable's outside diameter?
- 2. Do the preterminated trunks meet the application requirements of the National Electric Code® (NEC® Article 770) OFNP and FT-6 listed for plenum?
- 3. Do the preterminated trunks meet the connector performance specifications of TIA/EIA-568-C.3, Optical Fiber Cabling Components Standard (normative) Annex A?
- 4. Do the preterminated trunks meet the optical standards per TIA/EIA-455-204 and IEC 60793-1-41 for intermediate-performance laser-based systems (up to 1 Gb/s)?
- 5. Do the preterminated trunks meet the optical standards per TIA/EIA-455-220 and IEC 60793-1-49 for high-performance laser-based systems (up to 10 Gb/s)?
- 6. Do the preterminated trunks meet the optical fiber cable transmission performance parameters according to TIA-568-C.3?
- 7. Have the preterminated trunks been tested to remain operational at a temperature range of -10°C to +60°C?

- 8. Is the preterminated trunk manufacturer ISO 9001 registered?
- 9. Are the preterminated trunk furcation plugs designed to allow for securing the trunks inside or outside the connector housing?
- 10. Do the furcation plugs of the preterminated trunks consist of an outer shell that is filled with epoxy encapsulate?
- 11. Are the preterminated trunks manufactured with all RoHS-compliant components?
- 12. Are the preterminated trunks manufactured with ultra-bendable fiber to meet fiber performance standards per TIA-568-C.3? Multimode 2.8 dB at 850  $\mu$ m/1.0 dB at 1300  $\mu$ m; single-mode 0.4 dB at 1310  $\mu$ m/0.3 dB at 1550  $\mu$ m?
- 13. Are the pulling grips of the preterminated trunks manufactured to withstand a maximum pulling force of 100 lb?
- 14. Are the preterminated trunks shipped on reels that are 100 percent recyclable?

## Corning says **YES** to all of these questions.