



## Features and Benefits

**Compact design with small dimensions**

**Electrical spring contact to top hat rail (bonding, grounding)**

**Inclined design with labeling field and dust protection flap**

**Tool-less and fast installation on top hat rails**

**Tool-less installation of module**

**Top hat rail adapter light grey, RAL 7035**

**Flame retardant, fire Class UL94 V-0**

**Temperature range: -20°C to +70°C**

**Recyclable and free of heavy metal**



Part Number: WAXISE-V0103-C001

## Specifications

Environmental Conditions	
Temperature Range, Installation	-20 °C to 70 °C

Design	
Color	Gray
Number of Ports	1

General Specifications	
Product Category	Core Product
Halogen-free	Yes

Ordering Information	
Weight	16
Units per Delivery	1/1



Standards	
Flame Retardance	Flame retardant, fire Class UL94 V-0
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

## Ordering Information

Part Number	WAXISE-V0103-C001
Product Description	<p>The FutureCom™ Industrial top hat rail adapter is suitable for installation on 35 mm top hat rails.</p> <p>It provides a potential equalization spring and, due to its modular design, allows a free configuration of each single port with FutureCom copper modules as well as LANscape® fiber optic modules.</p>

**Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA • 800-743-2675  
 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)**

**A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks).**

**All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.**

**© 2016 Corning Optical Communications. All rights reserved.**