



Jumper in a Box (JIAB)

Part Number Configurators

Part Number Configurators

SC and LC Simplex | Jumper in a Box

-
SR
2
-

1

2

3

4

5

1 Select connector code.

Single-mode
 0202 = LC UPC
 2222 = LC APC
 2244 = LC APC/SC APC
 4444 = SC APC
 5858 = SC UPC

2 Defines cable and fiber type.
 SR2 = Simplex R 1.6 mm,
 Single-mode (OS2)

3 Select quantity. Quantity per box is determined by length.

P = Plastic Box
 P70 = 1–5 m or 1–16 ft
 P50 = 6–10 m or 17–35 ft
 P40 = 11–15 m or 36–52 ft
 P30 = 16–20 m or 53–66 ft

R = Refill
 R70 = 1–5 m or 1–16 ft
 R50 = 6–10 m or 17–35 ft
 R40 = 11–15 m or 36–52 ft
 R30 = 16–20 m or 53–66 ft

4 Select jumper length*.
 01–20 m
 01–65 ft
* Maximum length is 20 m or 65 ft.

5 Select unit of measure.
 F = Feet
 M = Meters

SC Duplex | Jumper in a Box

-

-

1

2

3

4

5

1 Select connector code.

Multimode Duplex
 5757 = SC PC

Single-mode Duplex
 7272 = SC UPC

2 Defines cable and fiber type.
 ZR4 = 2.0 mm Zipcord R MM OM4
 ZR3 = 2.0 mm Zipcord R MM OM3
 ZR2 = 2.0 mm Zipcord R SM OS2
 ZR1 = 2.0 mm Zipcord R MM OM1

3 Select quantity. Quantity per box is determined by length.

P = Plastic Box
 P60 = 1–2 m or 1–7 ft
 P50 = 3–4 m or 8–13 ft
 P40 = 5–6 m or 14–20 ft
 P35 = 7–8 m or 21–26 ft
 P30 = 9–10 m or 27–33 ft

R = Refill
 R60 = 1–2 m or 1–7 ft
 R50 = 3–4 m or 8–13 ft
 R40 = 5–6 m or 14–20 ft
 R35 = 7–8 m or 21–26 ft
 R30 = 9–10 m or 27–33 ft

4 Select jumper length*.
 01–10 m
 01–33 ft
* Maximum length is 10 m or 33 ft.

5 Select unit of measure.
 F = Feet
 M = Meters

Part Number Configurators

LC Duplex | Jumper in a Box

-

-

-

1

2

3

4

5

1 Select connector code.

Multimode Duplex
0505 = LC PC

Single-mode Duplex
0404 = LC UPC

3 Select quantity. Quantity per box is determined by length.

P = Plastic Box
P70 = 1 m or 3 ft
P60 = 2 m or 4–7 ft
P50 = 3–5 m or 8–16 ft
P40 = 6–8 m or 17–26 ft
P30 = 9–10 m or 27–33 ft

R = Refill
R70 = 1 m or 3 ft
R60 = 2 m or 4–7 ft
R50 = 3–5 m or 8–16 ft
R40 = 6–8 m or 17–26 ft
R30 = 9–10 m or 27–33 ft

4 Select jumper length*.
01–10 m
01–33 ft
* Maximum length is 10 m or 33 ft.

2 Defines cable and fiber type.
ZR4 = 2.0 mm Zipcord R MM OM4
ZR3 = 2.0 mm Zipcord R MM OM3
ZR2 = 2.0 mm Zipcord R SM OS2
ZR1 = 2.0 mm Zipcord R MM OM1

5 Select unit of measure.
F = Feet
M = Meters

LC Duplex Reverse Polarity Uniboot | Jumper in a Box

-

-

-

1

2

3

4

5

1 Select connector code.

Multimode Duplex
7979 = LC PC Uniboot

Single-mode Duplex
7878 = LC UPC Uniboot

3 Select quantity. Quantity per box is determined by length.

P = Plastic Box
P70 = 1–5 m or 1–16 ft
P50 = 6–10 m or 17–35 ft
P40 = 11–15 m or 36–52 ft
P30 = 16–20 m or 53–66 ft

R = Refill
R70 = 1–5 m or 1–16 ft
R50 = 6–10 m or 17–35 ft
R40 = 11–15 m or 36–52 ft
R30 = 16–20 m or 53–66 ft


4 Select jumper length*.
01–20 m
01–65 ft
* Maximum length is 20 m or 65 ft.

2 Defines cable and fiber type.
OM4 = DFX 250 R MM OM4
OM3 = DFX 250 R MM OM3
OS2 = DFX 250 R SM OS2, Corning® ClearCurve®

5 Select unit of measure.
F = Feet
M = Meters



Let's connect!



CO/HE Solutions

corning.com/isp

Hybrid Fiber Coax Solutions

corning.com/mso

Community Broadband Solutions

corning.com/community-broadband

FTTH Solutions

corning.com/ftth

CORNING

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA • 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019, 2024 Corning Optical Communications. All rights reserved. CRR-1187-AEN / June 2024