

Pharma Vial Tubing CORNING

Dimensional Specification

All requirements and criteria applicable to dimensional characteristics are summarized in the table below. For details see "Tubing Specifications — Definition and Supporting Information".

Sample size according to ISO 2859 unless specified otherwise. Reference volume = 1 pallet

Requirement	Definition Item	Unit Defect Spec / Limit		AQL	Remarks	
Outer Diameter	OD _{avg}	The individual tubing sample is defective if there is a 60 mm section out of tolerance over the entire length.		Cumulative AQL of 0.25	Standard tolerances see page 5	
Circularity	NCR = 1/2 (OD _{max} – OD _{min})	OD range		Limit for NCR		
		< 25.0 mm		0.4% of OD _{nom}		
		25.0 – 35.0 mm		0.6% of OD _{nom}		
		> 35.0 mm 0		0.8% of OD _{nom}		
Wall Thickness	WT _{avg}	The individual tubing sample is defective if there is a 60 mm section out of tolerance over the entire length.			See page 5	
Wall Siding (Lop)	$WS = WT_{max} - WT_{min}$	Maximum siding value is 6% of the nominal wall thickness.				
Length	L _{max}	The individual tubing sample is defective if overall length is out of tolerance.				Standard tolerances see page 5
Bow	B _{center}	Defective if greater than 0.7 mm				Over a 1000 mm length
Square Cut	SC	OD < 25.0 Not to exceed 8% OD _{nom}		2.5		
		OD ≥ 25	Not to	exceed 2.0 mm		
		Useable end	Not to	exceed 0.8 mm		Only upon request
Glazing	GID _{max} as a percentage of OD _{nom}	Light		edges rounded with num turn in	0.65	May be specified differently on the two tube ends
		Medium 80–90% of OD _{nom}			two tube ellus	
		Heavy 65–75% of OD _{nom}				
Vent Hole	Dimensions	Not to be smaller than 1 mm, not exceeding 4 mm		1.0		
	Missing vent hole			1.0		

Notes

OD, WT, NCR, WS, measurements are to be taken on the usable length of the tube. Any local deviation in each that correspinds with knots or stones or other dimensionally relevant visual characteristic shall not be evaluated with respect to the dimensional specification, but rather according to the relevant visual specification.



Visual Quality Specifications

Requirements applicable to visual characteristics are summarized in the tables below. For details see "Tubing Specifications — Definition and Supporting Information".

Sample size according to ISO 2859 unless specified otherwise. Reference volume = 1 pallet

Requirement	Detail / Parameter	Individual Defect Definition				AQL / Criteria	Remarks
Airlines	Single	L > 150 mm or W > 0.08 mm				0.4	Defective if any airline in the tube exceeds limit length or width
	Aggregate length of airlines	Aggregate length of airlines L > 15 mm and W > 0.02 mm				≤ 6.5%	Of tested tubing length. Apply to both open and closed airlines.
Inclusions	Size (S) / count	Tube is defective if inclusion count per 5 kg tubing exceeds the following limits.					Inclusions up to 0.5 mm are not a defect.
		S ≥ 0.8 0 allowed per 5 kg			kg		AQL not specified. 5 kg tubing must be controlled
		S ≥ 0.5 Max 5 allowed per 5 kg			per 5 kg		
Glass Particles	Size (S) / count	Tube is defective if the following maximum allowed numbers of glass particles is exceeded in any class.			f glass	0.4	Glass particles up to 0.2 mm are not considered
		OD range [mi	m]	S ≥ 0.5	S ≥ 0.2		Cumulative size classes apply.
		OD < 15.0		0	5		арріу.
				0	8		
				10			
Cracks	Surface cracks	Any size, any length				0.025	End cracks ≤ 2 mm are not considered defects, 20 mm from each side not considered
	End cracks	L > 2.0 mm				0.65	
Scratches Coated tubes	Longitudinal	W > 0.1 mm AND L > 30 mm				1.0	20 mm from each side not considered Only for bundlepack
Coated tubes	Aggregate length	W > 0.1 mm AND AL > 150 mm					
	Circular	W > 0.1 mm AND Arc > 1/2 circumference					only for buildicpack
Scratches Uncoated tubes	Longitudinal	W > 0.2 mm AND L > 100 mm				1.0	20 mm from each side not considered (applies also for all tubes in sleeve pack)
Uncoated tubes	Aggregate length	W > 0.2 mm AND AL > 300 mm			1		
	Circular	W > 0.2 mm AND Arc > 1 circumference					
Surface Impurities	Outer surface	If impurities cannot be easily removed > 1.0 mm			removed	0.1	
	Inner surface	> 0.5 mm				0.1	

Pharma Vial Tubing CORNING

Other Requirements

Requirements for other characteristics are summarized in the tables below.

Requirement	Detail	Defect Specification	AQL	Remarks
Residual Stress	Longitudinal	Stress > 4.0 MPa	2.5	
	Circular	Stress > 4.5 MPa	ess > 4.5 MPa	
Mix-Up	Delivered articles is not uniform in the pallet	E.g. different glass types, dimensions, coating level, different identification (label)	Not permissible	
Identification	Wrong data	Incorrect identification data on the bundle label. E.g. declared dimensions, bundle weight, pallet weight	Not permissible	Test unit = 1 bundle
	Missing bundle label	Missing bundle labels	Not permissible	
Certificates	Wrong or missing data	Missing certificate or pallet label	Not permissible	
Туре І	EP 3.2.1 – Test B, USP660 – Glass grain test	> 0.1 ml of 0.02 M HCl per 1 g of glass	Not permissible	JP 7.01 Test For glass containers for Injections upon request



Standard Dimensions

Length standard tolerance is -0.0 +4.0 mm.

The following table defines the standard OD and WT tolerances depending on the OD and WT nominal values.

OD range (mm)	WT range (mm)	OD tol (mm)	WT tol (mm)
9.00 – 14.99	0.60 - 0.99	0.12	0.03
	1.00 – 1.19	0.14	0.03
	1.20 – 1.39	0.15	0.04
	1.40 – 1.60	0.19	0.05
15 – 17.99	0.70 – 0.89	0.14	0.03
	0.90 – 1.09	0.14	0.04
	1.10 – 1.39	0.18	0.04
	1.40 – 1.60	0.20	0.05
18 – 19.99	0.70 – 0.89	0.18	0.03
	0.90 – 1.09	0.19	0.04
	1.10 – 1.39	0.20	0.04
	1.40 – 1.60	0.23	0.05
20.0 – 24.99	0.70 – 1.09	0.19	0.04
	1.10 – 1.39	0.20	0.05
	1.40 – 1.60	0.23	0.05
25.0 – 29.99	0.75 – 1.09	0.19	0.04
	1.10 – 1.39	0.20	0.05
	1.40 – 1.60	0.25	0.06
30.0 – 34.99	1.00 – 1.39	0.24	0.05
	1.40 – 1.60	0.30	0.06
35.0 – 36.00	1.20 – 1.39	0.40	0.08
	1.40 – 1.60	0.40	0.08

CORNING

Europe

Corning Pharmaceutical Glass S.p.A. Via Montelungo, 4 56122 Pisa, Italy

Phone: +39 050 56 66 11

E-mail: cpginfoeu@corning.com

North America

Corning Pharmaceutical Glass, LLC 563 Crystal Avenue Vineland, NJ 08360-3257 USA

Phone: +1 856 794 7100

E-mail: cpginfousa@corning.com

www.corning.com