

# Corning® SMF-28e+® Optical Fiber

## Product Information



Built on Corning's solid foundation of quality and proven performance, Corning® SMF-28e+® optical fiber is a reliable and widely deployed fiber. Optimized for access and metro networks, SMF-28e+ fiber is compliant with Recommendation ITU-T G.652.D and features a 9.2 μm mode field diameter for compatibility with legacy networks.

### Optical Specifications

#### Maximum Attenuation

Wavelength (nm)	Maximum Value* (dB/km)
1310	≤ 0.35
1383**	≤ 0.35
1490	≤ 0.24
1550	≤ 0.20
1625	≤ 0.23

\*Alternate attenuation offerings available upon request.  
 \*\*Attenuation values at this wavelength represent post-hydrogen aging performance.

#### Attenuation vs. Wavelength

Range (nm)	Ref. λ (nm)	Max. α Difference (dB/km)
1285 – 1330	1310	0.03
1525 – 1575	1550	0.02

The attenuation in a given wavelength range does not exceed the attenuation of the reference wavelength (λ) by more than the value α.

#### Macrobend Loss

Mandrel Radius (mm)	Number of Turns	Wavelength (nm)	Induced Attenuation* (dB)
16	1	1550	≤ 0.03
30	100	1625	≤ 0.1

Specifications for options compliant with ITU-T G.657.A1:

15	10	1550	≤ 0.25
15	10	1625	≤ 1.0
10	1	1550	≤ 0.75
10	1	1625	≤ 1.5

\*The induced attenuation due to fiber wrapped around a mandrel of a specified radius.

#### Point Discontinuity

Wavelength (nm)	Point Discontinuity (dB)
1310	≤ 0.05
1550	≤ 0.05

#### Cable Cutoff Wavelength (λ<sub>cc</sub>)

λ<sub>cc</sub> ≤ 1260 nm

#### Mode Field Diameter

Wavelength (nm)	Mode Field Diameter (μm)
1310	9.2 ± 0.4
1550	10.4 ± 0.5

#### Dispersion

Wavelength (nm)	Dispersion Value [ps/(nm·km)]
1550	≤ 18
1625	≤ 22

Zero Dispersion Wavelength (λ<sub>0</sub>): 1304 nm ≤ λ<sub>0</sub> ≤ 1324 nm  
 Zero Dispersion Slope (S<sub>0</sub>): ≤ 0.092 ps/(nm<sup>2</sup>·km)

#### Polarization Mode Dispersion (PMD)

	Value (ps/√km)
PMD Link Design Value	≤ 0.06*
Maximum Individual Fiber PMD	≤ 0.1

\*Complies with ITU-T G.650-2 Appendix IV, (m = 20, Q = 0.01%), August 2015.

The PMD link design value is a term used to describe the PMD of concatenated lengths of fiber (also known as PMD<sub>0</sub>). This value represents a statistical upper limit for total link PMD. Individual PMD values may change when fiber is cabled.

#### ColorPro® Identification Technology

SMF-28e+ fiber is also available in colored and ringmarked variants, enabled by ColorPro® identification technology. Corning fibers with ColorPro® identification technology deliver better efficiency in cable manufacturing, simplify inventory management, and leverage an enhanced fiber product offering.

#### How to Order

Contact your sales representative, or call the Optical Fiber Customer Service Department:  
 Ph: 1-607-248-2000 (U.S./Can.)  
 +44-1244-525-320 (Europe)  
 Email: cofic@corning.com  
 Please specify the fiber type, attenuation, and quantity when ordering.



## Dimensional Specifications

### Glass Geometry

Fiber Curl	$\geq 4.0$ m radius of curvature
Cladding Diameter	$125.0 \pm 0.7$ $\mu\text{m}$
Core-Clad Concentricity	$\leq 0.5$ $\mu\text{m}$
Cladding Non-Circularity	$\leq 0.7\%$

### Coating Geometry

Coating Diameter	$242 \pm 5$ $\mu\text{m}$
Coating-Cladding Concentricity	$< 12$ $\mu\text{m}$

\*A  $200 \pm 5$   $\mu\text{m}$  coating diameter option compliant with ITU-T G.657.A1 is available upon request, coating-cladding concentricity  $< 10$   $\mu\text{m}$ .

## Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm, and 1625 nm (dB/km)
Temperature Dependence	$-60^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ *	$\leq 0.05$
Temperature Humidity Cycling	$-10^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ up to 98% RH	$\leq 0.05$
Water Immersion	$23^{\circ}\text{C} \pm 2^{\circ}\text{C}$	$\leq 0.05$
Heat Aging	$85^{\circ}\text{C} \pm 2^{\circ}\text{C}$	$\leq 0.05$
Damp Heat	$85^{\circ}\text{C}$ at 85% RH	$\leq 0.05$

Operating Temperature Range:  $-60^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$

\*Reference temperature =  $+23^{\circ}\text{C}$

## Mechanical Specifications

### Proof Test

The entire fiber length is subjected to a tensile stress  $\geq 100$  kpsi (0.69 GPa). Higher proof test levels are available.

### Length

Fiber lengths available up to 50.4 km/spool.

## Performance Characterizations

Characterized parameters are typical values.

Core Diameter	8.2 $\mu\text{m}$
Numerical Aperture	0.14 NA is measured at the one percent power level of a one-dimensional far-field scan at 1310 nm.
Effective Group Index of Refraction ( $n_{\text{eff}}$ )	1310 nm: 1.4674 1550 nm: 1.4679
Fatigue Resistance Parameter ( $n_d$ )	20
Coating Strip Force	Dry: 0.6 lbs. (3 N) Wet, 14-day room temperature: 0.6 lbs. (3 N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB