



# Corning Iris® Glass

## Product Information

As the industry moves toward sleeker, more slender designs, it needs a way to produce thinner displays. Corning Iris® Glass is a glass light-guide plate (LGP) for edge-lit LCD displays. Due to its intrinsic rigidity and dimensional stability, it outperforms the incumbent technology - plastic - and allows set manufacturers to significantly reduce set thickness and create displays with slimmer bezels.

Corning's latest composition also features outstanding transmission and minimal color shift, delivering bright displays with rich, accurate colors.

## Dimensions and Product Specifications

Dimensions	Available up to 70" diagonal
Dimensional Tolerance	± 0.5 mm
Thicknesses	0.7 mm, 1.1 mm, 1.5 mm, 1.8mm, 2.0 mm
Thickness Tolerance	< 0.1 mm
Edge	Ra ≤ 0.2 μm
Surface Criteria	No visible defect using 600 Lux


## Properties

Density	2.4 g/cm <sup>3</sup>
Young's Modulus	> 68 GPa
Refractive index (633 nm)	1.49
Moisture Absorption	< 0.001%
CTE	< 1080 <sup>-7</sup> / °C

## Thermal

Temperature (°C)	Specific Heat (J/g-K)	Thermal Diffusivity (cm <sup>2</sup> /sec)	Thermal Conductivity (cm <sup>2</sup> /sec)
50	0.89	0.0056	0.012
100	0.95	0.0056	0.012

# Transmittance



Spectral Transmission Over 500 mm Path Length  
(Fresnel reflections removed)

# CORNING

Email: [display@corning.com](mailto:display@corning.com)

Web: [www.corning.com/worldwide/en/products/display-glass/products/corning-iris-glass](http://www.corning.com/worldwide/en/products/display-glass/products/corning-iris-glass)

© 2019 Corning Incorporated 2019\_All Rights reserved

Corning is a registered trademark of Corning Incorporated. Corning, N.Y. USA

Issued: February 2019