

Glass designation :

UV DG 37

Code

80188

Color :

Gray-Blue

Filter category :

Medium

Application :

**100 % UV absorbing glass suited for general or special purpose Tinted Glass.
Gray blue color with excellent color rendition. Pass all national and international standards for traffic signal recognition.**

PHYSICAL PROPERTIES

Density : **2.48** g/cm³
Linear Exp. Coef. : **68.1** 10⁻⁷ / °C
Viscosity : **Soft. Pt 649** °C
Ann. Pt 493 °C
Strain Pt 456 °C

REFRACTIVE INDEX

Line		λ (nm)	Value
F'	Cadmium	480.0	1.52974
F	Hydrogen	486.1	1.52923
e	Mercury	546.1	1.52533
d	Helium	587.6	1.52320
C'	Cadmium	643.8	1.52108
C	Hydrogen	656.3	1.52068
Abbe Number	ve		60.7
	vd		61.2

TRANSMISSION PROPERTIES (2 mm)

VISIBLE 380 - 780 nm

Luminous transmission factor **37.0%**
Transmission category
ISO 8980-3 **2**

ULTRAVIOLET

UV - B tλ(max) 280 - 315 nm **< 0.1 %**
t(avg) 280 - 315 nm **< 0.1 %**
Solar UV-B transmission factor **< 0.1 %**

UV - A tλ(max) 315 - 350 nm **< 0.1 %**
t(moy) 315 - 380 nm **< 0.1 %**
Solar UV-A transmission factor **< 0.1 %**

BLUE LIGHT 380 - 500 nm
Blue light transmission factor **43%**

TRAFFIC SIGNAL RECOGNITION

ISO 14889 **Pass**
ANSI Z80-3 **Pass**
AS 1067.1 **Pass**


COATING & TEMPERING

(See also notes below)

Vacuum coating **YES**
Chemical tempering **YES**
Air tempering **NO**

t(%)

Transmission Curve: UV DG 37 Code 80188



Glass designation :

UV DG 37

Code

80188

Color :

Gray-Blue

Filter category :

Medium

Application :

100 % UV absorbing glass suited for general or special purpose Tinted Glass. Gray blue color with excellent color rendition. Pass all national and international standards for traffic signal recognition.

Chemtempering :

Recommended bath and cycle (no preheating nor postcooling) :

Bath :	Potassium Nitrate	99.5 %	(Sodium nitrate 0,5% max)	Time :	16 Hr
	Silicic Acid	0.5 %		θ °C :	410 °C

Air tempering :

Do not air temper this glass.

Coatings :

Vacuum coatings for coloring, antireflexion or mirror are possible.

Special attention is required to achieve an appropriate surface quality, including in the selection of the cleaning products used after surfacing and before coating. The use of strong acidic solution should be avoided.

Compatible Bariums :

This glass can not be used to manufacture fused multifocal lenses.

There is no compatible bariums to be fused with this glass

Properties according to ISO 14889

ISO 14889 Chapter 4.3.1

Physiological compatibility

The above glass products are not known to be physiologically incompatible, nor known to create a significant number of allergic reactions, when the lenses made out of these materials are used as intended by the manufacturer

ISO 14889 Chapter 4.3.2

Flammability

The above glass products are not flammable, and when tested as described in chapter 5.1 of ISO 14889, there is no continued combustion after withdrawal of the test rod.