

Transwell® Large Format Inserts

Effectively grow large amounts of tissue or cells in a more natural environment

CORNING

Now there is a way to grow a large amount of tissue or cells in a more *in vivo*-like environment with the Transwell large format insert and tray, exclusively available from Corning Life Sciences.

The large format Transwell insert is a sterile, ready-to-use permeable support device that features a 0.4 µm polycarbonate track-etched membrane. The larger format insert and tray retains all of the unique design elements of smaller format Transwell products, but with the added convenience of a larger cell growth area and two options for insert height levels.

Features

- ▶ 100 cm² cell growth area
- ▶ Unique hanging design with two-stage insert heights
- ▶ Suitable for coating with a variety of extracellular matrices (ECM) and basement membrane extracts (BME)


Benefits

- ▶ Rectangular design is ideal for growing tissue in modular formats for maximum coverage.
- ▶ Two-tier receiver tray permits submerged or air liquid interface (ALI) culture.

Transwell 100 cm² large format insert can be used to:

- ▶ Produce a cell culture environment that closely resembles an *in vivo* state
- ▶ Grow a large amount of tissue or cells
- ▶ Allow polarized cells to carry out metabolic activities in a more natural manner via either apical and basolateral feeding or basolateral only with an apical air interface

As an industry leader for over 25 years, Transwell permeable supports are backed by extensive citations, protocols, and scientific support—all to help create a cell culture that more closely mimics an *in vivo* environment.



Transwell large format inserts feature a two-tier receiver tray, which permits submerged or air liquid interface (ALI) culture.

Ordering Information

Transwell® Large Format Inserts

Cat. No.	Description Size	Membrane	Tray Size (inches)	Growth Surface Area (cm ²)	Qty/Pk	Qty/Cs
7424	Transwell, tissue culture-treated, with tray with lid	0.4 µm	6.927 x 4.803 x 1.462	110	5	20
7524	Transwell, rectangular reservoir with lid	N/A	6.927 x 4.803 x 1.462	N/A	5	20

Custom pore sizes and packaging options are available. Contact our scientific support team by email at ScientificSupport@corning.com or phone 800.492.1110, option 3, or 978.442.2200 for more information.

Product Specifications

- ▶ Insert: Membrane 0.4 µm track-etched polycarbonate
- ▶ Body: Virgin polystyrene
- ▶ Tray: Virgin polyethylene terephthalate
- ▶ Sterility Assurance Level (SAL) of 10⁻⁶
- ▶ Tissue culture-treated insert
- ▶ Manufactured in compliance with cGMP standards
- ▶ USP Class VI plasticware
- ▶ Validation package available upon request

Product Dimensions

- ▶ Length of tray: 6.927 inches; bottom of Transwell insert to tray (in high position): 0.549 inches
- ▶ Width of tray: 4.803 inches; bottom of Transwell insert to tray (in low position): 0.124 inches
- ▶ Height with lid: 1.462 inches; volume added/tray (in high position): 197.7 mL
- ▶ Tolerances of dimensions: ±.050 volume added/tray (in low position): 42.2 mL

Tray Dimensions

- ▶ Length of tray: 6.927 inches; width of tray: 4.803 inches; height with lid: 1.462 inches
- ▶ Volume added/tray (in high position): 197.7 mL
- ▶ Tolerances of dimensions: ±.050 volume added/tray (in low position): 42.2 mL

For a complete list of Corning solutions for cell culture, visit www.corning.com/lifesciences.

For more specific information on claims, contact our scientific support team by email at ScientificSupport@corning.com or phone 800.492.1110, option 3, or 978.442.2200.

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

Corning Incorporated Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476
www.corning.com/lifesciences

Worldwide Support Offices

ASIA/PACIFIC
Australia/New Zealand
t 0402-794-347
China
t 86 21 2215 2888
f 86 21 6215 2988
India
t 91 124 4604000
f 91 124 4604099

Japan
t 81 3-3586 1996
f 81 3-3586 1291
Korea
t 82 2-796-9500
f 82 2-796-9300
Singapore
t 65 6733-6511
f 65 6861-2913
Taiwan
t 886 2-2716-0338
f 886 2-2516-7500

EUROPE
France
t 0800 916 882
f 0800 918 636
Germany
t 0800 101 1153
f 0800 101 2427
The Netherlands
t 31 20 655 79 28
f 31 20 659 76 73
United Kingdom
t 0800 376 8660
f 0800 279 1117

All Other European Countries
t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73
LATIN AMERICA
Brasil
t (55-11) 3089-7419
f (55-11) 3167-0700
Mexico
t (52-81) 8158-8400
f (52-81) 8313-8589

CORNING | **FALCON** | **AXYGEN** | **GOSELIN** | **PYREX**

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks.
All other trademarks in this document are the property of their respective owners.