## SpectraMux® - Coarse WDM (Eight Channel)



#### **Features and Benefits**

20 nm Channel Separation

·
Bi - Directional
High Isolation
Low Insertion Loss
Epoxy-Free Optical Path
Express Channel Available

### **Standards**

RoHS	Free of hazardous substances according to RoHS2011/65/EU
Design and Test Criteria	Product is qualified to Telcordia GR-1209-CORE and GR-1221-CORE

Corning introduces the Spectramux® family of products, which are designed for cost effective multiwavelength network applications. Channel spacing of 20 nm with wide bandpass characteristics allow for non-temperature controlled lasers to be used in transmitters. Based on Corning's proven thin film technology, SpectraMux CWDMs allow for four and eight wavelengths to be used for uni- or bi-directional transmission. Like all Corning DWDM products, these devices are designed for long life service under the most demanding field conditions. Most connector types are available for terminated ends.



# **SpectraMux® – Coarse WDM (Eight Channel)**



## **Specifications**

Parameters (Eight-Channel)	Minimum	Typical	Maximum
Center Wavelength Ic		1471, 1491, 1511, 1531 nm 1551, 1571, 1591, 1611 nm	
Pass Channel Insertion Loss		2.5 dB	3.0 dB
Express Channel Insertion Loss (Optional)			3.5 dB
Passband Width	13 nm	15 nm	
Passband Flatness		0.3 dB	
Adjacent Channel Isolation	30 dB	40 dB	
Non-Adjacent Channel Isolation	40 dB	50 dB	
Optical Return Loss	50 dB	50 dB	
Directivity	50 dB		
PDL			0.2 db
PMD			0.2 ps
Maximum Optical Power		300 mW	
Operating Temperature Range		-5°C to +65°C	
Storage Temperature Range		-40°C to +85°C	
Tensile Load (900 μm Buffered)		5N Maximum	
*Specifications do not include connector lo	oss		

Packaging Dimensions	Fiber Type	Pigtail Length
126 mm x 93 mm x 15 mm	Fiber Type: Corning® SMF-28e® or compatible, 900 μm	1 m (Standard)

## SpectraMux® - Coarse WDM (Eight Channel)



### **Ordering Information**

SpectraMux® - Coarse WDM (Eight Channel)

 $C W 4 - \square 2 2 \square - \square 1 \square \square \square$ 

1 Select Mux or DeMux
1: Mux
2: DeMux

2 Select Package Type 2: 250 mm Box

4: LGX Rack Mounted Module

2: 250 mm Box 3: 900 mm Box 3 Select Connector Type A: None

L: LC/PC P: FC/PC

Q: FC/APC S: SC/PC T: SC/APC

U: MU/PC

4 Select Optional Channel

0: No Express 1: With Express

5 Select Customization
00: Standard
Running number used for special types
or custom made

These part numbers are specific to Corning Optical Communications OEM Solutions Business Unit. Please contact OEM sales at +1-408-736-6900 or oemsales@corning.com and visit www.corning.com/opcomm/oem for sales support.



