


Corning® Microcarriers for Bioprocess Scale-Up

CORNING

Corning Microcarriers are designed to simplify your scale-up processes. The microcarriers are sterile, ready-to-use, and available in closed systems packaging to be used directly with bioreactors. Additionally, the microcarriers are surface treated to enhance cell attachment, maximizing cell yield and viability. To get the most out of your manufacturing, try Corning Microcarriers.



hMSC on Corning Synthemax II polystyrene microcarriers

Features

- ▶ Consistency – USP Class VI polystyrene material provides a consistent platform
- ▶ Performance – Corning Microcarriers are offered with four surface treatments:
 - Corning Synthemax® II Coating: the unique Corning Synthemax II substrate creates a synthetic surface on the microcarriers for stem cell expansion. Use Low Concentration for MSC applications and High Concentration for iPS/ES applications.
 - CellBIND® surface treatment infuses the surface of the microcarriers with oxygen to improve cell attachment
 - Positive charge surface treatment
 - Collagen coating
- ▶ Highest Sterility Assurance Level (SAL) of 10^{-6}
- ▶ Certified nonpyrogenic
- ▶ Available as Closed System Solutions

Product Specifications


- ▶ Bead size: 125-212 μm
- ▶ Density: $1.026 \pm 0.004 \text{ g/cm}^3$
- ▶ cm^2/gram : 360



Corning Synthemax II and Enhanced Attachment Microcarriers in 10 g vials



Closed system packaging for Corning Microcarriers



Closed System Packaging

Vials and Closed Systems Packaging

Corning® Microcarriers are available sterile and ready to use in 10 g vials. This format provides flexibility to select the amount of beads to use.

During the mature phase of process development and into manufacturing, closed system packaging would be necessary to maintain sterility and ease bioreactor loading. Corning microcarriers are also available in off-the-shelf and custom closed bag packaging. Tubing, connectors and materials are customizable based on individual needs.

Technical Support

Corning strives to provide the highest technical support for all our products. Please reach out to your account manager, sales specialists or field applications scientist for ideas on how to optimize Corning Microcarriers for your scale-up needs.

Corning Microcarriers Ordering Information

Cat. No.	Description	Size	Qty/Cs
3772	Corning Untreated Microcarriers	10g vial	1
3779	Corning CellBIND® Microcarriers	10g vial	1
3781	Corning Low Concentration Synthemax® II Microcarriers	10g vial	1
3784	Corning High Concentration Synthemax II Microcarriers	10g vial	1
3786	Corning Collagen Coated Microcarriers	10g vial	1
3787	Corning Positive Charge Surface Microcarriers	10g vial	1

For additional Corning product, technical, or distributor information, please e-mail us at CLStechserv@corning.com, visit our website www.corning.com/lifesciences or call 1.800.492.1110. Outside the United States, call 978.442.2200.

Corning Incorporated Life Sciences

836 North St.
Building 300, Suite 3401
Tewksbury, MA 01876
t 800.492.1110
t 978.442.2200
f 978.442.2476

www.corning.com/lifesciences

Worldwide Support Offices

ASIA/PACIFIC

Australia/New Zealand
t 0402-794-347

China

t 86 21 2215 2888
f 86 21 6215 2988

India

t 91 124 4604000
f 91 124 4604099

Japan

t 81 3-3586 1996
f 81 3-3586 1291

Korea

t 82 2-796-9500
f 82 2-796-9300

Singapore

t 65 6733-6511
f 65 6861-2913

Taiwan

t 886 2-2716-0338
f 886 2-2516-7500

EUROPE

France

t 0800 916 882
f 0800 918 636

Germany

t 0800 101 1153
f 0800 101 2427

The Netherlands

t 31 20 655 79 28
f 31 20 659 76 73

United Kingdom

t 0800 376 8660
f 0800 279 1117

All Other European Countries

t 31 (0) 20 659 60 51
f 31 (0) 20 659 76 73

LATIN AMERICA

Brasil

t (55-11) 3089-7419
f (55-11) 3167-0700

Mexico

t (52-81) 8158-8400
f (52-81) 8313-8589

The Corning Family of Brands

CORNING **costar** cellgro® PYREX® **AXYGEN**® GOSSSELIN™