# Corning® SMF-28e+® Optical Fiber

### **Product Information**

# **CORNING**

ColorPro® Identification

SMF-28e+ fiber is also available in colored and ringmarked variants,

variants, enabled by ColorPro® identification technology.

Corning fibers with ColorPro® identification technology

deliver better efficiency in cable manufacturing, simplify inventory

management, and leverage an

enhanced fiber product offering.

Technology

**How to Order** 

Contact your sales

representative, or call the Optical Fiber Customer Service Department: Ph: 1-607-248-2000 (U.S./Can.) +44-1244-525-320 (Europe) Email: cofic@corning.com Please specify the fiber type, attenuation, and quantity when ordering.



Built on Corning's solid foundation of quality and proven performance, Corning® SMF-28e+® optical fiber is the most widely deployed fiber in the world. Optimized for access and metro networks and meeting the demand for high-speed connectivity, SMF-28e+ fiber is compatible and fully compliant with Recommendation ITU-T G.652.D.

## **Optical Specifications**

#### **Maximum Attenuation**

| Wavelength | Maximum Value* |
|------------|----------------|
| (nm)       | (dB/km)        |
| 1310       | ≤ 0.35         |
| 1383**     | ≤ 0.35         |
| 1490       | ≤ 0.24         |
| 1550       | ≤ 0.20         |
| 1625       | ≤ 0.23         |

<sup>\*</sup>Alternate attenuation offerings available upon request.

#### Attenuation vs. Wavelength

| Range       | Ref. λ | Max. $\alpha$ Difference |
|-------------|--------|--------------------------|
| (nm)        | (nm)   | (dB/km)                  |
| 1285 – 1330 | 1310   | 0.03                     |
| 1525 — 1575 | 1550   | 0.02                     |

The attenuation in a given wavelength range does not exceed the attenuation of the reference wavelength ( $\lambda$ ) by more than the value  $\alpha$ .

#### **Macrobend Loss**

| Mandrel<br>Radius<br>(mm) | Number<br>of<br>Turns | Wavelength<br>(nm) | Induced<br>Attenuation*<br>(dB) |
|---------------------------|-----------------------|--------------------|---------------------------------|
| 16                        | 1                     | 1550               | ≤ 0.03                          |
| 30                        | 100                   | 1625               | ≤ 0.1                           |

<sup>\*</sup>The induced attenuation due to fiber wrapped around a mandrel of a specified radius.

### **Point Discontinuity**

| Wavelength | Point Discontinuity |
|------------|---------------------|
| (nm) _     | (dB)                |
| 1310       | ≤ 0.05              |
| 1550       | ≤ 0.05              |

### Cable Cutoff Wavelength ( $\lambda_{cc}$ )

 $\lambda_{cc} \leq 1260 \text{ nm}$ 

#### **Mode Field Diameter**

| Wavelength | Mode Field Diameter |
|------------|---------------------|
| (nm)       | (μm)                |
| 1310       | 9.2 ± 0.4           |
| 1550       | 10.4 ± 0.5          |

#### Dispersion

| Wavelength<br>(nm) | Dispersion Value<br>[ps/(nm•km)] |
|--------------------|----------------------------------|
| 1550               | ≤ 18                             |
| 1625               | ≤ 22                             |

Zero Dispersion Wavelength ( $\lambda_0$ ): 1304 nm  $\leq \lambda_0 \leq$  1324 nm Zero Dispersion Slope  $(S_0)$ :  $\leq 0.092 \text{ ps/(nm}^2 \cdot \text{km)}$ 

#### **Polarization Mode Dispersion (PMD)**

Value (ps/Vkm)

|                              | · a. a. (P3, · ) |
|------------------------------|------------------|
| PMD Link Design Value        | ≤ 0.06*          |
| Maximum Individual Fiber PMD | ≤ 0.1            |

<sup>\*</sup>Complies with ITU-T G.650-2 Appendix IV, (m = 20, Q = 0.01%), August 2015.

The PMD link design value is a term used to describe the PMD of concatenated lengths of fiber (also known as PMD<sub>Q</sub>). This value represents a statistical upper limit for total link PMD. Individual PMD values may change when



Issued: November 2021 Supersedes: September 2019

<sup>\*\*</sup>Attenuation values at this wavelength represent post-hydrogen aging performance.

# **Dimensional Specifications**

**Glass Geometry** 

### **Coating Geometry**

| Fiber Curl               | ≥ 4.0 m radius of curvature |
|--------------------------|-----------------------------|
| Cladding Diameter        | 125.0 ± 0.7 μm              |
| Core-Clad Concentricity  | ≤ 0.5 μm                    |
| Cladding Non-Circularity | ≤ 0.7%                      |

| Coating Diameter               | 242 ± 5 μm |
|--------------------------------|------------|
| Coating-Cladding Concentricity | < 12 μm    |

# **Environmental Specifications**

| Environmental Test           | Test Condition              | Induced Attenuation<br>1310 nm, 1550 nm, and 1625 nm<br>(dB/km) |
|------------------------------|-----------------------------|---|
| Temperature Dependence       | -60°C to +85°C*             | ≤ 0.05  |
| Temperature Humidity Cycling | -10°C to +85°C up to 98% RH | ≤ 0.05  |
| Water Immersion              | 23°C ± 2°C                  | ≤ 0.05  |
| Heat Aging                   | 85°C ± 2°C                  | ≤ 0.05  |
| Damp Heat                    | 85°C at 85% RH              | ≤ 0.05  |

Operating Temperature Range: -60°C to +85°C

# **Mechanical Specifications**

#### **Proof Test**

The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.69 GPa). Higher proof test levels are available.

### Length

Fiber lengths available up to 50.4 km/spool.

### **Performance Characterizations**

Characterized parameters are typical values.

| Core Diameter   | 8.2 μm  |
|---|---|
| Numerical Aperture                                      | 0.14  NA is measured at the one percent power level of a one-dimensional far-field scan at 1310 nm. |
| Effective Group Index of Refraction (n <sub>eff</sub> ) | 1310 nm: 1.4674<br>1550 nm: 1.4679  |
| Fatigue Resistance Parameter (n <sub>d</sub> )          | 20  |
| Coating Strip Force                                     | Dry: 0.6 lbs. (3 N)<br>Wet, 14-day room temperature: 0.6 lbs. (3 N)                                 |
| Rayleigh Backscatter Coefficient (for 1 ns Pulse Width) | 1310 nm: -77 dB<br>1550 nm: -82 dB  |

<sup>\*</sup>Reference temperature = +23°C