

Mode Field Diameter and Effective Area

White Paper



CORNING
Discovering Beyond Imagination

Optical
Fiber

WP7071
Issued: October 2001
Supersedes: March 2000
ISO 9001 Registered

Michael R. Vastag
Senior Applications Engineer

Mode Field Diameter

The mode field diameter (MFD) represents a “measure of the transverse extent of the electromagnetic field intensity of a mode of light in a fiber cross section”¹. In optical fiber, this typically is larger than the fiber core, since a portion of the light propagates through the cladding. MFD traditionally has been determined using a Gaussian approximation of the intensity distribution with the MFD defined as the width of the curve at the $1/e^2$ power level. As fiber refractive index profiles have evolved, however, their complexity has rendered the Gaussian approximation invalid. The current international standard measurement is the “Petermann II” method, a rigorous approach that calculates MFD by integrating the actual intensity distribution over the range of far field angles. Thus, it does not rely on the shape of the fiber’s transmitted intensity curve; rather, it integrates the continuous intensity function, regardless of shape. The Petermann II mode field diameter definition is as follows:

$$MFD = 2\omega_o = \left(\frac{\lambda}{\pi} \right) \left[\frac{2 \int_0^{\pi/2} I(\theta) \sin(\theta) \cos(\theta) d\theta}{\int_0^{\pi/2} I(\theta) \sin^3(\theta) \cos(\theta) d\theta} \right]^{1/2}$$

where:

$I(\theta)$ is the intensity distribution at all angles

Effective Area

Effective area is not just the geometric transform of the MFD (the old πr^2 – sometimes called the mode field area [MFA]). Rather, it is a mathematical representation of the light transmitting area calculated with respect to a fiber’s response to nonlinear effects, primarily self phase modulation (SPM) and four wave mixing (FWM). Thus, the effective area is different for each type of fiber, based primarily on that fiber’s refractive index profile and the input wavelength. The effective area has been empirically determined to be typically in the range of 95-104% of the MFA, though it has been shown to be as much as 111% of the MFA². We calculate the effective area by using a nonlinear solution to the Schrodinger’s equation, which accounts for the fiber’s response to non-linear effects:

$$A_{eff} = \left\{ \frac{2\pi \left[\int_0^{\infty} E(r)^2 r dr \right]^2}{\int_0^{\infty} E(r)^4 r dr} \right\}$$

where:

$$E(r) = E_o \int_0^{\infty} [Pm(\Theta)]^{1/2} J_o(r) \beta \sin(\Theta) \sin 2\Theta d\Theta,$$

the near field Hankel Transform of the far field scan³

It is possible to empirically determine a mapping relationship between the MFD and the effective area, but this relation is wavelength dependent. The general relation is as follows:

$$A_{\text{eff}} = k(\lambda) \left(\frac{\pi}{4} \right) MFD^2 \quad \text{where:}$$

k (λ) is the mapping value and MFD is determined by the Petermann II method⁴.

In summary, the effective area and MFD are not directly related. The effective area is the more appropriate representation of the light-carrying region in fibers used in applications in which nonlinear effects can be a significant restriction to system performance.

References

- ¹TIA/EIA FOTP-191 "Measurement of Mode Field Diameter of Single-Mode Optical Fiber," September, 1998.
- ²Y. Liu et al., "Large effective area dispersion shifted fibers with dual-ring index profiles," OFC '96, paper WK15.
- ³M. Hackert and M. Zainul, "Effective Area Measurement Comparison Between Direct Far Field Scan and Variable Aperture Method in the Far Field," Corning Incorporated, 1996.
- ⁴Y. Namihira, "Relationship between nonlinear effective area and modefield diameter for dispersion shifted fibres," Electronic Letters 30, 1994.

Additional References

- 1. TIA/EIA FOTP-167 "Mode Field Diameter Method in the Far Field," March 1992.
- 2. V. da Silva et al., "Comparison of nonlinear coefficient of optical fibers at 1550 nm," OFC '96, paper ThA4.
- 3. Y. Liu et al., "Dispersion shifted large effective area fiber for amplified high-capacity long-distance systems," OFC '97, paper TuN5 (invited).
- 4. Y. Liu et al., "Single-Mode Dispersion Shifted Fibers with Effective Area Larger than 80 μm^2 and Good Bending Performance," ECOC '95, paper Tu.L.2.4.

Corning Incorporated www.corning.com/opticalfiber

One Riverfront Plaza
Corning, NY 14831
U.S.A.

Phone: 800-525-2524 (U.S. and Canada)
607-786-8125 (International)

Fax: 800-539-3632 (U.S. and Canada)
607-786-8344 (International)

Email: cobic@corning.com

Europe

Berkeley Square House
Berkeley Square
London W1X 5PE
U.K.

Phone: 00 800 2800 4800 (U.K.* Ireland, France,
Germany, The Netherlands, Spain and Sweden)
*Callers from U.K. dial (00) before the phone number

00 800 781 516 (Italy)

+44 7000 280 480 (All other countries)

Fax: +44 7000 250 450

Email: eurocofic@corning.com

Asia Pacific

Australia
Phone: 1-800-148-690
Fax: 1-800-148-568

Indonesia
Phone: 001-803-015-721-1261
Fax: 001-803-015-721-1262

Malaysia
Phone: 1-800-80-3156
Fax: 1-800-80-3155

Philippines
Phone: 1-800-1-116-0338
Fax: 1-800-1-116-0339

Singapore
Phone: 800-1300-955
Fax: 800-1300-956

Thailand
Phone: 001-800-1-3-721-1263
Fax: 001-800-1-3-721-1264

Latin America

Brazil
Phone: 000817-762-4732
Fax: 000817-762-4996

Mexico
Phone: 001-800-235-1719
Fax: 001-800-339-1472

Venezuela
Phone: 800-1-4418
Fax: 800-1-4419

Greater China

Beijing
Phone: (86) 10-6505-5066
Fax: (86) 10-6505-5077

Hong Kong
Phone: (852) 2807-2723
Fax: (852) 2807-2152

Shanghai
Phone: (86) 21-6361-0826 ext. 107
Fax: (86) 21-6361-0827

Taiwan
Phone: (886) 2-2716-0338
Fax: (886) 2-2716-0339

E-mail: iuyt@corning.com

Corning is a registered trademark of Corning Incorporated, Corning, N.Y.

©2001, Corning Incorporated

