


## EDGE™ Distribution System: Pre-Engineered to Go Faster

A New Path to Speed & Sustainability

Our pre-engineered data center solutions can help customers install faster, reduce packaging, and minimize risk:


- **Pre-Engineered for Fast, Easy Installation** – Compared to a traditional patch cord deployment, EDGE DS is one assembly, one SKU, and one box, installed in 45 minutes vs. 3 hours.\*
- **Personalized to Your Exact Needs** – Custom fiber count, access points, and dimensions designed for the customer's specific data center design. Plus custom labeling and color coding simplify installation.
- **Minimize Risk** – Simplified installation means less ladder time, and less skilled labor needs, reducing the risk associated with server row cable deployments.

A **point-to-multi-point** solution for **server row cabling** needs.



**Feeder Connectors** at the end-of-row Goal Post/IDF.

**Custom Labeling and Color Coding** in the factory minimizes field labor requirements.




**Access Points** along the assembly personalized to your data center design.

**Drop Legs and Connectors** provide needed connectivity to each cabinet.



A **single assembly/SKU** provides up to 75% faster installation.

**More space:** Reduced tray congestion, simplified inventory management, and less packaging



REDUCE SERVER ROW CABLING TIME BY UP TO **75%\***

\*Base case: Row of 18 server cabinets with four fibers provided to each cabinet