

CORNING

EDGE™ Solutions



EDGE™ Solutions for Enterprise Data Centers and Storage Area Networks

Corning EDGE™ solutions create a fiber optic tip-to-tip solution for data centers and storage area networks (SANs) consisting of housings, modules, panels, trunks, harnesses, and jumpers.



Introducing EDGE™ Solutions

We interviewed over 3,000 data center operators and the answers were clear—infrastructure must be reliable, high-quality, flexible, manageable, scalable, and visible to support a 24/7 year-round operation.

Corning's award-winning EDGE™ solutions were developed to deliver on all of these priorities. In 2009, EDGE became the industry's first high-density preterminated optical cabling system designed specifically for the data center environment. It continues to drive the data center industry forward today. Corning's unwavering commitment to the EDGE Platform for over a decade means it's being continuously refined to simplify installation and improve performance.

Wide range of solutions for extended flexibility

EDGE solutions consist of an extensive range of housings, trunks, modules, adapter panels, harnesses, jumpers, and accessories.

Increased system density

EDGE solutions offer increased system density compared to traditional preterminated systems and the highest port density in the market.

Scale

EDGE and EDGE8 solutions are backed by Corning's robust operational infrastructure, meaning a durable supply chain and factory testing for a 100% product quality guarantee. And once your data center deployment is completed, you can expect more uptime than ever before.

Interoperability

As technology evolves and higher data rates become the norm, cabling infrastructures installed today must provide scalability to accommodate more bandwidth. Since EDGE8® and EDGE solutions are backward compatible, you can start small now and be ready for the future.

Innovative Corning® ClearCurve® optical fiber

Corning® ClearCurve® bend-optimized optical fiber is a core element across these solutions, ensuring reliability when designing custom-engineered components thanks to its significant reduction in macrobend loss even in the most challenging bend scenarios.

Preterminated components allow for reduced installation time and faster moves, adds, and changes (MACs)

Factory-terminated solutions provide improved system performance, ensure component compatibility, and yield consistent high quality.

Always improving


EDGE is always looking forward through new innovations. Future facing components like the EDGE Distribution System and EDGE Rapid Connect accelerate installation by 70%.

Advanced Cleaning Technology

All EDGE solutions, with the exception of TAP modules and 24-fiber MTP® single-mode assemblies, are manufactured with Corning® CleanAdvantage™ technology, a new cleaning process implemented at the factory-level that uses residue-free cleaning fluids. Corning's proprietary nozzle design enables a focused and directed spray to the end face, virtually cleaning the entire ferrule. All CleanAdvantage products are shipped with optimized dust caps engineered to maintain end-face cleanliness until the first mating connection. CleanAdvantage eliminates the need for scoping and cleaning prior to the initial field connection, reducing installation time and cost.

EDGE™ Innovation Timeline

Across the years, we've expanded the EDGE™ portfolio to include a wide breadth of solutions. Our commitment to this groundbreaking platform has led to award-winning performance that has been deployed in thousands of data centers worldwide.




Contents

| | |
|---|----|
| EDGE™ Housings | |
| High-Density Housings and Fixed Housings. | 7 |
| EDGE Trunks | |
| MTP® Trunks, MTP Extender Trunks, MTP Hybrid Trunks, MTP Hybrid Extender Trunks | 9 |
| EDGE MTP Jumpers | |
| 12 F MTP Jumpers and 24 F MTP Jumpers | 18 |
| EDGE Harnesses | |
| Staggered and Nonstaggered 12 F Harnesses, Conversion Harnesses, “Y” Harnesses, MTP Breakout Harnesses, Tap Harnesses . . . | 20 |
| EDGE Modules | |
| Preloaded Hardware, Modules, Low-loss Modules, Conversion Modules, Mesh Modules, Ultra-Low-Loss Modules | 28 |
| EDGE SE Splice Cassettes | |
| EDGE Multi-Splice Cassettes, EDGE Trunk Splice Cassettes, EDGE SE Field-Term Cassettes (empty) | 34 |
| EDGE MTP Adapter Panels | |
| Pass-Through Patch Panels with MTP Adapters | 38 |
| EDGE Tap Modules | |
| Port Monitoring in LAN and SAN DC Areas. | 39 |
| Lockable Uniboot Jumpers | |
| EDGE LC Lockable Uniboot Jumpers | 43 |
| Reverse Polarity Jumpers and Colored Clips | |
| LC Uniboot Jumpers with Optional Color Coding | 44 |
| Optical Distribution Frames | |
| EDGE Optical Distribution Frame (ODF). | 46 |
| Accessories | |
| Cleaning, Housing, and Trunk Accessories | 48 |

EDGE™ Solutions Overview

EDGE™ solutions are high-density preterminated optical cabling solutions offering industry-leading connector density. With unprecedented finger access, there is no need for additional tools enabling faster moves, adds, and changes (MACs).



EDGE Solutions | Photo LAN2279

Features and Benefits

Corning® CleanAdvantage™ technology and optimized dust caps

Eliminates the need for scoping and cleaning prior to initial field connection.

Corning® ClearCurve® fiber creates smaller-form-factor components for more rugged cabling

Reduces congestion within and between racks for improved airflow and less risk of downtime due to pinched or bent cables.

MTP® PRO Connector and Push-Pull Boot

Allows for pinning and polarity changing in the field while enabling easier mating and unmating in extremely dense applications.

MTP assemblies with reduced footprint and cable OD

Reduces congestion in high-connectivity environment. Provide easier access to modules and panel.

EDGE™ reverse polarity uniboot jumpers

Enables quick-and-easy polarity management.

New mounting system and improved mounting brackets

Allows for one-person installation and depth adjustment in the rack.

Bracket option for 23-in rack

Offers the ultimate design flexibility.

Snap-in strain-relief clips

Provides easier cable management.

Connected Mated Pair – Low Loss

| | Insertion Loss, Maximum OM3/OM4/OM5 | OS2 |
|---------------|--|---------|
| LC Connector | 0.15 dB | 0.25 dB |
| MTP Connector | 0.35 dB | 0.75 dB |

MTP to LC Modules – Low Loss

| | Insertion Loss, Maximum OM3/OM4/OM5 | OS2 |
|-----------------|--|--------|
| Component Value | 0.5 dB | 1.0 dB |

Connected Mated Pair – Ultra Low Loss

| | Insertion Loss, Maximum OM3/OM4/OM5 | OS2 |
|----------------|--|---------|
| LC Connector | 0.10 dB | 0.25 dB |
| MTP® Connector | 0.25 dB | 0.35 dB |

*All MTP connectors on trunks are manufactured to meet ultra-low-loss values

MTP® to LC Modules/MTP to LC Harnesses – Ultra Low Loss

| | Insertion Loss, Maximum OM3/OM4/OM5 | OS2 |
|-----------------|--|--------|
| Component Value | 0.35 dB | 0.6 dB |

Conversion Module/Conversion Harness

| | Insertion Loss, Maximum OM4 |
|-----------------|--------------------------------|
| Component Value | 0.5 dB |



EDGE™ Solutions HD Housing

EDGE™ solutions HD housings are mountable in 19-in racks or cabinets and provide industry-leading high-density connectivity when combined with EDGE modules, panels, harnesses, trunks, and jumpers.



EDGE-01U | Photo LAN1693



EDGE-01U-SP | Photo LAN7370



EDGE-02U | Photo LAN6656



EDGE-04U | Photo LAN6680

Features and Benefits

Sliding drawers

Allows unprecedented finger access, easier jumper/harness routing, and port identification.

Quick mounting system

Enables one-person installation and depth adjustment of the housing in the rack.

Removable top covers on the 1U and 2U housings

Provides easier access to modules and panels.

Total flexibility in the same HD housing

- Accepts EDGE universal modules
- Accepts EDGE conversion modules
- Accepts EDGE Tap modules
- Accepts EDGE 2x, 4x, and 6x MTP® adapters
- Accepts EDGE 6x LC duplex adapter panels

High-port concentration with LC duplex and MTP Base-12 system

- 1U EDGE Housing EDGE-01U
48x LC duplex ports (96 fiber)
48x MTP ports (384 fiber)
- 1U EDGE Housing EDGE-01U-SP
72x LC duplex ports (144 fiber)
72x MTP ports (576 fiber)
- 2U EDGE Housing EDGE-02U
144x LC duplex ports (288 fiber)
144x MTP ports (1152 fiber)
- 4U EDGE Housing EDGE-04U
288x LC duplex ports (576 fiber)
288x MTP ports (2304 fiber)

Ordering Information

| Part Number | Height | Dimensions (W x D x H) | Packaging Dimensions (W x D x H) | Shipping Weight | Number of Panels per Housing |
|-------------|--------|--------------------------|----------------------------------|------------------|------------------------------|
| EDGE-01U | 1U | 432 mm x 561 mm x 44 mm | 565 mm x 657 mm x 171 mm | 9.3 kg (20.4 lb) | 8 |
| EDGE-01U-SP | 1U | 432 mm x 561 mm x 44 mm | 565 mm x 646 mm x 171 mm | 8.2 kg (18 lb) | 12 |
| EDGE-02U | 2U | 432 mm x 561 mm x 88 mm | 565 mm x 660 mm x 216 mm | 10.9 kg (24 lb) | 24 |
| EDGE-04U | 4U | 432 mm x 561 mm x 177 mm | 565 mm x 660 mm x 305 mm | 16.8 kg (37 lb) | 48 |

Notes:

- When rear strain-relief plate is removed from part number EDGE-01U-SP, product depth reduces to 14.9 in.
- EDGE-01U has sliding inner assembly. EDGE-01U-SP does not have sliding inner assembly.

EDGE™ FX Housing

EDGE™ FX housings are available in 1U, 2U, and 4U sizes that mount into 19-in racks or cabinets as well as two other housings that can mount in the floor. Combine these housings with the EDGE modules, panels, trunks, harnesses, and jumpers to experience an industry-leading solution. The reduced depth of the rack-mount housings allow for the back-to-back installation in 4-post racks or cabinets as well as third-party floor boxes.

| Ordering Information | | | | | |
|----------------------|--------|--|---|------------------|------------------------------|
| Part Number | Height | Dimensions (W x D x H) | Packaging Dimensions (W x D x H) | Shipping Weight | Number of Panels per Housing |
| EDGE-01U-EMOD | 1U | 432 mm x 107 mm x 44.5 mm (17 in x 4.2 in x 1.75 in) | 534 mm x 201 mm x 138 mm (21 in x 7.9 in x 5.4 in) | 1.14 kg (2.5 lb) | 8 |
| EDGE-01U-EMOD-SP | 1U | 432 mm x 107 mm x 44.5 mm (17 in x 4.2 in x 1.75 in) | 534 mm x 201 mm x 138 mm (21 in x 7.9 in x 5.4 in) | 1.22 kg (2.7 lb) | 12 |
| EDGE-01U-FP | 1U | 488 mm x 439 mm x 43 mm (19.2 in x 17.3 in x 1.7 in) | 584 mm x 470 mm x 152 mm (22.9 in x 18.5 in x 5.9 in) | 4.4 kg (9.6 lb) | 8 |
| EDGE-02U-FP | 2U | 432 mm x 434 mm x 89 mm (17 in x 17.1 in x 3.5 in) | 569 mm x 346 mm x 229 mm (22.4 in x 13.6 in x 9 in) | 6.4 kg (14 lb) | 16 |
| EDGE-04U-FP | 4U | 432 mm x 434 mm x 178 mm (17 in x 17.1 in x 7 in) | 567 mm x 346 mm x 320 mm (22.4 in x 13.6 in x 7.25 in) | 9.6 kg (21 lb) | 32 |
| EDGE-FZB-04U | - | 527 mm x 527 mm x 241 mm (20.75 in x 20.75 in x 9.5 in) | 656 mm x 643 mm x 356 mm (25.8 in x 25.3 in x 14 in) | 17.8 kg (39 lb) | 32 |
| EDGE-SMH | - | 152 mm x 102 mm x 25 mm (6 in x 4 in x 1 in) | 229 mm x 184 mm x 57 mm (9 in x 7.25 in x 2.25 in) | 1 kg (3 lb) | 1 |



EDGE-01U-EMOD | Photo LAN4821



EDGE-01U-FP | Photo LAN2656



EDGE-02U-FP | Photo REN1610



EDGE-04U-FP | Photo REN1575



EDGE-SMH | Photo REN3548



EDGE-FZB-04U | Photo LAN1868

EDGE™ Trunks

EDGE™ MTP® trunks are preterminated cables with MTP PRO connectors. Available in MTP to MTP or MTP to LC configurations, these trunks provide the backbone of the passive network infrastructure and enable rapid deployment for your campus LAN or data center facility. All trunks are manufactured with Corning® CleanAdvantage™ technology and shipped with strain-relief clips, allowing for easy and quick tool-less installation in both EDGE solutions and Plug & Play™ systems housings.

Features and Benefits

Corning CleanAdvantage technology with optimized dust caps

Eliminates the need for scoping and cleaning prior to initial field connection.

MTP PRO Connector and Push-Pull Boot

Allows for pinning and polarity changing in the field while enabling easier mating and unmating in extremely dense applications.

Snap-in strain-relief clips

Provides easier cable management.

Small outer diameter

Improves cable tray fill ratio and allows for improved airflow.

Bend-improved fiber

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables.



EDGE-02U Rack-Mount Rear Side | Photo LAN7314



EDGE MTP to MTP Trunk | Photos REN7793 and REN7794



EDGE MTP to LC Hybrid Trunk | Photos REN7962 and REN7963

Trunk Specifications

| | |
|-----------------------|---|
| Approval and Listings | NFPA 262, National Electrical Code* (NEC*), OFNP, CSA FT-6 |
| | EIA/TIA 568.3-D – includes low/high temperature soak of -10°C/60°C, humidity testing at 90-95% at 40°C, connector durability (500 matings) and connector pull testing |
| Trunk Performance | Trunks can be pulled up to 100 lbs using the grip |

| Mechanical Characteristics | | | | | | | |
|----------------------------------|----------------------------|-----------------------------|----------------|---------------------------------------|-----------------------------|---|---|
| Fiber Count | Nominal Outer Diameter | Pulling Grip Outer Diameter | Furcation Type | Minimum Conduit Size with 18-in Elbow | Weight | Minimum Bend Radius (Installation - 15x OD) | Minimum Bend Radius (Operation - 5x OD) |
| Non-Armored Cable Specifications | | | | | | | |
| 12 | 5.5 mm ± 0.3 mm (0.22 in) | 41 mm (1.6 in) | EDGE Size 1 | 2.5 in | 32 kg/km (22 lb/1,000 ft) | 82.5 mm (3.25 in) | 27.5 mm (1.08 in) |
| 24 | 7.7 mm ± 0.3 mm (0.30 in) | 41 mm (1.6 in) | EDGE Size 1 | 2.5 in | 50 kg/km (34 lb/1,000 ft) | 115.5 mm (4.55 in) | 38.5 mm (1.52 in) |
| 36 | 8.0 mm ± 0.3 mm (0.31 in) | 41 mm (1.6 in) | EDGE Size 1 | 2.5 in | 56 kg/km (38 lb/1,000 ft) | 120 mm (4.72 in) | 40 mm (1.57 in) |
| 48 | 8.5 mm ± 0.3 mm (0.33 in) | 56 mm (2.2 in) | EDGE Size 2 | 3.0 in | 63 kg/km (42 lb/1,000 ft) | 127.5 mm (5.02 in) | 42.5 mm (1.67 in) |
| 72 | 10.5 mm ± 0.3 mm (0.41 in) | 56 mm (2.2 in) | EDGE Size 2 | 3.0 in | 93 kg/km (62 lb/1,000 ft) | 157.5 mm (6.2 in) | 52.5 mm (2.07 in) |
| 96 | 11.9 mm ± 0.3 mm (0.47 in) | 56 mm (2.2 in) | EDGE Size 2 | 3.0 in | 111 kg/km (75 lb/1,000 ft) | 178.5 mm (7.03 in) | 59.5 mm (2.34 in) |
| 144 | 12.5 mm ± 0.3 mm (0.49 in) | 56 mm (2.2 in) | EDGE Size 2 | 3.0 in | 130 kg/km (87 lb/1,000 ft) | 187.5 mm (7.38 in) | 62.5 mm (2.46 in) |
| 192 | 13.5 mm ± 0.8 mm (0.33 in) | 38.1 mm (1.5 in) | Heat-shrink | 2.0 in | 182 kg/km (122 lb/1,000 ft) | 202.5 mm (7.97 in) | 67.5 mm (2.66 in) |
| 216 | 14.0 mm ± 0.8 mm (0.55 in) | 38.1 mm (1.5 in) | Heat-shrink | 2.0 in | 195 kg/km (131 lb/1,000 ft) | 210 mm (8.27 in) | 70 mm (2.76 in) |
| 288 | 16.0 mm ± 0.8 mm (0.63 in) | 38.1 mm (1.5 in) | Heat-shrink | 2.0 in | 238 kg/km (160 lb/1,000 ft) | 250 mm (9.45 in) | 80 mm (3.15 in) |
| 432 | 22.9 mm ± 0.8 mm (0.90 in) | 48.3 mm (1.9 in) | Heat-shrink | 2.5 in | 400 kg/km (269 lb/1,000 ft) | 343.5 mm (13.52 in) | 114.5 mm (4.51 in) |
| 576 | 24.5 mm ± 0.8 mm (0.96 in) | 48.3 mm (1.9 in) | Heat-shrink | 2.5 in | 472 kg/km (317 lb/1,000 ft) | 367.5 mm (14.47 in) | 122.5 mm (4.82 in) |
| Armored Cable Specifications | | | | | | | |
| 12 | 11.3 mm ± 1.5 mm (0.45 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 109 kg/km (73 lb/1,000 ft) | 169.5 mm (6.67 in) | 56.5 mm (2.22 in) |
| 24 | 13.7 mm ± 1.5 mm (0.54 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 145 kg/km (97 lb/1,000 ft) | 205.5 mm (8.09 in) | 68.5 mm (2.70 in) |
| 36 | 13.7 mm ± 1.5 mm (0.54 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 151 kg/km (102 lb/1,000 ft) | 205.5 mm (8.09 in) | 68.5 mm (2.70 in) |
| 48 | 15.1 mm ± 1.5 mm (0.59 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 167 kg/km (113 lb/1,000 ft) | 226.5 mm (8.92 in) | 75.5 mm (2.97 in) |
| 72 | 16.6 mm ± 1.5 mm (0.65 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 207 kg/km (140 lb/1,000 ft) | 249 mm (9.80 in) | 83 mm (3.27 in) |
| 96 | 17.3 mm ± 1.5 mm (0.68 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 232 kg/km (156 lb/1,000 ft) | 259.5 mm (10.22 in) | 86 mm (3.41 in) |
| 144 | 18.8 mm ± 1.5 mm (0.74 in) | 51 mm (2.0 in) | P&P Size 1 | 3.0 in | 260 kg/km (175 lb/1,000 ft) | 282 mm (11.10 in) | 94 mm (3.70 in) |



Transmission Performance

| Fiber Type* | Multimode | Multimode | Multimode | Multimode |
|--|-------------------------|-------------------------|-------------------------|----------------|
| Fiber Core Diameter (µm)† | 50 | 50 | 50 | 8.2 |
| Fiber Category‡ | OM3 | OM4 | OM5 | OS2 |
| Fiber Code | T | Q | V | G |
| Wavelengths (nm) | 850/1300 | 850/1300 | 850/953/1300 | 1310/1383/1550 |
| Maximum Attenuation (dB/km) | 2.8/1.0 | 2.8/1.0 | 2.8/1.0 | 0.4/0.4/0.3 |
| Minimum Overfilled Launch (OFL) Bandwidth MHz•km | 1500/500 | 3500/500 | 3500/1850/500 | – |
| Minimum Effective Modal Bandwidth (EMB) MHz•km | 2000/– | 4700/– | 4700/2470/– | – |
| Serial 1 Gigabit Ethernet (m) | 1000/600 | 1100/600 | 1100/600/– | 5000/–/– |
| Serial 10 Gigabit Ethernet (m) | 300/– | 550/– | 550/–/– | 100000/–/40000 |
| Induced Attenuation @ 7.5 mm Radius dB | < 0.2 (2 turns, 850 nm) | < 0.2 (2 turns, 850 nm) | < 0.2 (2 turns, 850 nm) | – |

*Single-mode (OS2) fiber is ITU-T G.652.D compliant.

†50 µm multimode fiber (OM3/OM4) meets 0.75 ns optical skew when used in all Corning Plug & Play™/EDGE™ systems solutions.

‡OM3/OM4 multimode fiber minimum effective modal bandwidth assumes 1.0 dB maximum total connector/splice loss.

Note: Contact a Corning Customer Care Representative for additional information.

Optical Performance Multimode

| | Connector Polish | End Face | Reflectance | Maximum Insertion Loss | Operation |
|-------------|------------------|----------|-------------|------------------------|---------------|
| MTP® Trunks | PC | Flat | ≤ -20 dB | ≤ 0.25 dB* | -10°C to 60°C |

Optical Performance Single-mode

| | Connector Polish | End Face | Reflectance | Maximum Insertion Loss | Operation |
|------------|------------------|----------|-------------|------------------------|---------------|
| MTP Trunks | APC | Angled | ≤ -65 dB | ≤ 0.35 dB* | -10°C to 60°C |

*Note: IL in preconnectorized products is measured in the factory through two mated pairs.

Trunk Shipping Information


| Reel Capacities – 12 to 144 Fibers (Armored) | | | | | | | |
|--|-----------------|----------------|--------------|--------------|--------------|--------------|--------------|
| Packaging Method | Box H | AA (32) | AB (36) | AC (42) | Z (48) | | |
| Packaging Material | Corrugated box | Plastic reel | Plastic reel | Plastic reel | Plywood reel | | |
| Reel Diameter (in) | | 32 | 36 | 42 | 48 | | |
| Reel Width (in) | | 20 | 20 | 20 | 35.5 | | |
| Box Dimensions (in) | 31 x 31.5 x 7 | - | - | - | - | | |
| Fiber Count | Capacities (ft) | | | | | | |
| 12 | 10-50 | 51-3,227 | 3,228-4,957 | 4,958-6,100 | - | | |
| 24 | 10-50 | 51-2,196 | 2,197-3,372 | 3,373-4,100 | - | | |
| 36 | 10-50 | 51-1,496 | 1,497-2,380 | 2,381-4,100 | - | | |
| 48 | 10-50 | 51-1,450 | 1,451-2,300 | 2,301-4,000 | - | | |
| 72 | 10-50 | 51-1,250 | 1,251-2,297 | 2,298-2,850 | 2,851-5,600 | | |
| 96 | 10-50 | 51-940 | 940-1,530 | 1,531-2,580 | 2,581-2,900 | | |
| 144 | 10-50 | 51-680 | 680-1,240 | 1,241-2,200 | 2,201-2,500 | | |
| Reel Capacities – 12 to 144 Fibers (Non-Armored) | | | | | | | |
| Packaging Method | Box E | Box H | Small EDGE™ | Med EDGE | Large EDGE | AA | AB |
| Packaging Material | Corrugated Box | Corrugated Box | Plastic Reel | Plastic Reel | Plastic Reel | Plastic Reel | Plastic Reel |
| Reel Diameter (in) | - | - | 19.5 | 19.5 | 19.5 | 32 | 36 |
| Reel Width (in) | - | - | 5 | 10 | 16 | 20 | 20 |
| Box Dimensions (in) | 21 x 21 x 3.3 | 31x 31.5 x 7 | | | | | |
| Fiber Count | Capacities (ft) | | | | | | |
| 12 | 10-110 | 111-170 | 171-650 | 651-1900 | 1901-3000 | 3001-5000 | 5001-10900 |
| 24 | 10-110 | 111-170 | 171-500 | 501-1000 | 1001-1600 | 1601-2300 | 2301-5300 |
| 36 | 10-110 | 111-170 | 171-450 | 451-950 | 951-1500 | 1501-2200 | 2201-5100 |
| 48 | 10-110 | 111-170 | 171-350 | 351-900 | 901-1450 | 1451-2000 | 2001-4500 |
| 72 | 10-80 | 81-120 | 121-200 | 201-600 | 601-950 | 951-1200 | 1201-3000 |
| 96 | 10-80 | 81-120 | 121-180 | 181-450 | 451-750 | 751-1000 | 1001-2300 |
| 144 | 10-80 | 81-120 | 121-150 | 151-350 | 351-650 | 651-920 | 921-2100 |

Trunk Shipping Information

| Reel Capacities – 192 to 576 Fibers (Non-Armored) | | | | | |
|---|-----------------|--------------|--------------|--------------|--------------|
| Packaging Method | Box H | AA (32) | AB (36) | AC (42) | Z (48) |
| Packaging Material | Corrugated box | Plastic reel | Plastic reel | Plastic reel | Plywood reel |
| Reel Diameter (in) | | 32 | 36 | 42 | 48 |
| Reel Width (in) | | 20 | 20 | 20 | 35.5 |
| Box Dimensions (in) | 31 x 31.5 x 7 | - | - | - | - |
| Fiber Count | Capacities (ft) | | | | |
| 192 | 10-202 | 203-836 | 837-1,824 | 1,825-3,271 | 3,272-8,800 |
| 216 | 10-172 | 173-777 | 778-1,696 | 1,697-3,041 | 3,042-8,200 |
| 288 | 10-137 | 138-593 | 594-1,299 | 1,300-2,394 | 2,395-6,200 |
| 432 | 10-66 | 67-292 | 293-633 | 634-1,246 | 1,247-3,000 |
| 576 | 10-61 | 61-252 | 253-554 | 555-1,089 | 1,090-2,685 |

EDGE™ MTP® Extender Trunk Cables


EDGE MTP® extender trunks provide additional distance for the backbone of the EDGE solution. With a non-pinned MTP PRO connector on one end, a pinned connector on the other, and a TIA-568 Type-A polarity, these trunks are designed to interface with an EDGE solutions or Plug & Play™ systems module and an MTP trunk. All extender trunks are manufactured with Corning® CleanAdvantage™ technology and shipped with strain-relief clips to allow easy tool-less installation.



EDGE MTP Trunk Cable | Photos REN7793

MTP extender trunks are most often used in a zone distribution area (ZDA).

Ordering Information



- 1 Select grip.**
G = Grip on first end only
Z = No grip
- 2 Select MTP PRO connector.**
(end one on outside of reel).
93 = MTP 12 F (pinned) multimode
89 = MTP 12 F (pinned) single-mode
- 3 Select MTP PRO connector.**
(end two on inside of reel).
75 = MTP 12 F (non-pinned) multimode
90 = MTP 12 F (non-pinned) single-mode

*For fiber counts above 144 F, the legs will be staggered starting at 33 in.

- 4 Select standard fiber count.**
12 = 12 fiber E4 = 144 fiber
24 = 24 fiber K2 = 192 fiber
36 = 36 fiber M6 = 216 fiber
48 = 48 fiber U8 = 288 fiber
72 = 72 fiber AK = 432 fiber
96 = 96 fiber AZ = 576 fiber

- 5 Select fiber type.**
T = 50 μm multimode (OM3)
Q = 50 μm multimode (OM4)
V = 50 μm multimode (OM5)
G = Single-mode Ultra (OS2)

- 6 Select cable type.**
PN = Plenum, non-armored
AD = Plenum, BX armored
**Armored cable only available for fiber counts less than or equal to 144 F.*

- 7 Defines leg length.**
(end one on outside of reel).
C = 60 in (+3.5/-1.0 in)*
Mates with trunk (long leg reaches from rear to the front side of housing)

- 8 Defines leg length.**
(end two on inside of reel).
D = 33 in (+3.5/-1.0 in)*
Mates with module/harness.

- 9 Defines trunk type.**
X = Extender

- 10 Select cable length.**
005-999 ft
(1ft increments measured from furcation to furcation)
002-300 m
(1 m increments measured from furcation to furcation)
Longer cable lengths available upon request.


- 11 Select unit of measure.**
F = Feet
M = Meters



EDGE Solutions Extender Trunk Cable Configuration | Drawing ZA-3869


Hybrid MTP® to LC Uniboot Trunks

EDGE™ MTP® to LC uniboot hybrid trunks combine non-pinned MTP PRO connectors, which connect to EDGE modules, and LC uniboot connectors, which connect directly to the electronics. These trunks enable additional options for cabling of data centers. All hybrid trunks are manufactured with Corning® CleanAdvantage™ technology and shipped with strain-relief clips to allow easy tool-less installation.



EDGE Hybrid MTP to LC Uniboot Trunks | Photo REN7796

Ordering Information



1 Select grip.

G = Grip on first end
Z = No grips

2 Select MTP PRO connector.

(end one on outside of reel).
75 = MTP 12 F (non-pinned) multimode
90 = MTP 12 F (non-pinned) single-mode

3 Select LC connector.

(end two on inside of reel).
79 = LC Uniboot multimode
78 = LC Uniboot single-mode

4 Select standard fiber count.

12 = 12 fiber 72 = 72 fiber
24 = 24 fiber 96 = 96 fiber
36 = 36 fiber E4 = 144 fiber
48 = 48 fiber

5 Select fiber type.

T = 50 μm multimode (OM3)
Q = 50 μm multimode (OM4)
V = 50 μm multimode (OM5)
G = Single-mode Ultra (OS2)

6 Select cable type.

PN = Plenum, non-armored
AD = Plenum, BX armored

7 Defines leg length.

(end one on outside of reel).
D = 33 in (+3.5/-1.0 in)*
Mates with module

8 Select leg length.

(end two on inside of reel).
K = 24 in (+3.5/-1.0 in)
L = 36 in (+3.5/-1.0 in)(standard)
M = 48 in (+3.5/-1.0 in)
N = 60 in (+3.5/-1.0 in)
P = 72 in (+3.5/-1.0 in)

9 Defines trunk type.

W = Universal hybrid trunk

10 Select cable length.


005-999 ft
(1 ft increments measured from furcation to furcation)

002-300 m
(1 m increments measured from furcation to furcation)

Longer cable lengths available upon request.

11 Select unit of measure.


F = Feet
M = Meters



EDGE Solutions Hybrid Trunk Configuration | Drawing ZA-3870


Hybrid MTP® to LC Uniboot Extender Trunks

EDGE™ MTP® to LC uniboot hybrid extender trunks combine pinned MTP PRO connectors, which connect to MTP trunks, and LC uniboot connectors, which connect directly to the electronics. These trunks enable additional options for cabling of data centers and are most often used in a zone distribution area (ZDA). All hybrid trunks are manufactured with Corning® CleanAdvantage™ technology.



EDGE Hybrid MTP to LC Uniboot Extender Trunk | Photo REN7796

Ordering Information



1 Select grip.

G = Grip on first end
Z = No grips

2 Select MTP PRO connector.

(end one on outside of reel).
93 = MTP 12 F (pinned) multimode
89 = MTP 12 F (pinned) single-mode

3 Select LC connector.

(end two on inside of reel).
79 = LC Uniboot multimode
78 = LC Uniboot single-mode

4 Select standard fiber count.

12 = 12 fiber 72 = 72 fiber
24 = 24 fiber 96 = 96 fiber
36 = 36 fiber E4 = 144 fiber
48 = 48 fiber

5 Select fiber type.

T = 50 μm multimode (OM3)
Q = 50 μm multimode (OM4)
V = 50 μm multimode (OM5)
G = Single-mode Ultra (OS2)

6 Select cable type.

PN = Plenum, non-armored
AD = Plenum, BX armored

7 Defines leg length.

(end one on outside of reel).
C = 60 in (+3.5/-1.0 in)*
Mates with trunk

8 Select leg length.

(end two on inside of reel).
K = 24 in (+3.5/-1.0 in)
L = 36 in (+3.5/-1.0 in)(standard)
M = 48 in (+3.5/-1.0 in)
N = 60 in (+3.5/-1.0 in)
P = 72 in (+3.5/-1.0 in)

9 Defines trunk type.

Z = Universal hybrid extender

10 Select cable length.


005-999 ft
(1 ft increments measured from furcation to furcation)

002-300 m
(1 m increments measured from furcation to furcation)

Longer cable lengths available upon request.

11 Select unit of measure.

F = Feet
M = Meters




EDGE Solutions Hybrid Extender Trunk Configuration | Drawing ZA-3871


EDGE™ MTP® Jumpers

EDGE™ MTP® jumpers are used to create a connection between MTP adapter panels, conversion modules, and electronics, typically providing connectivity within the rack or within the row. These plenum-rated cable assemblies feature a smaller (2.0 mm) outside diameter than traditional 12-fiber jumpers to improve finger access as well as reduce congestion and increase airflow in the horizontal and vertical rack space. EDGE 12-fiber MTP jumpers have the same connector size and cable footprint as LC duplex jumpers used today. The density, airflow, and cable management advantages of EDGE solutions is preserved as you migrate to higher data rates.

These jumpers are manufactured using Corning® CleanAdvantage™ technology and shipped with optimized dust caps, eliminating the need for cleaning and scoping prior to the initial field connection. They are built with MTP® PRO connectors, allowing for a simple one-step color-coded polarity change without removing the connector housing. The connector also provides the capability for field-friendly pinning configuration changes with safe handling of pins and easy color identification while maintaining product integrity.



EDGE MTP Jumper | Photo REN7928



EDGE MTP Jumper | Drawings ZA-3866 and ZA-3868

Ordering Information

* J 12 E 8 - N

1
2
3
4
5
6
7
8

**For custom labels, add the letter "L" as prefix to the part number e.g., LJ757512QE8-NBxxxF*

Print for custom labels can be up to 30 characters. Information to be printed on custom labels must be provided at the time of order.

- 1 Select MTP® PRO connector.**
 75 = MTP 12 F (non-pinned) multimode
 93 = MTP 12 F (pinned) multimode
 89 = MTP 12 F (pinned) single-mode
 90 = MTP 12 F (non-pinned) single-mode

- 2 Select MTP PRO connector.**
 75 = MTP 12 F (non-pinned) multimode
 93 = MTP 12 F (pinned) multimode
 89 = MTP 12 F (pinned) single-mode
 90 = MTP 12 F (non-pinned) single-mode

- 3 Select fiber type.**
 T = 50 μm multimode (OM3)
 Q = 50 μm multimode (OM4)
 V = 50 μm multimode (OM5)
 G = Single-Mode Ultra (OS2)

- 4 Defines cable type.**
 E8 = Plenum, interconnect

- 5 Select jumper.**
 N = Jumper, no furcation

- 6 Select polarity.**
 A = TIA-568 Type-A
 B = TIA-568 Type-B

Note: For jumper polarity, reference [AEN151](#).


- 7 Select jumper length.**
 003-200 ft
(Measured in 1 ft increments)
 001-060 m
(Measured in 1 m increments)

- 8 Select unit of measure.**
 F = Feet
 M = Meters

Note: Always list lowest numbered connector first.

EDGE™ MTP® 24-F Jumpers

EDGE™ 24-fiber MTP jumpers allow for seamless migration to 100G when used in direct-connect architectures between electronics. The assemblies are plenum-rated and feature a 3.3 mm outside diameter. Multimode 24-fiber jumpers are manufactured with Corning® CleanAdvantage™ technology and shipped with optimized dust caps.



EDGE 24-F MTP Jumper | Photo LAN4167

Ordering Information

| | | | | | | | | | | | | | | |
|---|----------------------|----------------------|----------------------|----------------------|----|----------------------|----|---|----------|----------|----------------------|----------------------|----------------------|----------------------|
| J | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | 24 | <input type="text"/> | PH | - | N | A | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| | 1 | 2 | | 3 | | 4 | | | 5 | 6 | | 7 | 8 | |

- | | | |
|--|---|---|
| <p>1 Select MTP® connector. A6 = MTP 24 F (non-pinned) multimode A9 = MTP 24 F (non-pinned) single-mode</p> <p>2 Select MTP connector. A6 = MTP 24 F (non-pinned) multimode A9 = MTP 24 F (non-pinned) single-mode</p> | <p>3 Select fiber type. T = 50 μm multimode (OM3) Q = 50 μm multimode (OM4) G = Single-mode Ultra (OS2)</p> <p>4 Defines cable type. PH = Plenum, micro-module</p> <p>5 Defines jumper. N = Jumper, no furcation</p> | <p>6 Select polarity. A = Type-A, polarity</p> <p>7 Select jumper length. 003-200 ft (Measured in 1 ft increments) 001-060 m (Measured in 1 m increments)</p> <p>8 Select unit of measure. F = Feet M = Meters</p> |
|--|---|---|

Note: Refer to [AEN150](#) for application guidance.

EDGE™ Harnesses

One of the critical challenges facing data center owners, operators, and maintenance personnel in high-density (HD) computing areas is how to provide high-port-concentration deployments to support the latest generation of high-speed switches without losing them under a mass of jumpers.

EDGE™ staggered and nonstaggered harnesses are ultra-slim 12-fiber preterminated cable with an MTP® PRO connector on one end and six LC uniboot connectors on the other. The majority of the harness is a single cable which breaks out into six, 2-fiber legs to enable connectivity to the switch ports. Stagger options replicate the specific switch ports to save on excess cable length. MTP PRO allows for a simple one-step color-coded polarity change feature without removing the connector housing. The connector also provides the capability for field-friendly pinning configuration changes with safe handling of pins and easy color identification while maintaining product integrity.

Specially designed harnesses are available for numerous distribution switches including Cisco, Arista, Brocade, Juniper, and HP using SFP+ (LC interfaces) for Ethernet or Fiber Channel with duplex transmission for port mirroring, aggregation, fabric, or breakout applications.

EDGE conversion harnesses and 24-fiber harnesses ensure 100% trunk fiber utilization at 40 and 100G. These solutions allow for design flexibility with various breakout configurations to meet your connectivity needs. EDGE Tap harnesses, in conjunction with EDGE Tap modules, offer a network monitoring solution that integrates directly into the EDGE structured cabling footprint, with increased rack space utilization and density.

Features and Benefits

Slim, round 2-fiber interconnect cable

Improves airflow and reduces congestion.

MTP PRO Connector and Push-Pull Boot

Allows for pinning and polarity changing in the field while enabling easier mating and unmating in extremely dense applications.

Low-loss connectivity

Enables system design flexibility.

Bend-improved fiber

Allows tighter cable bends for slack storage and routing, less risk of downtime due to pinched or bent cables.

Corning® CleanAdvantage™ technology and optimized dust caps

Eliminates the need for scoping and cleaning prior to initial field connection.

Conversion harnesses transition connectivity from 12 to 8 fibers


Ensures 100% utilization of trunks at 40 and 100G.



EDGE MTP to LC Uniboot Harness, nonstaggered | Photo REN7795



EDGE 2x3 Conversion Harness | Photo REN7929



EDGE Staggered Harness Offerings

EDGE™ MTP® to LC Uniboot Staggered Harnesses

EDGE™ MTP® to LC uniboot staggered harnesses provide breakout from 12-fiber MTP® PRO connectors to LC uniboot connectors. These harnesses are available in five stagger configurations to meet various port-replication needs.

The EDGE module harness is designed to create a cross-connect point near the electronics by enabling port replication. This harness uses LC uniboot connectors to interface with the electronics and a non-pinned MTP PRO connector to connect into the back of a module. With port replication, the installation will look the same even after multiple moves, adds, and changes (MACs). This solution can be used in a horizontal distribution area (HDA).

The EDGE trunk harness is designed to facilitate an interconnect point when the electronics are located in a separate area than the cross-connect or patching field. This harness uses LC uniboot connectors to interface with the electronics and a pinned MTP PRO connector to connect into a trunk. This solution can be used in an equipment distribution area (EDA).



EDGE MTP to LC Uniboot Staggered Harnesses | Photo REN7933

Ordering Information

| | | | | | | | | | | | |
|---|----------------------|----------------------|----------|----------------------|----------|----------|----------------------|----------------------|----------------------|----------------------|----------------------|
| H | <input type="text"/> | <input type="text"/> | 12 | <input type="text"/> | PH | - | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | | | |

- 1 Select MTP PRO connector.**
 75 = MTP 12 F (non-pinned) multimode
 93 = MTP 12 F (pinned) multimode
 89 = MTP 12 F (pinned) single-mode
 90 = MTP 12 F (non-pinned) single-mode

- 2 Select the breakout connector type.**
 79 = LC uniboot multimode
 78 = LC uniboot single-mode
LCs are universally wired.

- 3 Select fiber type.**
 T = 50 μm multimode (OM3)
 Q = 50 μm multimode (OM4)
 V = 50 μm multimode (OM5)
 G = Single-Mode Ultra (OS2)

- 4 Defines cable type.**
 PH = Plenum, harness

- 5 Select leg length in inches.**
 (leg OD is 2.0 mm).
 1 = Type 1 Stagger
 2 = Type 2 Stagger
 3 = Type 3 Stagger
 4 = Type 4 Stagger (uniform)
 5 = Type 5 Stagger

Note: For harness stagger type, reference [AEN157](#).

- 6 Select harness polarity.**
 A = Type-A
 B = Type-B

- 7 Select harness length.**
 003-020 ft
(1 ft increments measured from plug to MTP, does not include LC stagger)
 001-006 m
(1 m increments measured from plug to MTP, does not include LC stagger)

- 8 Select unit of measure.**
 F = Feet
 M = Meters

*An EDGE harness should have **Type-A polarity** and a **pinned MTP PRO** connector when connecting to a **trunk**.
 An EDGE harness should have **Type-B polarity** and a **non-pinned MTP PRO** connector when connecting to a **module**.
 Harness length is measured from MTP connector to furcation plug and therefore does not include LC leg length.*

EDGE™ MTP® to LC Uniboot Nonstaggered Harnesses

EDGE™ MTP® to LC uniboot nonstaggered harnesses provide breakout from 12-fiber MTP® PRO connectors to LC uniboot connectors. These harnesses come with nonstaggered legs in several length options.

The EDGE module harness is designed to create a cross-connect point near the electronics by enabling port replication. This harness uses LC uniboot connectors to interface with the electronics and a non-pinned MTP PRO connector to connect into the back of a module. With port replication, the installation will look the same even after multiple moves, adds, and changes (MACs). This solution can be used in a horizontal distribution area (HDA).

The EDGE trunk harness is designed to facilitate an interconnect point when the electronics are located in a separate area than the cross-connect or patching field. This harness uses LC uniboot connectors to interface with the electronics and a pinned MTP PRO connector to connect into a trunk. This solution can be used in an equipment distribution area (EDA).



EDGE MTP to LC Uniboot Nonstaggered Harnesses | Photo REN7795

Ordering Information

| | | | | | | | | | | | | | | |
|---|----------------------|----------------------|----------------------|----------------------|----|----------------------|----|---|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|
| H | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | 12 | <input type="text"/> | PH | - | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| | 1 | 2 | | 3 | | 4 | | | 5 | 6 | | 7 | 8 | |

- 1 Select MTP PRO connector.**
 75 = MTP 12 F (non-pinned) multimode
 93 = MTP 12 F (pinned) multimode
 89 = MTP 12 F (pinned) single-mode
 90 = MTP 12 F (non-pinned) single-mode

- 2 Select the breakout connector type.**
 79 = LC uniboot multimode
 78 = LC uniboot single-mode
LCs are universally wired.

- 3 Select fiber type.**
 T = 50 μm multimode (OM3)
 Q = 50 μm multimode (OM4)
 V = 50 μm multimode (OM5)
 G = Single-Mode Ultra (OS2)

- 4 Defines cable type.**
 PH = Plenum, harness

- 5 Select leg length in inches.**
 (leg OD is 2.0 mm).
 J = 12 in (+3.5/-1.0 in)
 K = 24 in (+3.5/-1.0 in)
 L = 36 in (+3.5/-1.0 in)
 M = 48 in (+3.5/-1.0 in)
 N = 60 in (+3.5/-1.0 in)
 P = 72 in (+3.5/-1.0 in)
 R = 98 in (+3.5/-1.0 in)

Furcation legs are color code by fiber type.

- 6 Select harness polarity.**
 A = Type-A
 B = Type-B

- 7 Select harness length.**
 003-200 ft
(1 ft increments measured from plug to MTP, does not include leg length)
 001-060 m
(1 m increments measured from plug to MTP, does not include leg length)


- 8 Select unit of measure.**
 F = Feet
 M = Meters

An EDGE harness should have **Type-A polarity** and a **pinned MTP PRO** connector when connecting to a **trunk**.
 An EDGE harness should have **Type-B polarity** and a **non-pinned MTP PRO** connector when connecting to a **module**.
 Harness length is measured from MTP connector to furcation plug and therefore does not include LC leg length.

EDGE™ Conversion Harnesses

EDGE™ conversion harnesses are plenum-rated preterminated harnesses that provide conversion from 12- to 8-fiber connectivity for full-fiber utilization. These harnesses are offered as a 2x3 MTP® harness (two 12-fiber MTP® PRO connectors on one end, three 8-fiber MTP PRO connectors on the other) for connection to electronics with MPO-style ports

EDGE conversion harnesses are a TIA-568 Type-A component. They are manufactured with Corning® CleanAdvantage™ technology and shipped with optimized dust caps, eliminating the need for scoping and cleaning prior to initial field connection.



EDGE 2x3 Conversion Harness | Photo REN7929

Ordering Information

| |
|---|
| H 9 3 7 5 2 4 P H - A F |
| 1 2 3 4 |

- 1** Select fiber type.

 - T = 50 μm multimode (OM3)
 - Q = 50 μm multimode (OM4)
- 3** Select the 8-fiber MTP connector leg length in inches (leg OD is 2.6 mm).

 - K = 24 in (+3.5/-1.0 in)
 - L = 36 in (+3.5/-1.0 in)
- 4** Select harness length in feet (does not include leg length).


 - 003-200 ft
 - (1ft increments measured from plug to plug, does not include leg length)*

Note: Refer to [AEN151](#) for application information.

EDGE™ 24-Fiber “Y” Harnesses

EDGE™ solutions 24-fiber “Y” harnesses are plenum-rated preterminated assemblies that provide conversion from 24- to 12-fiber connectivity for full-fiber utilization of an existing Base-12 backbone. These harnesses are offered as a 1x2 MTP® assembly (one 24-fiber MTP connector on one end, two 12-fiber MTP® PRO connectors on the other), creating the connection from the patch panel to 20-fiber/24-fiber switch ports.

Multimode 24-fiber “Y” harnesses are manufactured with Corning® CleanAdvantage™ technology.



EDGE 24-Fiber “Y” Harness | Photo REN7941

Ordering Information

| | | | | | | | | | | | | | | |
|---|----------------------|----------------------|----------------------|----------------------|----|----------------------|----------|---|----------------------|----------------------|----------------------|----------------------|----------------------|---|
| H | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | 24 | <input type="text"/> | PH | - | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | F |
| | 1 | 2 | 3 | 4 | | 5 | 6 | | 7 | | | | | |


- 1 Select 24-fiber MTP connector.**
A6 = MTP 24 F (non-pinned) multimode
A9 = MTP 24 F (non-pinned) single-mode
- 2 Select 12-fiber MTP PRO connector.**
75 = MTP 12 F (non-pinned) multimode
93 = MTP 12 F (pinned) multimode
89 = MTP 12 F (pinned) single-mode
90 = MTP 12 F (non-pinned) single-mode
- 3 Select fiber type.**
Q = 50 μm multimode (OM4)
G = Single-Mode Ultra (OS2)
- 4 Defines cable type.**
PH = Plenum, harness
- 5 Select leg length in inches.**
K = 24 in
L = 36 in
- 6 Select polarity.**
6 = Type-6 polarity
7 = Type-7 polarity
8 = Type-8 polarity
9 = Type-9 polarity
Z = Type-Z polarity

Refer to [AEN150](#) for application and polarity information.
- 7 Select harness length.**
003-200 ft
(1 ft increments measured from plug to MTP, does not include leg length)

Notes:
 Type-6 and Type-7 polarity are only available with Non-Pinned 12-fiber MTP PRO for connector 2.
 Type-Z, Type-8, and Type-9 polarity are only available with Pinned 12-fiber MTP PRO for connector 2.
 Type-6 and Type-8 polarity are only available for multimode.

EDGE™ 24-Fiber MTP® Breakout Harnesses

EDGE™ solutions 24-fiber MTP® breakout harnesses are plenum-rated preterminated harnesses that provide conversion from 24- to 8-fiber connectivity. These harnesses are offered as a 1x3 MTP assembly (one 24-fiber MTP connector on one end, three 8-fiber MTP® PRO connectors on the other), allowing for connectivity between the 24-fiber switch ports to three 8-fiber ports. These harnesses can be used to breakout 24-fiber ports using Base-8 structured cabling. The MTP breakout harness is also available as a 20-fiber 1x10 assembly with one 24-fiber MTP on one end and (10) 2-fiber LC duplex connectors on the other.



EDGE 24-Fiber MTP Breakout Harness | Photo REN7937

Multimode 24-fiber breakout harnesses are manufactured with Corning® CleanAdvantage™ technology.

Ordering Information



1 Select 24-fiber MTP connector.
 A6 = MTP 24 F (non-pinned) multimode
 A9 = MTP 24 F (non-pinned) single-mode

2 Select breakout connector.
 05 = LC Duplex multimode
 04 = LC Duplex single-mode
 75 = MTP 12 F (non-pinned) multimode
 93 = MTP 12 F (pinned) multimode
 89 = MTP 12 F (pinned) single-mode
 90 = MTP 12 F (non-pinned) single-mode

3 Select fiber count.
 24 = 24 fiber
 20 = 20 fiber
20 fiber only available for LC duplex breakout connectors

4 Select fiber type.
 Q = 50 μm multimode (OM4)
 G = Single-mode Ultra (OS2)

5 Defines cable type.
 PH = Plenum, harness

6 Select breakout leg length.
 K = 24 in
 L = 36 in

7 Select polarity.
 A = Type-A polarity
 B = Type-B polarity
Refer to [AEN150](#) and [AEN156](#) for application and polarity information.

8 Select harness length.
 003-200 ft
(1 ft increments measured from plug to MTP, does not include leg length)

EDGE™ Tap Harnesses

The EDGE™ Tap harness is used to breakout the 12-fiber MTP® tap port at the rear of the EDGE Tap module into LC duplex connectors. These duplex connectors then can be easily separated into simplex connectors to plug into monitoring electronics.

The use of harnesses provides a solution that occupies less space than traditional jumpers, as the cable end of the harness is much smaller than the size of equivalent jumpers. This reduced cabling bulk improves airflow for increased cooling and facilitates easier moves, adds, and changes (MACs).

The MTP® PRO connector allows for pinning and polarity changes in the field.



EDGE Tap Harness | Photo REN7939

Ordering Information

| | | | | | | | | | | | | | |
|---|----------------------|----------------------|----------------------|----|----------------------|-----|---|----------------------|---|----------------------|----------------------|----------------------|----------------------|
| H | <input type="text"/> | <input type="text"/> | <input type="text"/> | 12 | <input type="text"/> | E 8 | - | <input type="text"/> | B | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| | 1 | 2 | | | 3 | | | 4 | | 5 | | | 6 |

- 1 Select MTP PRO connector.**
 75 = MTP 12 F (non-pinned) multimode
 90 = MTP 12 F (non-pinned) single-mode

- 2 Select the LC connector.**
 03 = LC Simplex multimode
 02 = LC UPC Simplex single-mode

- 3 Select fiber type.**
 Q = 50 μm multimode (OM4)
 G = Single-mode Ultra (OS2)

- 4 Select leg length in inches. (leg OD is 2.0 mm).**
 J = 12 in (+3.5/-1.0 in)
 K = 24 in (+3.5/-1.0 in)
 L = 36 in (+3.5/-1.0 in)


- 5 Select harness length.**
 003-200 ft
(1 ft increments measured from plug to MTP, does not include leg length)
 001-060 m
(1 m increments measured from plug to MTP, does not include leg length)

- 6 Select unit of measure.**
 M = Meters
 F = Feet

Note: Refer to [AEN164](#) for application information.

EDGE8® MTP® to LC Harnesses

The EDGE8® MTP® to LC uniboot harness is for connection to electronics with LC-style ports and for use in aggregation of 10G ports to a 40G port. These harnesses have a pinned or non-pinned MTP PRO connector on one end and four LC uniboot connectors on the other. These harnesses are uniquely wired to manage polarity within and maintain transmit-to-receive connectivity.



EDGE8 Harness | Photo REN7931

Ordering Information

| | | | | | | | | | | | | |
|---|----------------------|----------------------|----------|----|----------------------|----|---|----------------------|----------------------|----------------------|----------------------|----------------------|
| H | <input type="text"/> | <input type="text"/> | 79 | 08 | <input type="text"/> | PH | - | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| | 1 | 2 | 3 | | 4 | | | 5 | 6 | | 7 | 8 |

1 Select MTP PRO Connector
 E5 = MTP 8 F (pinned) multimode
 E6 = MTP 8 F (non-pinned) multimode

2 Select the breakout connector type.
 79 = LC uniboot multimode
LCs are universally wired

3 Select fiber type.
 T = 50 μ m multimode (OM3)
 Q = 50 μ m multimode (OM4)

4 Defines cable type.
 PH = Plenum, harness

5 Select leg length in inches. (leg OD is 2.0 mm).
 J = 12 in (+3.5/-1.0 in)
 K = 24 in (+3.5/-1.0 in)
 L = 36 in (+3.5/-1.0 in)
 M = 48 in (+3.5/-1.0 in)
 N = 60 in (+3.5/-1.0 in)
 P = 72 in (+3.5/-1.0 in)
 R = 98 in (+3.5/-1.0 in)

6 Defines harness polarity.
 A = Type-A polarity
 B = Type-B polarity
Note: For harness polarity, reference [AEN152](#).

7 Select harness length.
 003-200 ft
(1 ft increments measured from plug to MTP, does not include leg length)
 001-060 m
(1 m increments measured from plug to MTP, does not include leg length)

8 Select unit of measure.
 F = Feet
 M = Meters

Preloaded EDGE Hardware

By preloading EDGE™ modules into the housings at the factory prior to shipping, Corning can offer reduced packaging, reduced shipping and storage space, as well as speed up the hardware mounting and installation time for the customer.



Preloaded EDGE Housings | Photo CRR6167

Features and Benefits

Multiple preloaded housing configurations available: fully populated, half populated, and serialized custom configurations

Requires 50% less storage space when compared to individual housings and modules

55% lighter packaging

Less packaging means fewer trips to the dumpster or recycling bin – saving valuable time on the jobsite

Preloaded with proven EDGE technology for fast, simple, and reliable installation

| Ordering Information | | | |
|----------------------|---|--------------|-------------|
| Part Number | Configuration Description | Housing Size | Module Type |
| EG01-UM0489G-04 | EDGE-01U Preloaded with 4 single-mode modules | EDGE-01U | SM |
| EG01-UM0489G-08 | EDGE-01U Preloaded with 8 single-mode modules | EDGE-01U | SM |
| EG01-UM0593Q-04 | EDGE-01U Preloaded with 4 multimode modules | EDGE-01U | OM4 |
| EG01-UM0593Q-08 | EDGE-01U Preloaded with 8 multimode modules | EDGE-01U | OM4 |
| EG1S-UM0489G-06 | EDGE-01U-SP Preloaded with 6 single-mode modules | EDGE-01U-SP | SM |
| EG1S-UM0489G-12 | EDGE-01U-SP Preloaded with 12 single-mode modules | EDGE-01U-SP | SM |
| EG1S-UM0593Q-06 | EDGE-01U-SP Preloaded with 6 multimode modules | EDGE-01U-SP | OM4 |
| EG1S-UM0593Q-12 | EDGE-01U-SP Preloaded with 12 multimode modules | EDGE-01U-SP | OM4 |
| EG02-UM0489G-12 | EDGE-02U Preloaded with 12 single-mode modules | EDGE-02U | SM |
| EG02-UM0489G-24 | EDGE-02U Preloaded with 24 single-mode modules | EDGE-02U | SM |
| EG02-UM0593Q-12 | EDGE-02U Preloaded with 12 multimode modules | EDGE-02U | OM4 |
| EG02-UM0593Q-24 | EDGE-02U Preloaded with 24 multimode modules | EDGE-02U | OM4 |
| EG04-UM0489G-24 | EDGE-04U Preloaded with 24 single-mode modules | EDGE-04U | SM |
| EG04-UM0489G-48 | EDGE-04U Preloaded with 48 single-mode modules | EDGE-04U | SM |
| EG04-UM0593Q-24 | EDGE-04U Preloaded with 24 multimode modules | EDGE-04U | OM4 |
| EG04-UM0593Q-48 | EDGE-04U Preloaded with 48 multimode modules | EDGE-04U | OM4 |

For custom configurations not listed, contact engineer.en.americas@corning.com

EDGE™ Modules

EDGE™ modules provide the interface between the MTP® connector on the trunk and the LC duplex jumpers that connect directly into the electronics. LC duplex adapters on EDGE modules feature hinged VFL-compatible shutters that move up and out of the way when the connector is inserted. Specially designed indents in the shutters ensure that the end faces of the connectors are never touched. These shutters replace the standard dust caps that are typically never replaced after initial removal, exposing the interior end faces to dust particles and possible damages.

EDGE conversion modules ensure 100% trunk fiber utilization at 40 and 100G. These solutions allow for design flexibility with various breakout configurations to meet your connectivity needs.

Features and Benefits

Shuttered LC adapters

Creates one-hand operation while eliminating the need to remove and store dust caps.

VFL-compatible shutters

Decreases time needed to test and troubleshoot a link.

Rear-loading capability

Reduces the time to prepare and install modules into fiber housings.

High density

Enables 576 fibers in a 4U housing and 144 fibers in a 1U.

Low insertion loss performance

Improved performance specs allow for more mated pairs and/or longer link distance.

Universal wiring

Decreases complexity and risks associated with managing polarity during moves, adds, and changes.

Corning® CleanAdvantage™ technology and optimized dust caps


Eliminates the need for scoping and cleaning prior to initial field connection (excludes mesh modules and Tap modules).

Conversion modules transition connectivity from 12 to 8 fibers

Ensures 100% utilization of trunks at 40 and 100G.

Conversion modules offer the industry's best rack density for parallel optics

72 MTP ports per 1U enable higher-revenue generation per rack unit.



EDGE MTP to LC Module | Photo REN6521




EDGE Conversion Module | Photo REN7071

Low-Loss Modules

EDGE™ low-loss modules provide an interface between the MTP® connector on an MTP trunk and the LC duplex jumpers that connect directly to the electronics. These modules feature VFL-compatible LC shuttered adapters and are manufactured with Corning® CleanAdvantage™ technology.

They are specified to 0.5 dB for multimode (OM3/OM4/OM5) and 1.0 dB for single-mode (OS2).



EDGE Module | Photo REN6521

Ordering Information



1 Select polarity.
 UM = Universal polarity
 RM = Straight-through

2 Defines fiber count.
 12 = 12 fibers

3 Select adapters on module front.
 05 = Shuttered LC duplex multimode
 04 = Shuttered LC UPC duplex single-mode
 18 = Shuttered LC APC duplex single-mode

4 Select MTP adapter on the back of the module.
 93 = MTP 12 F (pinned) multimode
 89 = MTP 12 F (pinned) single-mode

5 Select fiber type.
 T = 50 μm multimode (OM3)
 Q = 50 μm multimode (OM4)
 V = 50 μm multimode (OM5)
 G = Single-mode Ultra (OS2)

6 Defines modules.
 Z - 4 pack
 *Leave blank for single pack

*Note: If you leave this blank you will get a single module

EDGE™ Conversion Modules


EDGE™ conversion modules have 12-fiber MTP® adapters in the rear for mating to backbone trunks and breakout to 8-fiber MTP adapters in the front for connectivity to electronics. These conversion modules fully utilize all fibers in each Base-12 set in the trunk by breaking out Base-12 MTP adapters at the rear of the module into a proportionate number of Base-8 MTP adapters at the front.

EDGE conversion modules are available in two configurations: 2x3 (two 12-fiber MTP adapters in the rear and three 8-fiber MTP adapters in the front) and 4x6 (four adapters in the rear and six in the front)

These modules come from the factory as a TIA-568 Type-B component. However, EDGE conversion modules also offer on-site MTP connectivity changes to manage field polarity. The front of the module features reversible translucent shuttered adapters. These modules are manufactured with Corning® CleanAdvantage™ technology and shipped with optimized dust caps on the rear side of the module.



EDGE 2x3 Conversion Module | Photo REN7106



EDGE 4x6 Conversion Module | Photo REN7071


Ordering Information

| Part Number | Adapter Type Front | Adapter Color Front | Adapter Type Back | Fiber Category |
|-----------------|--------------------|---------------------|-------------------|----------------|
| ECM-UM24-93-93Q | Shuttered MTP | Aqua | MTP | 50 μm MM (OM4) |
| ECM-UM48-93-93Q | Shuttered MTP | Aqua | MTP | 50 μm MM (OM4) |

Note: For application reference, please refer to [AEN150](#), [AEN151](#), and [AEN152](#)

EDGE™ Mesh Modules

EDGE™ 4x4 mesh modules are used to break out four-channel parallel ports to create a duplex fabric, eliminating the need to break the MTP® into LC connectivity. The mesh modules contain four 8-fiber MTPs in the rear for mating to backbone trunks and break out to four 8-fiber MTPs in the front for connectivity to the electronics. These modules allow customers to take advantage of higher port densities per switch with lower power consumption and a lower cost per 10G port. They also improve their ability to create port diversification when using QSFP+ transceivers for 10G applications.



EDGE Multimode Mesh Module | Photo REN890



EDGE Single-Mode Mesh Module | Photo REN899


Ordering Information

| Part Number | Adapter Type Front | Adapter Color Front | Adapter Type Back | Fiber Category |
|----------------|------------------------|---------------------|-------------------|-----------------------|
| EMM-MM32-9393Q | Shuttered MTP (pinned) | Aqua | MTP (Pinned) | 50 µm Multimode (OM4) |
| EMM-MM32-9375Q | Shuttered MTP (pinned) | Aqua | MTP (Non-pinned) | 50 µm Multimode (OM4) |
| EMM-SM32-8989G | Shuttered MTP (pinned) | Black | MTP (Pinned) | Single-mode (OS2) |
| EMM-SM32-8990G | Shuttered MTP (pinned) | Black | MTP (Non-pinned) | Single-mode (OS2) |

Ultra-Low-Loss Modules


EDGE™ ultra-low-loss modules provide an interface between the MTP® connector on an MTP trunk and the LC duplex jumpers that connect directly to the electronics. These modules allow for extended-reach capabilities in high-speed serial duplex transmission. They feature VFL-compatible LC shuttered adapters and are manufactured with Corning® CleanAdvantage™ technology.

The OM3/OM4/OM5 EDGE ultra-low-loss modules are specified to 0.35 dB compared to 0.5 dB for the low-loss EDGE module. The OS2 EDGE ultra-low-loss modules are specified to 0.60 dB compared to 1.0 dB for the standard EDGE module.



EDGE Module | Photo REN6521

Ordering Information



1 Select polarity.
UM = Universal polarity
RM = Straight-through

2 Defines fiber count.
12 = 12 fibers

3 Select adapters on module front.
05 = Shuttered LC duplex multimode
04 = Shuttered LC UPC duplex single-mode
18 = Shuttered LC APC duplex single-mode

4 Select MTP adapter on the back of the module.
93 = MTP 12 F (pinned) multimode
89 = MTP 12 F (pinned) single-mode

5 Select fiber type.
T = 50 μm multimode (OM3)
Q = 50 μm multimode (OM4)
V = 50 μm multimode (OM5)
G = Single-mode Ultra (OS2)

6 Defines modules.
Z - 4 pack
*Leave blank for single pack


*Note: If you leave this blank you will get a single module

EDGE™ SE Splice Cassettes

The EDGE™ SE Solution is an innovative field-termination addition to the award-winning EDGE solution for high-density data center cabling infrastructure systems. The integral termination cassette allows for a wide range of fiber termination options without sacrificing any of the density, cable management, or ease of handling of the broader EDGE solutions family.

The EDGE SE solution can accommodate fusion splicing or direct termination. The cassette features LC duplex adapters with integrated dust caps that provide protection for the internal connectors and a translucent finish for ease of fiber identification. The cable entry in the rear of the cassette allows for multiple cable options from loose tube cable designs to tight-buffered cables. Combining the adapters, strain-relief, and splice organizers together in the cassette allows for superior fiber handling and safety of terminated fibers giving greater flexibility and confidence in Day 2 moves, adds, and changes (MACs).

With the ability to add fibers in building blocks of 12, the modular nature of EDGE solutions with EDGE SE cassettes is ideal for “pay-as-you-grow” applications. Solutions featuring EDGE SE cassettes make system changes where fibers are continuously added through a product or data center’s lifetime, such as colocation meet-me rooms or customer access point, more convenient.



EDGE Splice Cassette, 12 Fibers, LC Duplex, OS2 | Photo LAN4219

EDGE™ Multi-Splice Cassettes

The preloaded multi-splice cassettes accommodate fusion splicing and come with 12 colored LC pigtails (Telcordia color code), heat-shrink or crimp splice organizers and accept loose tube or tight-buffered cables for termination of multiple fiber optic cable types.

Low-loss connectivity enables system design flexibility, and the integrated LC duplex adapters across the front provide dust protection with VFL-safe translucent, inward-folding shutters.

The cassettes can install quickly from the front or rear of the housing, all steps can be performed from one side of a cabinet row (cable attach, buffer tube routing, module insertion) and enable a pay-as-you-grow approach.



Splice Cassette, 12 F, LC Duplex, OM4 | Photo LAN4849




Optical Performance

| | Module Insertion Loss, Max | Operating Temperature |
|-------------|----------------------------|-----------------------|
| SE cassette | ≤ 0.5 dB | -20°C to 60°C |

Ordering Information

| Part Number | Polarity | Adapter Type Front | Adapter Color Front | Fiber category | Splice Protection |
|------------------------|-----------|--------------------|---------------------|----------------|-------------------|
| EDGE-CS12-AD-P00QE | Telcordia | Shuttered LC | Aqua | 50 µm MM (OM4) | Heat-shrink |
| EDGE-CS12-AE-P00RE | Telcordia | Shuttered LC | Blue UPC | SM (OS2) | Heat-shrink |
| EDGE-CS12-AF-P00RE | Telcordia | Shuttered LC | Green APC | SM (OS2) | Heat-shrink |
| EDGE-CS12-AD-P00QE-CSP | Telcordia | Shuttered LC | Aqua | 50 µm MM (OM4) | Crimp |
| EDGE-CS12-AE-P00RE-CSP | Telcordia | Shuttered LC | Blue UPC | SM (OS2) | Crimp |
| EDGE-CS12-AF-P00RE-CSP | Telcordia | Shuttered LC | Green APC | SM (OS2) | Crimp |

For OM4 heather violet, please use AV connector code.

| Part Number | Product Description | Units Per Delivery | |
|-------------|---|--------------------|---|
| CAB-TT-TOOL | Zipper Tool (cutting transition tubes and feeding in the fiber) | 1/1 |  |
| CAB-TT-050M | Set with 50 m of transition tubes | 1/1 |  |
| CAB-TC | Tube Connectors (24 x 1-1, 2-1, 3-1) | 1/1 |  |

EDGE™ Trunk Splice Cassettes

The preloaded multi-splice cassettes accommodate fusion splicing and come with 12 colored LC pigtails (Telcordia color code), heat-shrink or crimp splice organizers and accept loose tube or tight-buffered cables for termination with EDGE™ trunk cables.

Low-loss connectivity enables system design flexibility, and the integrated LC duplex adapters across the front provide dust protection with VFL-safe translucent, inward-folding shutters.

The cassettes can install quickly from the front or rear of the housing, all steps can be performed from one side of a cabinet row (cable attach, buffer tube routing, module insertion) and enable a pay-as-you-grow approach.



Splice Cassette, 12 F, LC Duplex, OS2 APC | Photo LAN4852

Optical Performance

| | Module Insertion Loss, Max | Operating Temperature |
|-------------|----------------------------|-----------------------|
| SE cassette | ≤ 0.5 dB | -20°C to 60°C |

Ordering Information

| Part Number | Polarity | Adapter Type Front | Adapter Color Front | Fiber category | Splice Protection |
|------------------------|-----------|---------------------|---------------------|----------------|-------------------|
| EDGE-CS12-AD-P00QU | Universal | Shuttered LC Duplex | Aqua | 50 µm MM (OM4) | Heat-shrink |
| EDGE-CS12-AE-P00RU | Universal | Shuttered LC Duplex | Blue UPC | SM (OS2) | Heat-shrink |
| EDGE-CS12-AF-P00RU | Universal | Shuttered LC Duplex | Green APC | SM (OS2) | Heat-shrink |
| EDGE-CS12-AD-P00QM-CSP | Universal | Shuttered LC Duplex | Aqua | 50 µm MM (OM4) | Crimp |
| EDGE-CS12-AE-P00RM-CSP | Universal | Shuttered LC Duplex | Blue UPC | SM (OS2) | Crimp |
| EDGE-CS12-AF-P00RM-CSP | Universal | Shuttered LC Duplex | Green APC | SM (OS2) | Crimp |

For OM4 heather violet, please use AV connector code.

EDGE™ SE Field-Term Cassettes (empty)

Simplified for and increased confidence in handling, the empty cassettes allow termination of fibers through the integration of cable strain-relief, accommodating UniCam® or anaerobic connectors for direct connector termination. Low-loss connectivity enables system design flexibility, and the integrated LC duplex adapters across the front provide dust protection with VFL-safe translucent, inward-folding shutters.

The cassettes can install quickly from the front or rear of the housing, all steps can be performed from one side of a cabinet row (cable attach, buffer tube routing, module insertion) and enable a pay-as-you-grow approach.



Cassette, LC Duplex, OM4
| Photo LAN4850



Cassette, LC Duplex, OS2
| Photo LAN4851



Cassette, LC Duplex, OS2 APC
| Photo LAN4853

Ordering Information

| Part Number | Adapter Type Front | Adapter Color Front | Fiber Category |
|--------------|--------------------|---------------------|----------------|
| EDGE-CS12-AD | Shuttered LC | Aqua | 50 μm MM (OM4) |
| EDGE-CS12-AE | Shuttered LC | Blue UPC | SM (OS2) |
| EDGE-CS12-AF | Shuttered LC | Green APC | SM (OS2) |

Solution Configuration for EDGE Housings

| Part Number | Height Unit | Number of 1/10G Ports, MM/SM | Number of 40GBASE-LR4 Ports, only SM | Number of 100GBASE-LR4 Ports, only SM | Number of Modules | Fiber Capacity |
|-------------|-------------|------------------------------|--------------------------------------|---------------------------------------|-------------------|----------------|
| EDGE-01U-SP | 1U | 72 | 72 | 72 | 12 | 144 |
| EDGE-02U | 2U | 144 | 144 | 144 | 24 | 288 |
| EDGE-04U | 4U | 288 | 288 | 288 | 48 | 576 |
| EDGE-01U-FP | 1U | 48 | 48 | 48 | 8 | 96 |
| EDGE-02U-FP | 2U | 96 | 96 | 96 | 16 | 192 |
| EDGE-04U-FP | 4U | 192 | 192 | 192 | 32 | 384 |

For OM4 heather violet, please use AV connector code.


MTP® Adapter Panels

EDGE™ MTP® adapter panels provide a simple interface to mate MTP connectors. This occurs when connecting MTP trunks to MTP extender trunks, MTP trunks to trunk harnesses, and when MTP trunks are connected to MTP jumpers.

EDGE 72-fiber MTP panels feature reversible translucent shuttered MTP adapters at the front of the panel.



EDGE 72-Fiber MTP Panel | Photo LAN4147



MTP Adapter Panel with Four MTP Adapters | Photo LAN2695

Ordering Information

| Part Number | Fiber Count | Fiber Category |
|--------------|-------------|--------------------------------|
| EDGE-CP24-E3 | 24 | 50 μ m Multimode (OM3/OM4) |
| EDGE-CP24-EY | 24 | 50 μ m Multimode (OM5) |
| EDGE-CP24-90 | 24 | Single-mode (OS2) |
| EDGE-CP48-E3 | 48 | 50 μ m Multimode (OM3/OM4) |
| EDGE-CP48-EY | 48 | 50 μ m Multimode (OM5) |
| EDGE-CP48-90 | 48 | Single-mode (OS2) |
| EDGE-CP72-U3 | 72 | 50 μ m Multimode (OM3/OM4) |
| EDGE-CP72-UY | 72 | 50 μ m Multimode (OM5) |
| EDGE-CP72-U1 | 72 | Single-mode (OS2) |

EDGE™ Tap Modules

EDGE™ Tap modules, part of EDGE solutions for data centers and storage area networks (SAN), enable passive optical tapping of the network while reducing downtime and link loss, and increasing rack space utilization and density compared to other optical tap options.

Unlike other passive optical taps that must be added as separate devices in the network link, the EDGE Tap module integrates the coupler technology for passive optical tapping into a structured cabling component – the module. Monitored ports can be added without disrupting the system’s live traffic. Elimination of the tap as a separate device reduces insertion loss in the link. EDGE Tap modules use an advanced splitter technology for multimode to reduce insertion loss compared to traditional splitter technology.

Featuring the EDGE solutions high-density module footprint, EDGE Tap modules are available in multiple configurations for network monitoring at 1G, 10G, or 40G. These tap modules enable up to 72 monitored links per one rack unit and fit seamlessly into EDGE solutions hardware for maximum cable management and better utilization of rack space.

Note: Refer to [AEN164](#) for application information.

Features and Benefits

Network monitoring and tap splitters integrated into the structured cabling

Eliminates need for additional rack space and downtime associated with port tap changes.

Rear-exiting, MTP® connector-based tap ports

Zero-rack-space impact results in higher revenue generation per rack unit.

Advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach.

EDGE™ solutions-based footprint

Integrates seamlessly into an existing EDGE solutions infrastructure.

Universal polarity management

Eliminates the frustration of needing to flip connector pairs or modules.

Application defined split ratio

Provides 50/50 split ratio for Ethernet (DC LAN) and 70/30 split ratio for Fiber Channel (DC SAN) environments.



EDGE Tap Modules | Photo REN3557 (MTP to LC) REN3556 (LC to LC) REN3559 (MTP to MTP)

LC Duplex to LC Duplex Tap Modules

EDGE™ LC duplex to LC duplex Tap modules enable port monitoring access for traditional LC duplex systems. These modules allow the customer to manage the monitoring ports via the jumper infrastructure at the front of the cabinets.

LC duplex to LC duplex Tap modules feature two red LC duplex adapters for tapping and four aqua or blue LC duplex adapters for live ports. These modules are also available for BiDi applications with two duplex adapters for tapping and two duplex adapters for live ports.



LC to LC Multimode Tap Module | Photo REN3556



LC to LC Single-Mode Tap Module | Photo REN3563



LC to LC Duplex BiDi Tap Module | Photo REN3554

| Multimode | | |
|-------------|---|-----------------------------|
| Part Number | Description | # of Duplex Ports Monitored |
| ETM-5A-Q | EDGE Tap Module, LC-LC, 50/50 split ratio | 2 |
| ETM-5A-Q-BD | EDGE Tap Module, LC-LC, 50/50 split ratio, BiDi | 1 |
| ETM-7A-Q | EDGE Tap Module, LC-LC, 70/30 split ratio | 2 |

| Single-Mode | | |
|-------------|---|-----------------------------|
| Part Number | Description | # of Duplex Ports Monitored |
| ETM-5A-G | EDGE Tap Module, LC-LC, 50/50 split ratio | 2 |
| ETM-7A-G | EDGE Tap Module, LC-LC, 70/30 split ratio | 2 |

| Specs | | | | | | | |
|-------------|------------|-------------|-----------------------------|------------------------|-------------------------|----------------------------------|---------------------------------|
| Part Number | Fiber Type | Split Ratio | Splitter Loss (dB) Live/Tap | LC Connector Loss (dB) | MTP Connector Loss (dB) | Tap Module's Live Link Loss (dB) | Tap Module's Tap Link Loss (dB) |
| ETM-5A-Q | OM4 | 50/50 | 3.7/3.7 | 0.15 | N/A | 4 | 4 |
| ETM-5A-Q-BD | OM4 | 50/50 | 3.7/3.7 | 0.15 | N/A | 4 | 4 |
| ETM-7A-Q | OM4 | 70/30 | 1.8/5.8 | 0.15 | N/A | 2.1 | 6.1 |
| ETM-5A-G | OS2 | 50/50 | 3.5/3.5 | 0.25 | N/A | 4 | 4 |
| ETM-7A-G | OS2 | 70/30 | 2.0/5.8 | 0.25 | N/A | 2.5 | 6.3 |

MTP® to LC Duplex Tap Modules

EDGE™ MTP® to LC duplex Tap modules are designed for parallel optic infrastructure, for Ethernet duplex applications up to 100G, and Fiber Channel duplex applications up to 32G.

MTP to LC duplex Tap modules have one pinned MTP adapter labeled Live and one pinned red MTP adapter labeled Tap on the rear side, which enables monitoring of six Live LC duplex ports on the front side. MTPs on the rear side allow for easy Tap link integration into the infrastructure.



MTP to LC Duplex Multimode Tap Module | Photo REN3557



MTP to LC Duplex Single-Mode Tap Module | Photo REN3565



MTP to LC Duplex BiDi Tap Module | Photo REN3552

| Multimode | | |
|-------------|--|-----------------------------|
| Part Number | Description | # of Duplex Ports Monitored |
| ETM-5B-Q | EDGE Tap Module, MTP-LC, 50/50 split ratio | 6 |
| ETM-5B-Q-BD | EDGE Tap Module, MTP-LC, 50/50 split ratio, BiDi | 6 |
| ETM-7B-Q | EDGE Tap Module, MTP-LC, 70/30 split ratio | 6 |

| Single-Mode | | |
|-------------|--|-----------------------------|
| Part Number | Description | # of Duplex Ports Monitored |
| ETM-5B-G | EDGE Tap Module, MTP-LC, 50/50 split ratio | 6 |
| ETM-7B-G | EDGE Tap Module, MTP-LC, 70/30 split ratio | 6 |

| Specs | | | | | | | |
|-------------|------------|-------------|-----------------------------|------------------------|-------------------------|----------------------------------|---------------------------------|
| Part Number | Fiber Type | Split Ratio | Splitter Loss (dB) Live/Tap | LC Connector Loss (dB) | MTP Connector Loss (dB) | Tap Module's Live Link Loss (dB) | Tap Module's Tap Link Loss (dB) |
| ETM-5B-Q | OM4 | 50/50 | 3.7/3.7 | 0.15 | 0.35 | 4.2 | 4.4 |
| ETM-5B-Q-BD | OM4 | 50/50 | 3.7/3.7 | 0.15 | 0.35 | 4.2 | 4.4 |
| ETM-7B-Q | OM4 | 70/30 | 1.8/5.8 | 0.15 | 0.35 | 2.3 | 6.5 |
| ETM-5B-G | OS2 | 50/50 | 3.5/3.5 | 0.25 | 0.75 | 4.6 | 5.1 |
| ETM-7B-G | OS2 | 70/30 | 2.0/5.8 | 0.25 | 0.75 | 2.8 | 7.3 |

MTP® to MTP Connector Tap Modules

EDGE™ MTP® to MTP Tap modules are designed for parallel optic infrastructure, for Ethernet 40G and 100G applications, and Fiber Channel applications 32G and beyond.

MTP to MTP Tap modules provide two options to connect the monitoring equipment from the front or rear of the rack to support duplex or parallel optic deployments.



MTP to MTP Multimode Tap Module | Photo REN3559



MTP to MTP Single-Mode Tap Module | Photo REN3571

| Multimode | | | |
|-------------|---|-----------------------------|--------------------------|
| Part Number | Description | # of Duplex Ports Monitored | # of MTP Ports Monitored |
| ETM-5C-Q | EDGE Tap Module, MTP-MTP, 50/50 split ratio | 6 | 1 |
| ETM-7B-Q | EDGE Tap Module, MTP-MTP, 70/30 split ratio | 6 | 1 |
| ETM-5C-Q-R | EDGE Tap Module, MTP-MTP, 50/50 split ratio, rear tap | 6 | 1 |
| ETM-7B-Q-R | EDGE Tap Module, MTP-MTP, 70/30 split ratio, rear tap | 6 | 1 |

| Single-Mode | | | |
|-------------|---|-----------------------------|--------------------------|
| Part Number | Description | # of Duplex Ports Monitored | # of MTP Ports Monitored |
| ETM-5C-G | EDGE Tap Module, MTP-MTP, 50/50 split ratio | 6 | 1 |
| ETM-7B-G | EDGE Tap Module, MTP-MTP, 70/30 split ratio | 6 | 1 |
| ETM-5C-G-R | EDGE Tap Module, MTP-MTP, 50/50 split ratio, rear tap | 6 | 1 |
| ETM-7B-G-R | EDGE Tap Module, MTP-MTP, 70/30 split ratio, rear tap | 6 | 1 |

| Specs | | | | | | | |
|--------------|------------|-------------|-----------------------------|------------------------|-------------------------|----------------------------------|---------------------------------|
| Part Number | Fiber Type | Split Ratio | Splitter Loss (dB) Live/Tap | LC Connector Loss (dB) | MTP Connector Loss (dB) | Tap Module's Live Link Loss (dB) | Tap Module's Tap Link Loss (dB) |
| ETM-5C-Q | OM4 | 50/50 | 3.7/3.7 | N/A | 0.35 | 4.4 | 4.4 |
| ETM-7B-Q | OM4 | 70/30 | 1.8/5.8 | N/A | 0.35 | 2.5 | 6.5 |
| ETM-5C-Q-R | OM4 | 50/50 | 3.7/3.7 | N/A | 0.35 | 4.4 | 4.4 |
| ETM-7B-Q-R | OM4 | 70/30 | 1.8/5.8 | N/A | 0.35 | 2.5 | 6.5 |
| ETM-5C-G | OS2 | 50/50 | 3.5/3.5 | N/A | 0.75 | 5 | 5 |
| ETM-7B-G | OS2 | 70/30 | 2.0/5.8 | N/A | 0.75 | 3.5 | 7.3 |
| ETM-5C-G-R | OS2 | 50/50 | 3.5/3.5 | N/A | 0.75 | 5 | 5 |
| ETM-7B-G-R | OS2 | 70/30 | 2.0/5.8 | N/A | 0.75 | 3.5 | 7.3 |
| ETM-7C-Q-2X3 | OM4 | 70/30 | 1.8 / 5.8 | N/A | .35 | 2.5 | 6.5 |

EDGE™ LC Lockable Uniboot Jumpers

The EDGE™ LC lockable uniboot jumper is the newest addition to our acclaimed EDGE product portfolio. This state-of-the-art jumper delivers the same value as the LC uniboot connector and comes equipped with an integrated locking mechanism for your peace of mind. The new feature allows installers to lock uniboot jumpers in the field to prevent partial connections and accidental disconnects.

Features and Benefits

Corning® CleanAdvantage™ Technology and Optimized Dust Caps

Eliminates the need for scoping and cleaning prior to initial field connection.

Uniboot Design


Allows one cable to carry 2 fibers, reducing the jumper bulk when routing.

Lock-out


Eliminates partial connections and accidental disconnects.

Polarity Management

Reverse polarity without exposing fibers.



Multimode Assembly



Single-mode Assembly

Ordering Information

| | | | | | | | | | | | | |
|----------------------|----------------------|----------------------|----------------------|-----|----------------------|---|----------------------|-----|----------------------|----------------------|----------------------|----------------------|
| <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> | 0 2 | <input type="text"/> | D | <input type="text"/> | 2 0 | <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| 1 | 2 | 3 | 4 | | | | 5 | | | 6 | | |

- 1** Select connector one type.
 U9 = Multimode LC Uniboot (OM3/OM4)
 U8 = Single-mode LC UPC Uniboot (OS2)

- 2** Select connector type two.
 U9 = Multimode LC Uniboot (OM3/OM4)
 U8 = Single-mode LC UPC Uniboot (OS2)

- 3** Select fiber type.
 T = 50 µm multimode (OM3)
 Q = 50 µm multimode (OM4)
 G = Single-mode Ultra (OS2)


- 4** Select flame rate.
 1 = Riser
 8 = Plenum

- 5** Select length.
 001-250 (tip-to-tip)

- 6** Select unit of measure.
 F = Feet
 M = Meters

Reverse Polarity Uniboot Duplex Jumpers

EDGE™ reverse polarity uniboot duplex jumpers allow for the quick-and-easy conversion from a TIA-568 A-B polarity to a TIA-568 A-A polarity without exposing the fibers or needing any tools. This jumper comes with a straight-through polarity from the factory, but you can convert it to a flipped jumper with no tools. This uniboot design allows one cable to carry both fibers, reducing jumper bulk when routing.



Reverse Polarity Uniboot Duplex Jumpers | Photos REN6462 and REN6461

Features

Slim, round two-fiber interconnect cable.

Uniboot-style duplex connectors.

Improved handling in high-density applications.

Low-loss connectivity enables system design flexibility.


Enabled by bend-insensitive Corning® ClearCurve® multimode or Corning® SMF-28e® Ultra single-mode fibers.

Designed to withstand tight bends and challenging cable routes.

LC Uniboot Jumper Specifications

| Connector | Connector Code | Typical Connector Attenuation (dB) | Return Loss (dB) |
|-------------------|----------------|------------------------------------|------------------|
| MM LC uniboot | 79 | 0.10 | ≤ 26 |
| SM LC UPC uniboot | 78 | 0.25 | ≤ 55 |
| SM LC APC uniboot | 80 | 0.25 | ≤ 65 |

Ordering Information



- 1 Select connector one type.**
 79 = Multimode LC uniboot (OM3/OM4/OM5)
 78 = Single-Mode LC UPC uniboot (OS2)
 80 = Single-Mode LC APC uniboot (OS2)

- 2 Select connector two type.**
 79 = Multimode LC uniboot (OM3/OM4/OM5)
 78 = Single-Mode LC UPC uniboot (OS2)
 80 = Single-Mode LC APC uniboot (OS2)

- 3 Select fiber type.**
 T = 50 μm multimode (OM3)
 Q = 50 μm multimode (OM4)
 V = 50 μm multimode (OM5)
 G = Single-Mode Ultra (OS2)

- 4 Select flame rating.**
 1 = Riser
 8 = Plenum

- 5 Select length.**
 001-250 (tip-to-tip)

- 6 Select unit of measure.**
 F = Feet
 M = Meters

Reverse Polarity LC Duplex Clips

All reverse polarity uniboot LC duplex connectors come with a removable clip. We offer a total of 12 colors to allow for easy link identification or fabric segmentation.



EDGE™ Reverse Polarity Uniboot LC Duplex Clips | Photo LAN2254

Ordering Information

TRIGGER-BP-U-

1 Select color.

- N = Blue
- E = Orange
- G = Green
- W = White
- C = Slate
- R = Red
- B = Black
- Y = Yellow
- V = Violet
- P = Rose
- A = Aqua
- K = Beige

Note: Must order in multiples of 100.

Optical Distribution Frames

The 19-inch optical distribution frames (ODF) are optimized for high-density, cross-connect applications. When fully loaded with EDGE™ 4U housings, the dual frame provides a total capacity of 5,760 LC duplex or 11,520 MTP® ports. When the single frame is used, it provides total capacity of 2,880 LC duplex or 5,760 MTP ports.

The frame has been designed with modular jumper management plates and segmented jumper management hubs. A single 4-meter jumper length allows patching from any port to any other port on the dual- or single-frame configuration. Gravity-managed slack storage ensures single jumpers can be added or removed in less than 2 minutes when fully populated.

Additional accessories, like cable routing channels, front doors, back doors, and side panels are available to improve containment, aesthetics, cleanliness, and security.

Features and Benefits

Modular construction

Frame can be quickly assembled by a single installer. Easily scalable to dual- or quad-frame configurations.

One-jumper configuration


A single 4-meter jumper length allows patching from any port to any other port.

Cable and trunk strain-relief kits

Easy routing, dressing, and strain-relief for optical cables or preterminated trunks.







Additional bottom-channel kit available



Route fibers at the bottom of cabinet frame, no need for dedicated overhead trays.








Corning Optical Distribution Frame | Photo REN7527

Corning Optical Distribution Frames

| EDGE™ Optical Distribution Frames | | |
|-----------------------------------|---|---|
| Part Number | Product Description | |
| PF2TDAFG5LCANNNN2PADQ | EDGE™ Optical Distribution Frame (ODF), left cable management, 7 ft |  |
| PF2TDAFG5RCANNNN2PADQ | EDGE ODF, right cable management, 7 ft |  |
| PC2TDAFG5LCAA2FA2PADQ | EDGE ODF, left cable management, 7 ft with doors |  |
| PC2TDAFG5RCAB2FA2PADQ | EDGE ODF, right cable management, 7 ft with doors |  |
| PF2QDACG7ZDANNNN2PFDQ | EDGE ODF, dual, 7 ft |  |
| PC2QDACG7ZDAG7FA2PFDQ | EDGE ODF, dual, 7 ft with doors |  |








| Cleaning Accessories | | | |
|----------------------|--|--------------------|---|
| Part Number | Product Description | Units per Delivery | |
| CLEANER-PORT-LC | Single-Fiber Port Cleaner for LC, keyed LC, and MU connector end faces for both UPC and APC polishes | 1/1 |  |
| 2104466-01 | Fiber Optic Cleaning Tool used to clean MTP® connector end faces as well as MTP connectors installed in a module | 1/1 |  |






| Housing Accessories | | | |
|---------------------|--|--------------------|---|
| Part Number | Product Description | Units per Delivery | |
| EDGE8-TRAY-QTY1 | EDGE8® Hardware Accessory, EDGE8 tray kit, quantity of 1 | 1/1 |  |
| EDGE8-TRAY-QTY12 | EDGE8 Hardware Accessory, EDGE8 tray kit, quantity of 12 | 12/1 |  |
| EDGE-BKT-WT-2RU | Wire Tray Mounting Bracket for up to 2U of housing mounting space | 1/1 |  |
| EDGE-BKT-WT-4RU | Wire Tray Mounting Bracket for up to 4U of housing mounting space | 1/1 |  |
| EDGE-SMH-SLK | EDGE™ Single-Module Housing Slack Storage and Splicing Accessory, used in conjunction with the EDGE-SMH and EDGE panel in order to facilitate pigtail splicing or storage of slack beneath the EDGE single-module housing. | 1/1 |  |

EDGE™ Solutions

| Housing Accessories (continued) | | | |
|---------------------------------|---|--------------------|---|
| Part Number | Product Description | Units per Delivery | |
| EDGE-BKT-LR-2RU | Ladder Rack Mounting Bracket for up to 2U of housing mounting space | 1/1 |  |
| EDGE-BKT-LR-4RU | Ladder Rack Mounting Bracket for up to 4U of housing mounting space | 1/1 |  |
| EDGE-CDF-RJ04-BKT | EDGE™ Solutions Strain-Relief Bracket, accommodating four EDGE solutions clip parking positions | 1/1 |  |
| EDGE-CDF-RJ08-BKT | EDGE Solutions Strain-Relief Bracket, accommodating eight EDGE solutions clip parking positions | 1/1 |  |
| EDGE-CDF-RJ12-BKT | EDGE Solutions Strain-Relief Bracket, accommodating 12 EDGE solutions clip parking positions | 1/1 |  |
| PC1-BKT-23 | EDGE Extension and Flush-Mount Bracket for mounting 1U housings into 23-in racks or cabinets | 1/1 |  |
| PC2-BKT-23 | EDGE Extension and Flush-Mount Bracket for mounting 2U housings into 23-in racks or cabinets | 1/1 |  |

EDGE™ Solutions

| Housing Accessories (continued) | | | |
|---------------------------------|---|--------------------|---|
| Part Number | Product Description | Units per Delivery | |
| PC4-BKT-23 | EDGE™ Solutions Mounting Bracket for mounting 4U housings into 23-in racks or cabinets | 1/1 |  |
| EDGE-01U-FLSH-BKT | EDGE Extension and Flush-Mount Bracket for EDGE-01U | 1/1 |  |
| CJP-01U-P | Pretium™ Jumper Management Panel 1U; provides jumper management in a 1.75-in rack space | 1/1 |  |
| CJP-02U-P | Pretium Jumper Management Panel 2U; provides jumper management in a 3.5-in rack space | 1/1 |  |
| EDGE-CCHBKT-1 | Bracket to hold one EDGE solutions module that fits into Plug & Play™ housings | 1/1 |  |
| EDGE-CCHBKT-2 | Bracket to hold two EDGE solutions module that fits into Plug & Play housings | 1/1 |  |
| EDGE-EMOD-STRN | EDGE Solutions Strain-Relief Bracket, EMOD, 1U | 1/1 |  |

| MTP® PRO Accessories | | | |
|------------------------|---|--------------------|---|
| Part Number | Product Description | Units per Delivery | |
| MTPPRO-TOOL | Field tool to perform pinning and polarity changes of MTP® PRO connectors | 1/1 |  |
| MTPPRO-PEX-MME-NO PINS | MTP PRO Pin Exchanger Kit, SM MTP Elite, empty (without pins) | 1/1 |  |
| MTPPRO-PEX-MME-PINS | MTP PRO Pin Exchanger Kit, MM MTP Elite, loaded (with pins) | 1/1 |  |
| MTPPRO-PEX-SME-NO PINS | MTP PRO Pin Exchanger Kit, SM MTP Elite, empty (without pins) | 1/1 |  |
| MTPPRO-PEX-SME-PINS | MTP PRO Pin Exchanger Kit, SM MTP Elite, loaded (with pins) | 1/1 |  |

CORNING

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.
All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.
© 2021, 2023 Corning Optical Communications. All rights reserved. LAN-2267-AEN / August 2023

