

# Corning® ClearCurve® XB Specialty Optical Fiber

CORNING



*Reduced footprint  
components and  
bend sensitive  
applications*

*Corning's ClearCurve® XB fiber is a full-spectrum optical fiber with improved macro-bend performance compared to legacy single-mode fibers. Products of all types are constantly decreasing their size and becoming more complex. Having the ability to place fibers in increasingly smaller footprints without performance degradation is crucial to keeping the optical loss budgets low. The contribution by bend loss to the overall loss budget increases as the amount of fiber that is deployed in the bent state increases. Having a fiber that is designed for low bend loss makes these new smaller products a reality.*

## Applications:

- Bend sensitive applications
- Footprint reduction
- Small size and integrated EDFA's
- Couplers
- Pigtails/patchcords

## Features:

- Low bend loss design
- Fully compatible with legacy fibers
- Ease of handling and splice ability of standard single mode fibers
- Economical bend loss performance
- Optical attenuation that is flat across the C & L-Bands
- 200 kpsi proof test for higher mechanical reliability in small bend scenarios
- Fully compliant with the following standards:
  - ITU-T G.652.D
  - ITU-T G.657.A1

# ClearCurve® XB Specialty Optical Fiber

## Optical Specifications

Cable Cutoff Wavelength ( $\lambda_{cf}$ ) (nm)	$\leq 1260$
---	-------------

	Wavelength (nm)	Maximum Value* (dB/km)
Maximum Attenuation	1310	0.33 - 0.35
	1550	0.19 - 0.20
	1625	0.20 - 0.23

\* Maximum specified attenuation value available within the stated ranges

\*\* Attenuation post-hydrogen aging according to IEC 60793-2-50 Section C.5 for B.1.3 fibers.

	Wavelength (nm)	MFD ( $\mu\text{m}$ )
Mode-field Diameter	1310	$8.6 \pm 0.4$
	1550	$9.8 \pm 0.5$

	Wavelength (nm)	Dispersion Value [ps/(nm·km)]
Dispersion	1550	$\leq 18.0$
	1625	$\leq 22.0$

Zero Dispersion Wavelength ( $\lambda_0$ ):  $1304 \text{ nm} \leq \lambda_0 \leq 1324 \text{ nm}$

Zero Dispersion Slope ( $S_0$ ):  $\leq 0.089 \text{ ps}/(\text{nm}^2 \cdot \text{km})$

Polarization Mode Dispersion (PMD)	Value (ps/ $\sqrt{\text{km}}$ )
Maximum Individual Fiber	$\leq 0.1$

	Wavelength (nm)	Point Discontinuity (dB)
Point Discontinuity	1310	$\leq 0.05$
	1550	$\leq 0.05$

## Key Geometric, Mechanical and Environmental Specifications

Cladding Diameter ( $\mu\text{m}$ )	$125.0 \pm 0.7$
Core-Clad Concentricity ( $\mu\text{m}$ )	$\leq 0.5$
Cladding Non-Circularity (%)	$\leq 0.7$
Coating Diameter ( $\mu\text{m}$ )	$242 \pm 5$
Coating-Cladding Concentricity ( $\mu\text{m}$ )	$< 12$
Coloring Diameter* ( $\mu\text{m}$ )	$250 +15/-9$
Fiber Curl (m)	$\geq 4.0$ radius of curvature

\* If applicable

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 (dB/km)
Temperature Dependence ( $^{\circ}\text{C}$ )	-60 to 85 *	$\leq 0.05$
Temperature-Humidity Cycling ( $^{\circ}\text{C}$ )	-10 to 85 * up to 98% RH	$\leq 0.05$
Water Immersion ( $^{\circ}\text{C}$ )	23 * $\pm 2$	$\leq 0.05$
Dry Heat Soak ( $^{\circ}\text{C}$ )	85 * $\pm 2$	$\leq 0.05$
Damp Heat ( $^{\circ}\text{C}$ )	85 * at 85% RH	$\leq 0.05$
Operating Temperature Range ( $^{\circ}\text{C}$ )	-60 to 85	
Proof Test (kpsi)	$\geq 200$	
Lengths	Available up to 50.4 km per spool	

\* Reference temperature:  $23^{\circ}\text{C}$

# ClearCurve<sup>®</sup> XB Specialty Optical Fiber

## Performance Characterizations\*

Index of Refraction (Core)		1.45	
Numerical Aperture		0.13	
Macrobend Loss			
Mandrel Diameter (mm)	Number of Turns	Wavelength (nm)	Induced Attenuation** (dB)
20	1	1625	1.5
20	1	1550	0.5

\* Values in this table are nominal or calculated values

\*\* The induced attenuation due to fiber wrapped around a mandrel of a specified diameter.

For more information about Corning's leadership in Specialty Fiber technology visit our website at [www.corning.com/specialtyfiber](http://www.corning.com/specialtyfiber)  
To obtain additional technical information, an engineering sample or to place an order for this product, please contact us at:

**Corning Incorporated**    Tel: +1-607-974-9974  
                                    Fax: +1-607-974-4122  
                                    E-mail: [specialtyfiber@corning.com](mailto:specialtyfiber@corning.com)

© 2010 Corning Incorporated

